





SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	12
	LAST NO. USED	10


MISSING SYMBOLS		DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APPROV	APPROV
		DATE	STG	REV	N/P						
NO MISSING SYMBOL NUMBER		23MY02	R	10	-	-	ALL PARTS - CLEARED REV COLUMN & REVISED MATERIAL SPECS: 12048074 - UPDATED PDM ATTRIBUTES	222820	HAM	HAM	DLB
	22AU02	R	11	-	-	-	15366078, 15326396, 15326225, 12160223, 12160222, 12094200, 12097802 - REVISED MAT'L SIZE AND MAT'L SPEC	211578	ESF	EAR	CMC
	06FE03	R	12	-	-	-	ALL ACTIVE PARTS - UPDATED PDM ATTRIBUTES	236349	MAC	MAC	JMP
	140C03	R	13	-	-	-	15366078 - MAT'L SPEC WAS M3620 HCN4	245588	ADK	TLD	BG
	17FE04	-	14	-	-	-	12048074, 12094200, 12097802, 12160222, 12160223, 15326225, 15326396 & 15366078 - T.O.D. UPDATED	250621	J5	J5	BG
	190C04	R	15	-	-	-	ALL ACTIVE PARTS - ADDED TERMINAL ID NOTE	260108	RTV	JAA	NKM
	09MR06	R	16	-	-	-	12084200 & 15326396 - UPDATED PDM ATTRIBUTES	276509	JBD	AWD	JES
	24MY06	R	17	-	-	-	12092702 - OBSOLETE	280889	GLS	JAA	BGG
	16JN06	R	18	-	-	-	ALL ACTIVE PARTS - PSD WAS #4	281799	JTZ	JWZ	BGG
	27JL12	R	19	-	-	-	12160222-23 - UPDATED MATERIAL CALLOUT AND ADDED TYPE 203	418958	AJP	AJP	MAA
	02JA13	R	20	-	-	-	12160222-23 - UPDATED PDM ATTRIBUTES	420897	IMF	JAA	MAA
	24JA13	R	21	-	-	-	12160222-23 - UPDATED PDM ATTRIBUTES	421210	AGC	JAA	MAA
	19FE15	R	22	-	-	-	12160222-23 - ADDED TARNISH NOTE	428876	JVR	JWM	JSM
150C18	R	23	-	-	-	ALL ACTIVE PARTS - ADDED "SEALED" COLUMN ON CHART	441102	CGB	CGB	LES	
25FE20	R	24	-	-	-	12160222-23 - UPDATED PDM ATTRIBUTES	551096	JGO	JAA	OMS	



TYPE 202
SAME AS TYPE 10
EXCEPT AS SHOWN



TYPE 201



TYPE 203
SAME AS TYPE 202
EXCEPT AS SHOWN

NOTES:

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEE MATH MODEL FOR PRECISE DIMENSION)
FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR
TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. RECOMMENDED MATING BLADE - WIDTH : 1.64/1.4
THICKNESS : 0.86/0.79
LENGTH : 7.1/6.9
3. "PXX" INDICATES "P" PLUS LAST TWO DIGITS OF MAKE SERIES
NUMBER (P01, P02, P03, ETC.).
4. DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE
SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN
OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.
5. FOR TERMINALS PACKAGED & STORED IN THE APPROVED MANNER,
TARNISH ON SILVER PLATED SURFACES WILL NOT AFFECT THE
PERFORMANCE OF THE PART.

-	-	-	0.254 X 30.96	-	15366078	05	AC	0.254 X 29.8	AU PLATED COPPER ALLOY	1-0.8-0.5	60	2.8-2.03	202	3	X		
-	-	-	0.254 X 30.96	-	15326396	03	AD	0.254 X 29.8	AU PLATED COPPER ALLOY	0.5-0-0.35	21	2.2-1.3	202	2.1	X		
-	-	-	0.254 X 30.96	-	15326225	03	AC	0.254 X 29.8	SN PLATED COPPER ALLOY	1-0.8-0.5	60	2.8-2.03	202	3	X		
-	-	-	0.254 X 30.96	-	12160223	06	AE	0.254 X 29.8	AG PLATED COPPER ALLOY	1-0.8	17	2.65-1.85	203	3	X		
-	-	-	0.254 X 30.96	-	12160222	06	AE	0.254 X 29.8	AG PLATED COPPER ALLOY	0.5-0-0.35	21	2.2-1.3	203	2.1	X		
I2092702	O3	AB	0.254 X 30.96	METAL COPPER ALLOY	12084200	06	AD	0.254 X 29.8	SN PLATED COPPER ALLOY	0.5-0-0.35	21	2.2-1.3	202	2.1	X		
-	-	-	0.254 X 30.96	-	12059611	C1	-	0.254 X 30.96	SN PLATED COPPER ALLOY	0.35	22	2.1-1.7	201	2.2	-		
I2092667	B1	-	0.254 X 30.96	METAL COPPER ALLOY	12048074	11	AC	0.254 X 29.8	SN PLATED COPPER ALLOY	1-0.8-0.5	60	2.8-2.03	202	3	X		
PART	NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART	NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	SIZE (MM²)	ID	DIA	TYPE	G	SEALED
UNPLATED																CABLE	

[illegible]

• APTIV • CONNECTION SYSTEMS WARRLEN, OH COPYRIGHT 1996 APTIV. ALL RIGHTS RESERVED. THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENTS TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.									
								DATE	
DR									
APV001 S. LIMON A. 26AU96									
APV02 FCO. KOPCA 26AU96									
APV03 T. BUTTLE 220C96									
APV04A									
APV05									
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001									
UNLESS SPEC'ED									
WATER SHIELD CHART									
DRAWING NAME									
TAXI TERM F M/P 150 LOCKING LANCE									
DRAWING NUMBER									
12047884									
SIZE		SCALE		FRAME NO		SHEET NO		STD REV	
A0		1/4"		1 OF 1		2 OF 2		R 24	

6		PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)		CHART D	
FROM	0		
TO	12	> 12	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
±0.1		±0.2	
ANGULAR TOLERANCE		±2°	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12084200](#)