






SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	12
	LAST NO. USED	10

DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APPROV	APPROV 2
DATE	STG	N/P	CHG						
23MY02	R	10	-		ALL PARTS - CLEARED REV COLUMN & REVISED MATERIAL SPECS: 12048074 - UPDATED PDM ATTRIBUTES	222820	HAM	HAM	DLB
22AU02	R	11			15366078, 15326396, 15326225, 12160223, 12160222, 12084200 & 12048074 - REVISED MAT'L SIZE AND MAT'L SPEC	211578	ESF	EAR	CMC
06FE03	R	12	-		ALL ACTIVE PARTS - UPDATED PDM ATTRIBUTES	236349	MAC	MAC	JMP
14OC03	R	13	-		15366078 - MAT'L SPEC WAS M3620 HCN4	245588	AKD	TLK	B6
17FE04	-	14	-		12048074, 12084200, 12092702, 12160222, 12160223, 15326225, 15326396 & 15366078 - T.O.D. UPDATED	250621	JS	JS	B6
19OC04	R	15	-		ALL ACTIVE PARTS - ADDED TERMINAL ID NOTE	260108	RTV	JAA	NKM
09MR06	R	16	-		12084200 & 15326396 - UPDATED PDM ATTRIBUTES	276509	JBD	ABO	JES
24MY06	R	17	-		12092702 - OBSOLETE	280889	GLS	JAA	BDG
16JN06	R	18	-		ALL ACTIVE PARTS - PSD WAS #4	281799	JTZ	JMD	JUN
27JL02	R	19	-		12160222-23 - UPDATED MATERIAL CALLOUT AND ADDED TYPE 203	418959	AJP	AJP	MAA
02JA13	R	20	-		12160222-23 - UPDATED PDM ATTRIBUTES	420897	AMF	JAA	MAA
24JA13	R	21	-		12160222-23 - UPDATED PDM ATTRIBUTES	421210	AGC	JAA	MAA
19FE15	R	22	-		12160222-23 - ADDED TARNISH NOTE	428876	JVR	JVM	JSM
15OC18	R	23	-		ALL ACTIVE PARTS - ADDED "SEALED" COLUMN ON CHART	441102	G60	C60	LES
25FE20	R	24	-		12160222-23 - UPDATED PDM ATTRIBUTES	551096	G60	JAA	OMS



TYPE 202
SAME AS TYPE 10
EXCEPT AS SHOWN



TYPE 203
SAME AS TYPE 202
EXCEPT AS SHOWN

NOTES:

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEE MATH MODEL FOR PRECISE DIMENSION)
FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR
TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. RECOMMENDED MATING BLADE - WIDTH : 1.64/1.4
THICKNESS : 0.86/0.79
LENGTH : 7.1/6.9
3. "PXX" INDICATES "P" PLUS LAST TWO DIGITS OF MAKE SERIES
NUMBER (P01, P02, P03, ETC.).
4. DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE
SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN
OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.
5. FOR TERMINALS PACKAGED & STORED IN THE APPROVED MANNER,
TARNISH ON SILVER PLATED SURFACES WILL NOT AFFECT THE
PERFORMANCE OF THE PART.

-	-	-	0.254 X 30.96	-	15366078	05	AC	0.254 X 29.8	AU PLATED COPPER ALLOY	1-0.8-0.5	60	2.8-2.03	202	3	X
-	-	-	0.254 X 30.96	-	15326396	03	AD	0.254 X 29.8	AU PLATED COPPER ALLOY	0.5-0.35	21	2.2-1.3	202	2.1	X
-	-	-	0.254 X 30.96	-	15326225	03	AC	0.254 X 29.8	SN PLATED COPPER ALLOY	1-0.8-0.5	60	2.8-2.03	202	3	X
-	-	-	0.254 X 30.96	-	12160223	06	AE	0.254 X 29.8	AG PLATED COPPER ALLOY	1-0.8	17	2.65-1.85	203	3	X
-	-	-	0.254 X 30.96	-	12160222	06	AE	0.254 X 29.8	AG PLATED COPPER ALLOY	0.5-0.35	21	2.2-1.3	203	2.1	X
12092702	O3	AB	0.254 X 30.96	METAL COPPER ALLOY	12084200	06	AD	0.254 X 29.8	SN PLATED COPPER ALLOY	0.5-0.35	21	2.2-1.3	202	2.1	X
-	-	-	0.254 X 30.96	-	12059611	C1	-	0.254 X 30.96	SN PLATED COPPER ALLOY	0.35	22	2-1.47	201	2.2	-
12092667	B1	-	0.254 X 30.96	METAL COPPER ALLOY	12048074	11	AC	0.254 X 29.8	SN PLATED COPPER ALLOY	1-0.8-0.5	60	2.8-2.03	202	3	X
PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	SIZE (MM²)	ID	DIA	TYPE	G	SEALED
UNPLATED					PLATED					CABLE					

A PART DRAWING THAT A PART NUMBER
 INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE
 FOR ORDERING.
 PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE
 THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.
 CONTACT APPLI SALES TO ASSURE AVAILABILITY
 OF PARTS.
 DOW TYPE
 PART DRAWING
 STYLE
 VOLUME (CM)
 DISTR CODE
 OTHERWISE SPECIFIED
 THIS DOCUMENT IS IN ACCORDANCE WITH ANSI Y14.5M-1994
 AS MODIFIED BY THE ORIGINAL DIMENSIONING AND
 TOLERANCING ADDENDUM - 1991. ALL GEOMETRIC TOLERANCES
 ARE DEFINED IN DATUMS A-F. SURF. SLE 41 PERFECT FORM AT
 MAXIMUM DO NOT APPLY WHEN RELATIONSHIP BETWEEN FEATURES
 IS ESTABLISHED BY DIMENSIONS OR DIMENSIONAL TOLERANCES.
 DIMENSIONS AND TOLERANCES MAY BE QUANTIFIED SEPARATELY,
 REGARDLESS OF DATUM REFERENCE.
 ALL DIMENSIONS ARE IN MILLIMETERS
 REFERENCE
 THRO
 ANGLE
 DO NOT
 SCALE
 USE MATR DATA
 NX

• A P T I V •

CONNECTION SYSTEMS

WARREN, OH

COPYRIGHT 1996 APV, ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APV AND CONTAINS APV
 CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND
 UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL
 AS COMMUNICATION OF ANY DATA TO OTHERS, WITHOUT EXPRESS
 AUTHORIZATION, IS PROHIBITED.

DATE	
DR	
APVD1	26AUG96
APVD2	26AUG96
APVD3	220C96
APVD4	

SUBSTANCES OF CONCERN AND RECYCLED
 CONTENT PER APV11 10494601

MATERIAL SHEET CHART

DRAWING NAME									
TAXI TERM F M/P 150 LOCKING LANCE									
DRAWING NUMBER									
12047884									
SIZE	SCALE	FRAME	NO	SHEET	NO	STO	REV	TRV	PVP
A0	10:1	1	OF 1	1	OF 2	R	24		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12048074](#)