













①

ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33308978	01	CODE A	ALL PARTS VO / 16,6
33308979	01	CODE B	
33308980	01	CODE C	
33308981	01	CODE D	
33346866	01	CODE A	ALL PARTS NVO / 16,1
33347795	01	CODE B	
33347798	01	CODE C	
33347799	01	CODE D	

POSITION	1								2		3	
NAME	HOUSING STRAP MOUNT								SECONDARY LOCK		SL SEAL	
MATERIAL	PBT GF30 FR17				PBT GF30				PBT GF30 FR17	PBT GF30	LSR 50 SHORE	
COLOR:	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	ORANGE	YELLOW	REDDISH-BROWN	
PART-NO.:	33308619	33308620	33308622	33308625	33346509	33347328	33347332	33347335	33308630	33346468	33283927	
-	---	---	---	---	---	---	---	---	---	---	---	
-	1	---	---	---	---	---	---	---	1	---	1	
-	---	1	---	---	---	---	---	---	1	---	1	
-	---	---	1	---	---	---	---	---	1	---	1	
-	---	---	---	1	---	---	---	---	1	---	1	
-	---	---	---	---	1	---	---	---	---	1	1	
-	---	---	---	---	---	1	---	---	---	1	1	
-	---	---	---	---	---	---	1	---	---	1	1	
-	---	---	---	---	---	---	---	1	---	1	1	



NOTES

- ON MAIN VIEW ASSEMBLY 33308978 SHOWN (CODE A)
- DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION
- ASSEMBLY INSTRUCTION NO. :
 - 35269104-CUS71 - PRELIMINARY ASSEMBLY
 - 35269104-CUS72 - HARNESS ASSEMBLY
 - 35269103-CUS73 - CAR ASSEMBLY
- MATING PARTS:
 - 4 WAY 2.8 FEMALE CONNECTOR ASM DWG-NO.: 35095833
 - BACKSHELL 90 DEG APTIV DWG-NO.: 35024558 (HT DWG-NO.: 18-0195-001-CS6)
 - BACKSHELL 180 DEG APTIV DWG-NO.: 35024559 (HT DWG-NO.: 17-0598-001-CS6)
 - PROTECTION CAP APTIV DWG-NO.: 35391874 (HT DWG-NO.: 17-2270-001-CS6)
- MATING TERMINAL SYSTEM:
 - 2.8 TERMINAL DWG-NO.: 13548085
 - MAX WIRE CROSS SECTION: 2.5MM²

1 APTIV LOGO

2 MATERIAL NAME ACCORDING TO VDA 260

3 DATE INSERT

4 TOOL CAVITY NUMBER

5 INDEX REPLACEMENT INSERT

6 PART CAVITY NUMBER

7 MOVING DISTANCE OF SECONDARY LOCK

8 INTERFACE FOR CLIP MOUNTING

HT CLIP NUMBER:
YCCSFT6,SPT0.8-2.5; FT6LG,M.St.Aufn.11

DIM TO CHECK

FROM TO

1 DIM FOR HELP

THEORETIC DIM

DIMENSIONAL RANGE (MM)

FROM TO

TOLERANCE UNLESS OTHERWISE SPECIFIED

ANGULAR TOLERANCE

CHART E1

R 0.2 MAX

R 0.1 MAX

SHARP CORNER TOLERANCE

DWG STATUS

DATE STG REV N/P CHG

ZONE

REVISION HISTORY

AUTH

DR

APVD 1

APVD 2

250C18

R

01

AA

B7 A7

INITIAL RELEASE

REFERENCE HELLERMANN TYTON DWG-NO. ADDED CLIP REFERENCE CHANGED

P.NAJ M.ZYR M.GRU

150C19

R

01

AB

B7 G10

PROTECTION CAP APTIV DWG-NO.: 35391874 WAS 35274875 PART AVAILABILITY FOR PART NUMBERS 33346866, 33347795, 33347798, 33347799 UPDATED

P.NAJ M.GRU M.SKR

280C20

R

01

AC

B7

HT DWG-NO: 18-0195-001-CS6 WAS 17-0195-001-CS6

P.NAJ M.GRU

SCALE: 1:1

DWG TYP

PART DRAWING

WEIGHT (GR)

SEE CHART

VOLUME (CM³)

ROUTING

DISTR CODE

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES ACCORDING TO: SEE CHART

GD&T ACCORDING TO: ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

DR

P.NAJDUCH

APVD1

M.ZYROMSKI

APVD2

M.GRUDZEWSKI

APVD3

APVD4

APVD5

DATE

240C18

250C18

260C18

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001

SUBSTANCJE NIEBEZPIECZNE I POWTORNIE PRZETWORZONE OKRESLA APTIV 10949001

MATERIAL

SEE CHART

DRAWING NAME

4 WAY 2.8

CTCS STRAP MOUNT MALE ASSEMBLY

DRAWING NUMBER

35096188

SIZE

A1

SCALE

2:1

FRAME NO

1 OF 1

SHEET NO

1 OF 1

STG

R

REV

01

N/P

AC

CONTROLLED DOCUMENTS ARE ONLY AVAILABLE ON THE SERVER

Doc: 35096188-cus01-s01/01AC

Doc: 30-pa0-20

Time: 16:35:31

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33308978](#)