





		1	2
1	KV	KV	TKS
3	KV	KV	TKS

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED UP FOR EASE OF INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. THIS PRODUCT IS NOT CATEGORIZED AS AN APPARENCE ITEM, MINOR
DEFECTS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR
BLEMMISHES, GATE VESTIGES, AND SOFT FLARE THAT DO NOT AFFECT THE
FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER EAMP-4-3.CS.01.01EN
3. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.
4. DESIGNED FOR CORRUGATED TUBE NW26
5. MAXIMUM CABLE TIE WIDTH 5 MM

[illegible]

30303132

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33213199](#)