













ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33254098	01	CODE A	ALL PARTS V0 / 12.7
33254088	01	CODE B	
33254085	01	CODE C	
33254084	01	CODE D	
33344861	01	CODE A	ALL PARTS NVO / 12.3
33344862	01	CODE B	
33344863	01	CODE C	
33344864	01	CODE D	

POSITION	1				2				3		
NAME	HOUSING STRAP MOUNT				SECONDARY LOCK				SL SEAL		
MATERIAL	PBT GF30 FR17				PBT GF30				LSR 50 SHORE		
COLOR:	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	ORANGE	YELLOW	REDDISH-BROWN
PART-NO.:	33249101	33249102	33249107	33249108	33344604	33344607	33344622	33344624	33249026	33344606	33248990
-	---	---	---	---	---	---	---	---	---	---	---
-	1	---	---	---	---	---	---	---	1	---	1
-	---	1	---	---	---	---	---	---	1	---	1
-	---	---	1	---	---	---	---	---	1	---	1
-	---	---	---	1	---	---	---	---	1	---	1
-	---	---	---	---	1	---	---	---	---	1	1
-	---	---	---	---	---	1	---	---	---	1	1
-	---	---	---	---	---	---	1	---	---	1	1
-	---	---	---	---	---	---	---	1	---	1	1



NOTES	
-	ON MAIN VIEW ASSEMBLY 33254098 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION
-	ASSEMBLY INSTRUCTION NO.: 35269104-CUS71 - PRELIMINARY ASSEMBLY 35269104-CUS72 - HARNESS ASSEMBLY 35269103-CUS73 - CAR ASSEMBLY
-	MATING PARTS: - 3 WAY 1.5 FEMALE CONNECTOR ASM DWG-NO.: 33253566 - 2 WAY 1.5 FEMALE CONNECTOR ASM DWG-NO.: 35124386 - BACKSHELL 90 DEG APTIV DWG-NO.: 33365444 (HT DWG-NO.: 17-2274-001-CSG) - BACKSHELL 180 DEG APTIV DWG-NO.: 33365244 (HT DWG-NO.: 17-1454-001-CSG) - ROTARY BACKSHELL 90 DEG APTIV DWG-NO.: 35024558 (HT DWG-NO.: 18-0195-001-CSG) - ROTARY BACKSHELL 180 DEG APTIV DWG-NO.: 35024559 (HT DWG-NO.: 17-0598-001-CSG) - PROTECTION CAP APTIV DWG-NO.: 35426243 (HT DWG-NO.: 17-2269-001-CSG)
-	MATING TERMINAL SYSTEM: - 1.5 TERMINAL DWG-NO.: 15396739 MAX WIRE CROSS SECTION: 1.0MM ² RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1.5MM ² - USE COMBINATION: TE TERMINAL: TAB 1.6, DWG NO.: 1703278-5 SEAL: 2112323-1 MAX INSULATION CRIMP DIMENSIONS: HEIGHT: 3.40; WIDTH: 3.40
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	DATE INSERT
4	TOOL CAVITY NUMBER
5	INDEX REPLACEMENT INSERT

NOTES	
6	PART CAVITY NUMBER
7	MOVING DISTANCE OF SECONDARY LOCK
8	INTERFACE FOR CLIP MOUNTING HT CLIP NUMBER: YCCSFt6.5PT0.8-2.5; FT6LG.M.St.Aufn.11

		DIMENSIONAL RANGE (MM)				CHART E1					
☐ DIM TO CHECK	FROM	> 0	> 20	> 30	> 70	>100	>150	>200	>250	>300	
☐ DIM FOR HELP	TO	20	30	70	100	150	200	250	300	400	
TOLERANCE UNLESS OTHERWISE SPECIFIED											
☐ THEORETIC DIM		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33254088](#)