










ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT	-	---	---	---	---	---	---	---	---	---	---	---
33342243	01	CODE A	ALL PARTS V0 / 31,9	-	1	---	---	---	---	---	---	1	---	1	---
33342248	01	CODE B		-	---	1	---	---	---	---	---	1	---	1	---
33342251	01	CODE C		-	---	---	1	---	---	---	---	1	---	1	---
33342236	01	CODE D		-	---	---	---	1	---	---	---	1	---	1	---
33347860	01	CODE A	ALL PARTS NVO / 30,9	-	---	---	---	---	1	---	---	---	1	1	---
33349147	01	CODE B		-	---	---	---	---	1	---	---	---	1	1	---
33349148	01	CODE C		-	---	---	---	---	---	1	---	---	1	1	---
33349149	01	CODE D		-	---	---	---	---	---	---	1	---	1	1	---



POSITION	1	2	3
NAME	HOUSING STRAP MOUNT	SECONDARY LOCK	SL SEAL
MATERIAL	PBT GF30 FR17	PBT GF30	LSR 50 SHORE
COLOR:	BLACK GREY GREEN BLUE	ORANGE YELLOW REDDISH-BROWN	
PART-NO.:	33325393 33325392 33325389 33325376 33347468 33347885 33347891 33347892	33283290 33347486	33283927
33342243	01	CODE A	
33342248	01	CODE B	
33342251	01	CODE C	
33342236	01	CODE D	
33347860	01	CODE A	
33349147	01	CODE B	
33349148	01	CODE C	
33349149	01	CODE D	

NOTES

- ON MAIN VIEW ASSEMBLY 33342243 SHOWN (CODE A)
- DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION
- ASSEMBLY INSTRUCTION NO.:
 - 35269104-CUS71 - PRELIMINARY ASSEMBLY
 - 35269104-CUS72 - HARNESS ASSEMBLY
 - 35269103-CUS73 - CAR ASSEMBLY
- MATING PARTS:
 - 16 WAY 1.5/2.8 FEMALE CONNECTOR ASM DWG-NO.: 35195556
 - BACKSHELL 90 DEG APTIV DWG-NO.: 35024552 (HT DWG-NO.: 17-2277-001-CSG)
 - BACKSHELL 180 DEG APTIV DWG-NO.: 35024553 (HT DWG-NO.: 17-1491-001-CSG)
 - PROTECTION CAP APTIV DWG-NO.: 35462944 (HT DWG-NO.: 17-2273-001-CSG)
- MATING TERMINAL SYSTEM:
 - 1.5 TERMINAL DWG-NO.: 15396739
 - MAX WIRE CROSS SECTION: 1.0MM²
 - RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1.5MM² - USE COMBINATION:
 - TE TERMINAL: TAB 1.6, DWG NO.: 1703278-5
 - SEAL: 2112323-1
 - MAX INSULATION CRIMP DIMENSIONS: HEIGHT: 3.40; WIDTH: 3.40
 - 2.8 TERMINAL DWG-NO.: 13548085
 - MAX WIRE CROSS SECTION: 2.5MM²

1 APTIV LOGO

2 MATERIAL NAME ACCORDING TO VDA 260

3 DATE INSERT


4 TOOL CAVITY NUMBER

5 INDEX REPLACEMENT INSERT

6 PART CAVITY NUMBER

7 MOVING DISTANCE OF SECONDARY LOCK

DATE	STG	REV	N/P	CHG	ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
28NO18	R	01				INITIAL RELEASE		A.RAJ	P.NAJ	M.GRU
15MR19	R	01	AA		B6	REFERENCE HELLERMANN TYTON DWG-NO. ADDED		K.FAR	M.GRU	K.PIT
27OC20	R	01	AB		B6 G9 B6	PROTECTION CAP APTIV DWG-NO.: 35462944 WAS 35274879 PART AVAILABILITY FOR PART NUMBERS 33347860, 33349147, 33349148, 33349149 UPDATED NOTES UPDATED		P.NAJ	M.GRU	M.SKR



DWG. STATUS		REVISION HISTORY		AUTH	DR	APVD 1	APVD 2
DATE	STG REV N/P CHG	ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
28NO18	R 01		INITIAL RELEASE		A.RAJ	P.NAJ	M.GRU
15MR19	R 01	AA	REFERENCE HELLERMANN TYTON DWG-NO. ADDED		K.FAR	M.GRU	K.PIT
27OC20	R 01	AB	PROTECTION CAP APTIV DWG-NO.: 35462944 WAS 35274879 PART AVAILABILITY FOR PART NUMBERS 33347860, 33349147, 33349148, 33349149 UPDATED NOTES UPDATED		P.NAJ	M.GRU	M.SKR

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES ACCORDING TO: SEE CHART

GD&T ACCORDING TO: ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

SHARP CORNER TOLERANCE

R 0.2 MAX

R 0.1 MAX

CHART E1

DIMENSIONAL RANGE (MM)

FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400
TO	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	

TOLERANCE UNLESS OTHERWISE SPECIFIED

±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2
-------	------	------	------	------	------	------	----	------

ANGULAR TOLERANCE ±2°

APTIV

CONNECTION SYSTEMS

KRAKOW, POLAND

COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WLASNOSCIA APTIV I ZAWIERA POUFNE INFORMACJE. POWIELANIE, ROZPOWSZECZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEJKOLWIEK ICH ZAWARTOSCI BEZ NADANIA WYRAZNYCH UPRAWNIEN, JEST ZABRONIONE.

DR	A.RAJEEV	DATE	27NO18
APVD1	P.NAJDUCH	28NO18	
APVD2	M.GRUDZEWSKI	29NO18	
APVD3			
APVD4			
APVD5			

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001 SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIJE PRZETWORZONE OKREŚLA APTIV 10949001

MATERIAL

SEE CHART

DRAWING NAME

16 WAY 1.5/2.8 CTCS STRAP MOUNT MALE ASSEMBLY

DRAWING NUMBER

35195554

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	2:1	1 OF 1	1 OF 1	R	01	AB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33342243](#)