




ASSOCIATED PARTS			DWG STATUS			ZONE	REVISION HISTORY		AUTH	DR	APVD 1	APVD 2
			DATE	STG	REV							
N°	DESIGNATION	APTIV PN	17AP19	R	01	-		INITIAL RELEASE		P.K.S	E.L.M	J.FAB
1	PLUG 800 2W	35098453										

SECTION A - A



3D VIEW
SCALE 1 : 1



• **APTIV** •

CONNECTION SYSTEMS
Chennai, India

COPYRIGHT 2019 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND
UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL
AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS
AUTHORIZATION, IS PROHIBITED.

CE PLAN EST LE PROPRIETE DE DELPHI CORPORATION ET CONTIENT DES
INFORMATIONS DELPHI CONFIDENTIELLES. LA REPRODUCTION, LA DISTRIBUTION
ET L'UTILISATION DE CE DOCUMENT OU DE SES DONNEES MATHÉMATIQUES CAO,
AINSI QUE LA COMMUNICATION DE TOUT CONTENU À AUTRUI, SANS AUTORISATION
EXPRESSE EST INTERDITE.

		DATE
DR	PRAVEEN KUMAR.S	17AP19
APVD1	E.LAM	17AP19
APVD2	M.VENARD	17AP19
APVD3	J.FABRE	17AP19
APVD4		
APVD5		

MATERIAL	
SEE TABLE	

TUBE

35097408 CUS03

DRAWING NUMBER

35097408

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	5:1	1 OF 1	1 OF 1	R	01	-

DESCRIPTION	APTIV PN	WIRE SECTION	MATERIAL	COLOR
TUBE	35092416	35-50 mm ²	PA66 GF 30	BLACK

		SHARP CORNER TOLERANCE									
		DIMENSIONAL RANGE (MM)								CHART E	
		FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300
☐ DIM TO CHECK COTES A VERIFIER		TO	20	30	70	100	150	200	250	300	400
☐ DIM FOR HELP COTES POUR INFO		TOLERANCE UNLESS OTHERWISE SPECIFIED									
☐ THEORETIC DIM COTES THEORIQUES			+0.15	+0.2	+0.3	+0.4	+0.5	+0.6	+0.8	+1	+1.2
		ANGULAR TOL. FRACTION 1/2°									

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.

PART NUMBERS THAT DO NOT HAVE A LINE PRESENT
INDICATE THAT PHYSICAL PARTS ARE AVAILABLE
FOR ORDERING.

CONTACT APTIV SALES TO ASSURE
AVAILABILITY OF PARTS.

LA LIGNE — TRACÉE SUR LA RÉFÉRENCE
PIÈCE INDIQUE QUE LA PIÈCE N'EST PAS
DISPONIBLE À LA COMMANDE.

LES RÉFÉRENCES PIÈCES QUI NE SONT PAS BARRÉES
INDIQUENT QUE CELLES-CI SONT DISPONIBLES
PHYSIQUEMENT POUR ÊTRE COMMANDÉES

CONTACTER LE SERVICE COMMERCIAL DE APTIV
POUR S'ASSURER DE LA DISPONIBILITÉ DES PIÈCES

R 0.2 MAX — 
SHARP CORNER TOLERANCE

CHART E1					
> 70	>100	>150	>200	>250	>300
100	150	200	250	300	400

100	150	200	250	300	400
UNLESS OTHERWISE SPECIFIED					
±0.4	±0.5	±0.6	±0.8	±1	±1.2
TYPICAL TOLERANCE ±2%					

DWG TYPE PART DRAWING		DISTR CODE D
WEIGHT (GR) 2.08		
VOLUME (CM ³) 1.53		
ROUTING		

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
SEE TABLE

GD&T
ACCORDING TO:
ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT
SCALE
USE MATH
DATA

CAD

NX

User: q1446w
Part: 35097408-CUS03-S01/01
Date: 20-May-19 Time: 19:15:03

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35092416](#)