















TERMINAL, CABLE ALIGNMENT VIEWS
SCALE 10:1



STANDARD REELING



SPLICE AND REEL SPECIFICATIONS
SCALE 1:5

[illegible]

DRAWING NUMBER						
13949867						
SIZE	SCALE	FRAME NO	SHEET NO	STD	REV	N
A1x4	15:1	2 OF 2	1 OF 2	R	13	-
18			17			

SYMBOL DEFINITION		MISSING SYMBOLS	
DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF INSPECTIONS REQUIRED	45	7 9-10 12-23 25-28 30-32 34 36-38 42-44 47-153 155-160 162-189 196
	LAST NO. USED	199	

7/17/93		2048		REVISION HISTORY		AURA		BY		DATE	
2	01	01	01	INITIAL DRAWING RELEASED							
2	01	02	01	1502107,1502150,1502151,1502540 and 1502541 - LATCH, ALL PARTS - UPDATED			421104	AA	AKA/RSK		
2	01	03	01	NEW PASTE UP DUE TO REVEY AND ADDED INSPECTION AND SHUT-UP-ALONE							
4	01	04	01	3517385 - RELEASED			426201	00	000/000		
4	01	05	01	ALL PARTS - ADDED LABEL ON CABLE SLEEVE AND FIRE PROOF CONDUCTOR & INSULATION W/IN CHARTS (ON DRG AND NAVVED CHARTS) 3517385 - ON DRG							
4	01	06	01	1502150,1504561,3517385 - AWO WIRE GAUGE WAS 22-24							
4	01	05	05	1548086 - RELEASED			426903	AA	AKA/RSK		
4	01	06	05	1502109,1504561,3517385 - AWO WIRE GAUGE WAS 22-24 ON DRG			431062	00	000/000		
4	01	06	06	1504561 - UPDATED PART AVAILABILITY							
4	01	07	01	1504561 - UPDATED PART AVAILABILITY			431605	AA	AKA/RSK		
4	01	08	01	3337393,3337394,3337395 - RELEASED			432766	00	000/000		
4	01	09	01	REVISIONS COMPLETED BUT PARTIALLY NOTED ON PDS 3337394							
4	01	10	01	ALL PARTS - REDEMAN, ADDED "TERMINAL, 1504561" & "WIRE SLEEVES" TO SPECIFICATION VIEWS, REVEYED ALL NOTES AND SWATCH CHART			436019	00	000/000		
4	01	11	01	1504561 - UPDATED PART AVAILABILITY			440956	00	000/000		
4	01	12	01	1367970,1504561, 09 & 3333933			441252	AA	AKA/RSK		
4	01	13	01	1504561 - UPDATED PART AVAILABILITY							
4	01	13	02	1548086 & 3337393 - RELEASED			552605	AA	AKA/RSK		

UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
USE (SEAL MATH MODEL FOR PRECISE DIMENSIONS), FOR ALL
OTHER DIMENSIONS NOT SHOWN, USE THE FOLLOWING
BUILD, USE SEAL MATH MODEL FOR PRECISE TOOL PATH DATA.
ALL MATH: 0.02

"P" AND "C" INDICATES "P" PLUS LAST TWO DIGITS OF NAME DIE SERIES NUMBER
(P01, P02, P03, ETC.).

(1)(X)(1) CORPORATE BRAND STAMP TO BE LOCATED ON THIS
EXTERIOR SURFACE, VISIBLE AT ASSEMBLY.
OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE
"P20" OR "C1" LOGO.

TERMINAL SYMMETRICAL ABOUT CENTERLINE EXCEPT AS SHOWN.

RECOMMENDED WARE BLADE THICKNESS TO USE: STANDARD ENCAP-001

WARRANTY: DO NOT PROBE, TEST, OR OTHERWISE CONTACT THE
INTERIOR REGION THE SPRING OR ANY MOVING PARTS OF THIS TERMINAL.
SEVERE DAMAGE CAN OCCUR, COMPROMISING THE PERFORMANCE OF THE
ELECTRICAL INTERFACE.

PLATING TYPE:

1. MATE FIN 1.27 - 2.54 MICROMETERS THICK
2. MATE FIN 1.27 - 3.81 MICROMETERS THICK
3. GOLD 0.2 MICROMETERS THICK
4. MATE FIN 1.27 - 2.54 MICROMETERS THICK
5. IN. 0.025 DUCTILE NICKEL 2.54 MICROMETER THICK

PLATING TYPE INFORMATION SHOWN ABOVE IS REFERENCE ONLY.
PLATING REQUIREMENTS ARE CONTAINED IN APPLICABLE MATERIAL SPECIFICATION.

[illegible]

	INDICATE FOR ORDER
	PART NUMBER THAT ENTERS CONTACT OF PARTS
	DWG TYPE
	STYLE
	VOLUME 1
	THIS DO NOT AS PARTS TOLERANCE

PROCESS SENSITIVE DIMENSION DIMENSIONS ENCLOSED IN () INDICATE DIMENSIONS AND NO TOLERANCE ARE ESTABLISHED NOMINAL RANGE (MM) CHART D 0 >12 (UNLESS OTHERWISE SPECIFIED) +0.1 +0.2 SINGLE OR TOLERANCE +0.2* 4	ALL DIMENSIONS REFERRED TO THE PR 
--	---

DIMENSIONS ARE IN MILLIMETERS (SEE NOTE 1)		MATERIAL: 1018 STEEL SEE CHART	
DRAWING NAME: TAXI ASM TERM F 1.5		DRAWING NUMBER: 13949867	
RD ANGLE DIRECTION: 	DO NOT SCALE USE MATH DATA  NX	SIZE: A1 X 4 SCALE: 15:1	FRAME NO: 1 OF 2 SHEET NO: 1 OF 2 DATE: 11-13-11

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[13679770](#)