





SYMBOL DEFINITION		MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL ☐ DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	NO MISSING SYMBOL NUMBER	12
	LAST NO. USED		10


DWS STATUS		ZONE		REVISION HISTORY		AUTH		DR	APVD	APVD
DATE	STG	REV	N/P	CHG						
23MY02	R	10	-	-	ALL PARTS - CLEARED REV. COLUMN & REVISED MATERIAL SPECS: 12048074 - UPDATED PDM ATTRIBUTES	222820	HAM	HAM	DLB	
22AU02	R	11	-	-	15366078, 15326396, 15326225, 12160223, 12160222, 12084200 & 12048074 - REVISED MAT'L SIZE AND MAT'L SPEC	211578	ESF	EAR	OMC	
06FE03	R	12	-	-	ALL ACTIVE PARTS- UPDATED PDM ATTRIBUTES	236348	MAC	MAC	JMP	
14OC03	R	13	-	-	15366078 - MAT'L SPEC WAS M3620 HCN4	245588	ADK	TLD	BG	
17FE04	-	14	-	-	12048074, 12084200, 12092702, 12160222, 12160223, 15326225, 15326396 & 15366078 - T.O.D. UPDATED	250621	JS	JS	BG	
19OC04	R	15	-	-	ALL ACTIVE PARTS - ADDED TERMINAL ID NOTE	260108	RTV	JAA	MKW	
09MR06	R	16	-	-	12084200 & 15326396 - UPDATED PDM ATTRIBUTES	276509	JBD	AUG	JES	
24MY06	R	17	-	-	12092702 - OBSOLETE	280889	GLG	JAA	BDO	
16JN06	R	18	-	-	ALL ACTIVE PARTS - PSD WAS #4	281799	JTZ	JVM	BDO	
27JL12	R	19	-	-	12160222-23 - UPDATED MATERIAL CALLOUT AND ADDED TYPE 203	418958	AJP	AJP	MAA	
02JA13	R	20	-	-	12160222-23 - UPDATED PDM ATTRIBUTES	420897	IMF	JAA	MAA	
24JA13	R	21	-	-	12160222-23 - UPDATED PDM ATTRIBUTES	421210	AGC	JAA	MAA	
19FE15	R	22	-	-	12160222-23 - ADDED TARNISH NOTE	428876	JVR	JVM	JSM	
15OC18	R	23	-	-	ALL ACTIVE PARTS - ADDED "SEALED" COLUMN ON CHART	441102	CGD	CGD	LES	
25FE20	R	24	-	-	12160222-23 - UPDATED PDM ATTRIBUTES	551096	J60	JAA	OMS	



TYPE 202
SAME AS TYPE 101
EXCEPT AS SHOWN



TYPE 201



TYPE 203
SAME AS TYPE 202
EXCEPT AS SHOWN

NOTES:

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION.
(SEE MATH MODEL FOR PRECISE DIMENSION)
FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR
TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- RECOMMENDED MATING BLADE - WIDTH : 1.64/1.4
THICKNESS : 0.86/0.79
LENGTH : 7.1/6.9
- "PXX" INDICATES "P" PLUS LAST TWO DIGITS OF MAKE SERIES
NUMBER (P01, P02, P03, ETC).
- DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE
SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN
OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.
- FOR TERMINALS PACKAGED & STORED IN THE APPROVED MANNER,
TARNISH ON SILVER PLATED SURFACES WILL NOT AFFECT THE
PERFORMANCE OF THE PART.

-	-	-	0.254 X 30.96	-	15366078	05	AC	0.254 X 29.8	AU PLATED COPPER ALLOY	1-0.8-0.5	60	2.8-2.03	202	3	X
-	-	-	0.254 X 30.96	-	15326396	03	AD	0.254 X 29.8	AU PLATED COPPER ALLOY	0.5-0.35	21	2.2-1.3	202	2.1	X
-	-	-	0.254 X 30.96	-	15326225	03	AC	0.254 X 29.8	SN PLATED COPPER ALLOY	1-0.8-0.5	60	2.8-2.03	202	3	X
-	-	-	0.254 X 30.96	-	12160223	06	AE	0.254 X 29.8	AG PLATED COPPER ALLOY	1-0.8	17	2.65-1.85	203	3	X
-	-	-	0.254 X 30.96	-	12160222	06	AE	0.254 X 29.8	AG PLATED COPPER ALLOY	0.5-0.35	21	2.2-1.3	203	2.1	X
12092702	03	AB	0.254 X 30.96	METAL COPPER ALLOY	12084200	06	AD	0.254 X 29.8	SN PLATED COPPER ALLOY	0.5-0.35	21	2.2-1.3	202	2.1	X
-	-	-	0.254 X 30.96	-	12059611	C1	-	0.254 X 30.96	SN PLATED COPPER ALLOY	0.35	22	2-1.47	201	2.2	-
12092667	B1	-	0.254 X 30.96	METAL COPPER ALLOY	12048074	11	AC	0.254 X 29.8	SN PLATED COPPER ALLOY	1-0.8-0.5	60	2.8-2.03	202	3	X
PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	PART NO	REV	N/P	MAT'L SIZE	MAT'L SPEC	SIZE (MM²)	ID	DIA	TYPE	G	SEALED
			UNPLATED					PLATED		CABLE					

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING. PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING. CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS. DWS TYPE PART DRAWING STYLE VOLUME (CM³) DISTR CODE D		UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS MODIFIED BY THE 9M GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES AND RELATED DIMENSIONS MUST BE TO THE RIGHT OF THE FEATURE. DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA. ALL DIMENSIONS ARE IN MILLIMETERS REFERENCE THIRD ANGLE PROJECTION DO NOT SCALE USE MATH DATA NX	
---	--	--	--

• APTIV • CONNECTION SYSTEMS WARREN, OH COPYRIGHT 1996 APTIV. ALL RIGHTS RESERVED. THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.							
DR S. LIMON A. FCO. KOPCA T. DUTTLE	DATE 26AU96 26AU96 22OC96						
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001							
MATERIAL SEE CHART							
DRAWING NUMBER 12047884							
SIZE A0	SCALE 10:1	FRAME NO 1 OF 1	SHEET NO 2 OF 2	STG R	REV 24	N/P	-

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[12160222](#)