

MISSING DIMENSIONS AND DETAILS, BASIC APPLICATION  
FEHLENDE MASSE UND ANGABEN SIEHE STANDARD VARIANTE

5.6<sup>+0.1</sup><sub>-0.2</sub>  
4<sup>+0.1</sup><sub>-0.2</sub>  
2.4<sup>+0.2</sup><sub>0</sub>  
L<sub>1</sub>  
L<sub>2</sub>  
MAX. 0.3  
L<sub>max</sub>

H-H ~ 90°  
B<sub>1</sub>  
H<sub>1</sub>  
R<sub>1</sub>

J-J ~ 90°  
B<sub>2</sub>  
H<sub>2</sub>  
R<sub>2</sub>

VIEW OF THE CARRIER STRIP  
IS NOT IN SCALE  
ABBILDUNG DES ANBINDUNGS-  
STREIFENS NICHT MASSTÄBLICH

SLEEVE  
UEBERFEDER  
TERMINAL BODY  
BASISTEIL

PROGRESSION IN THE CRIMP DIE  
TRANSPORTTRICHTUNG IM CRIMPWERKZEUG

Ø 1.52  
SEE CHART  
SIEHE TABELLE

REMARKS / BEMERKUNGEN

- ESPECIAL FOR VERSION sel.Au/GEL:  
IN THE CONTACTAREA, FILLED WITH GEL  
NUR FUER VARIANTE sel.Au/GEL:  
IM KONTAKTIERUNGSBEREICH, MIT GEL GEFUELLT
- OUTER EMBOSMENT ONLY FOR CRIMP SECTION 0.50-0.75  
AUSSENPRÄGUNG NUR FUER CRIMPUERSCHNITT 0.50-0.75
- THIS AREA SELECTIVE AU  
DIESER BEREICH SELEKTIV AU
- SURFACE INDEX, CONTACT AREA  
OBERFLÄCHEN KENNZEICHNUNG, KONTAKTIERUNGSBEREICH
- CRIMP MANUFACTURING PARAMETERS AND TOOLING  
ACCORDING TO DELPHI-SPECIFICATION
- CRIMPVERARBEITUNGSPARAMETER UND WERKZEUGE  
GEMÄSS DELPHI-SPECIFICATION
- COMPANY LABEL  
FIRMENZEICHEN
- DATECODE: WWYY  
DATUMSCODE: WWJJ
- REVISION STATUS OUTSIDE OF ISO CRIMP  
REVISIONSSTAND IM AUSSENBEREICH ISO CRIMP

DIST. CODE  
D

GENERAL TOLERANCES  
ACCORDING TO:  
SEE CHART  
SIEHE TABELLE

SD&T  
ACCORDING TO:  
ISO 1101

REFERENCE  
PART DRAWING

FIRST ANGLE PROJECTION

DO NOT  
SCALE  
USE MATH  
DATA

DIMENSIONAL RANGE (MM)  
NENNMASSENBEREICH (MM)

FROM 0 TO 12  
TOLERANCE (UNLESS OTHERWISE SPECIFIED)  
ALLGEMEINTOLERANZEN

THEORETIC DIM  
TOLERANCE ± 0.2  
WINKEL TOLERANZ ± 2°

DATE: 05.07.07  
BY: M. SACH  
APPROVED: E. CAVASA  
APPROVED: M. SIKORA  
APPROVED: [blank]  
APPROVED: [blank]

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI (10494001)  
POTENTIAL REPAIRABLE, LOW STRENGTH AND RECYCLABLE PART  
GEMESS DELPHI (10494001)

MATERIAL

SEE CHART / SIEHE TABELLE

DRAWING NAME  
MICRO TERMINAL SYSTEM  
PRODUCT GROUP DRAWING, FEMALE TERMINAL

MICRO TERMINAL SYSTEM  
TABELLENZEICHNUNG, STECKHUELSE

DRAWING NUMBER  
13580658

SIZE: A0  
SCALE: 15:1  
FRAME NO: 1 OF 1  
SHEET NO: 1 OF 1  
REV: R 05  
AC

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13580633](#)