






[illegible]

DRAWING NUMBER							
13589458							
SIZE	SCALE	FRAME NO	SHEET NO	STD	REV	N/P	
A1x4	15:1	2 OF 2	1 OF 2	R	22	-	

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISION DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILDS, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
ALL DIMS 0.02
2. "PXX" INDICATES "XX" PLUS LAST TWO DIGITS OF WARE DIE SERIES NUMBER
(P01, P02, P03, ETC.).
3. (11X10.1) CORPORATE BRAND STAMP TO BE LOCATED ON THIS
EXTERIOR SURFACE, VISIBLE TO FINAL ASSEMBLY.
OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE
"P20" OR "P21" LOGO.
4. TERMINAL SYMMETRICAL ABOUT CENTERLINE EXCEPT AS SHOWN.
5. RECOMMENDED MATING BLADE THICKNESS PER USCAR STANDARD EWACAP-001
6. AFTER MANUFACTURE, DO NOT PROBE, TEST, OR OTHERWISE CONTACT THE
INTERIOR REGION (THE SPRING OR ANY MOVING PART) OF THIS TERMINAL.
SEVERE DAMAGE CAN OCCUR, COMPROMISING THE PERFORMANCE OF THE
ELECTRICAL INTERFACE.

[illegible]

ERPLATE	A INDICAT FOR (DR
ERPLATE	PART N THAT P
RS THICK	CONTO OF PAK
RS THICK	DWG TYP
	STYLE
	VOLUME
AL SPECIFICATION.	
	THIS E AS AM TOLER FEATU

PROCESS SENSITIVE DIMENSION		ALL DIMENSIONS ARE IN MILLIMETERS		DRAWING NAME	
DIMENSIONS ENCLOSED IN () INDICATE SENSITIVE DIMENSIONS AND NO TOLERANCE ARE ESTABLISHED		REFERENCE		TAXI ASM TERM F APEX 1.2	
		C18001 1.2 CUST		DRAWING NUMBER	
		THIRD ANGLE PROJECTION		13589458	
DO NOT SCALE		USE MATH DATA		SIZE	
				SCALE	
				15:1	
				FRAME NO	
				1 OF 2	
				SHEET NO	
				1 OF 2	
				REV	
				22	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[13827658](#)