






ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33340130	01	CODE A	ALL PARTS V0 / 26,1
33339571	01	CODE B	
33340234	01	CODE C	
33340235	01	CODE D	
33350122	01	CODE A	ALL PARTS NVO / 25,3
33350276	01	CODE B	
33350334	01	CODE C	
33350335	01	CODE D	

POSITION	1		2								3	4		5	
NAME	HOUSING		INSERT								HOUSING SEAL	SECONDARY LOCK		SLIDER	
MATERIAL	PBT GF30 FR17	PBT GF30	PBT GF30 FR17				PBT GF30				LSR 50 SHORE	PBT GF30 FR17	PBT GF30	PBT GF30 FR17	PBT GF30
COLOR:	BLACK	BLACK	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	REDDISH-BROWN	ORANGE	YELLOW	ORANGE	YELLOW
PART-NO.:	33338835	33349754	33338899	33338897	33338900	33338903	33350053	33350055	33350054	33349767	33339449	33338904	33350081	33338837	33350047
-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
-	1	-	1	-	-	-	-	-	-	-	1	1	-	1	-
-	1	-	-	1	-	-	-	-	-	-	1	1	-	1	-
-	1	-	-	-	1	-	-	-	-	-	1	1	-	1	-
-	1	-	-	-	-	1	-	-	-	-	1	1	-	1	-
-	-	1	-	-	-	-	1	-	-	-	1	-	1	-	1
-	-	1	-	-	-	-	-	1	-	-	1	-	1	-	1
-	-	1	-	-	-	-	-	-	1	-	1	-	1	-	1
-	-	1	-	-	-	-	-	-	-	1	1	-	1	-	1

DWG STATUS					ZONE	REVISION HISTORY			AUTH	DR	APVD 1	APVD 2	
DATE	STG	REV	N/P	CHG									
15MR19	R	01				INITIAL RELEASE					K.FAR	P.NAJ	M.GRU
11FE20	R	01	AA		G11 A7	PART AVAILABILITY FOR PART NUMBERS 33350122, 33350276, 33350334, 33350335 UPDATED NOTES UPDATED					P.NAJ	M.GRU	



NOTES	
-	ON MAIN VIEW ASSEMBLY 33340130 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK AND SLIDER IN OPEN POSITION
ASSEMBLY INSTRUCTION NO.:	
35269106-CUS71 - PRELIMINARY ASSEMBLY	
35269106-CUS72 - HARNESS ASSEMBLY	
35269103-CUS73 - CAR ASSEMBLY	
35269102-CUS73 - CAR ASSEMBLY	
MATING PARTS:	
- 12 WAY 1.5 MALE PANEL MOUNT ASM DWG-NO.: 35123474	
- BACKSHELL 90 DEG APTIV DWG-NO.: 33390631 (HT DWG-NO.: 17-2276-001-CS6)	
- BACKSHELL 180 DEG APTIV DWG-NO.: 33390632 (HT DWG-NO.: 17-1486-001-CS6)	
- PROTECTION CAP APTIV DWG-NO.: 35149888 (HT DWG-NO.: 17-2267-001-CS6)	
MATING TERMINAL SYSTEM:	
- 1.5 TERMINAL DWG-NO.: 15432214	
MAX WIRE CROSS SECTION: 1.0MM ²	
RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1.5MM ² - USE COMBINATION:	
TE TERMINAL: MCP 1.5, DWG NO.: 1418884-3	
SEAL: 964972-1	
MAX INSULATION CRIMP DIMENSIONS:	
HEIGHT: 3.40; WIDTH: 3.30	
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	TOOL CAVITY NUMBER
4	PART CAVITY NUMBER
5	MOVING DISTANCE OF SECONDARY LOCK
6	MOVING DISTANCE OF SLIDER

DIM TO CHECK	DIMENSIONAL RANGE (MM)					TOLERANCE UNLESS OTHERWISE SPECIFIED					CHART E1
	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	
1) DIM FOR HELP		20	30	70	100	150	200	250	300	400	
THEORETIC DIM	TOLERANCE UNLESS OTHERWISE SPECIFIED										
		+0.15	+0.2	+0.3	+0.4	+0.5	+0.6	+0.8	+1	+1.2	
	ANGULAR TOLERANCE ±2°										

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33340130](#)