



ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT	-	---	---	---	---	---	---	---	---	---	---	---	---	---	---
33342277	01	CODE A	ALL PARTS VO / 34,0	-	1	---	1	---	---	---	---	---	---	1	1	---	1	---
33342279	01	CODE B		-	1	---	---	1	---	---	---	---	---	1	1	---	1	---
33342280	01	CODE C		-	1	---	---	---	1	---	---	---	---	1	1	---	1	---
33342281	01	CODE D		-	1	---	---	---	---	1	---	---	---	1	1	---	1	---
33347876	01	CODE A	ALL PARTS NVO / 33,0	-	---	1	---	---	---	1	---	---	---	1	---	1	---	1
33347893	01	CODE B		-	---	1	---	---	---	---	1	---	---	1	---	1	---	1
33348731	01	CODE C		-	---	1	---	---	---	---	---	1	---	1	---	1	---	1
33348732	01	CODE D		-	---	1	---	---	---	---	---	---	1	1	---	1	---	1



NOTES					
- ON MAIN VIEW ASSEMBLY 33342277 SHOWN (CODE A)					
- DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK AND SLIDER IN OPEN POSITION					
ASSEMBLY INSTRUCTION NO.:					
35269106-CUS71 - PRELIMINARY ASSEMBLY					
35269106-CUS72 - HARNESS ASSEMBLY					
35269103-CUS73 - CAR ASSEMBLY					
35269102-CUS73 - CAR ASSEMBLY					
MATING PARTS:					
- 18 WAY 1.5 MALE PANEL MOUNT ASM DWG-NO.: 35195557					
- 18 WAY 1.5 MALE STRAP MOUNT ASM DWG-NO.: 35195558					
- BACKSHELL 90 DEG APTIV DWG-NO.: 35024552					
- (HT DWG-NO.: 17-2277-001-CSG)					
- BACKSHELL 180 DEG APTIV DWG-NO.: 35024553					
- (HT DWG-NO.: 17-1491-001-CSG)					
- PROTECTION CAP APTIV DWG-NO.: 35149890					
- (HT DWG-NO.: 17-2268-001-CSG)					
MATING TERMINAL SYSTEM:					
- 1.5 TERMINAL DWG-NO.: 15432214					
MAX WIRE CROSS SECTION: 1.0MM²					
RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE					
- CROSS SECTION 1.5MM² - USE COMBINATION:					
TE TERMINAL: MCP 1.5, DWG NO.: 1418884-3					
SEAL: 964972-1					
MAX INSULATION CRIMP DIMENSIONS:					
HEIGHT: 3.40; WIDTH: 3.30					
1	APTIV LOGO				
2	MATERIAL NAME ACCORDING TO VDA 260				
3	TOOL CAVITY NUMBER				
4	PART CAVITY NUMBER				
5	MOVING DISTANCE OF SECONDARY LOCK				
6	MOVING DISTANCE OF SLIDER				

○ DIM TO CHECK	DIMENSIONAL RANGE (MM)	CHART E1
FROM	> 0	> 20
TO	> 20	> 30
	> 30	> 70
	> 70	> 100
	> 100	> 150
	> 150	> 200
	> 200	> 250
	> 250	> 300
	> 300	> 400
1) DIM FOR HELP	TOLERANCE UNLESS OTHERWISE SPECIFIED	
	±0.15	±0.2
	±0.3	±0.4
	±0.5	±0.6
	±0.8	±1
	±1.2	±1.2
□ THEORETIC DIM	ANGULAR TOLERANCE ±2°	

DWG STATUS

DATE	STG	REV	N/P	CHG	ZONE
28NO18	R	01			
15MR19	R	01	AA		B6
27OC20	R	01	AB		G11 B6

REVISION HISTORY

AUTH	DR	APVD 1	APVD 2
		A.RAJ	P.NAJ
		M.GRU	K.PIT
		P.NAJ	M.GRU

SCALE: 1:1

DWG TYP

PART DRAWING

WEIGHT (GR)

SEE CHART

VOLUME (CM³)

ROUTING

DISTR CODE

D

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES ACCORDING TO:

SEE CHART

GD&T ACCORDING TO:

ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

• APTIV •

CONNECTION SYSTEMS

KRAKOW, POLAND

COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WŁASNOŚCIĄ APTIV I ZAWIERA POUFNE INFORMACJE POWIELANE, ROZPOWŚIECZANE I WYKORZYSTYWANE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANE INNYM JAKIEKOLWIEK ICH ZAWARTOŚCI, BEZ NADANIA WYRAŹNYCH UPRAWNIEN, JEST ZABRONIONE.

DR	A.RAJEEV	DATE	27NO18
APVD1	P.NAJDUCH		28NO18
APVD2	M.GRUDZEWSKI		29NO18
APVD3			
APVD4			
APVD5			

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001 SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIIE PRZETWORZONE OKREŚLA APTIV 10949001

MATERIAL

SEE CHART

DRAWING NAME

18 WAY 1.5 CTCS FEMALE ASSEMBLY

DRAWING NUMBER

35195559

SIZE	A1	SCALE	2:1	FRAME NO	1 OF 1	SHEET NO	1 OF 1	STG	R	REV	01	N/P	AB
------	----	-------	-----	----------	--------	----------	--------	-----	---	-----	----	-----	----

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33342279](#)