






MISSING SYMBOLS	DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APPD	APPCV
	DATE	STG	REV	N/P	CHG						
4 6 9	14JAO0	R	001	-	-		CLEARED REV COLUMN; ALL ACTIVE PARTS- UPDATED PDM ATTRIBUTES	196648	CRW	G61	LLD
	17JL00	R	002	-	-		REINSTATE 12077412	000010	J1B	J1B	J1A
	150C04	R	03	-	-		ALL ACTIVE PARTS - ADDED TERMINAL ID NOTE	260003	RJV	WM	WMK
	24FE05	R	04	-	-		ALL ACTIVE PARTS - REVISED MAT'L SPEC & DRAWING NAME	265136	J5	J5	J5
	18MY05	R	05	-	-		12176389 - UPDATED PDM ATTRIBUTES	268280	JBD	FKV	MTM
	30SE05	R	06	-	-		12077411, 12077413, 12084201, 12129493 & 12176392 - UPDATED PDM ATTRIBUTES; 12077411 - ADDED 1.0 MM# 6; ALL ACTIVE PARTS - ADDED NOTE# 6	272905	JTV	AVS	WTM
	11JAO8	R	07	-	-		ALL PARTS - 2X 5 +-0.15 TYP WAS 2X 5 +-0.01 TYP	403419	WHC	WHC	WTM
	18FE15	R	08	-	-		33231919 - RELEASED AND 12176387-90 - ADDED TARNISH NOTE	428904	NRW	JVM	D5
	18SE15	R	09	-	-		33231919 - DIM 19.95 +-0.4 WAS 19.95 +-0.15 / -0.4 AND UPDATED PART AVAILABILITY	430685	LES	LES	MJD
	22MY19	R	10	-	-		12176387 - 3 WAS 5 ON SIZE (MM#) COLUMN	443374	LVD	J1E	J1E



TYPE 101

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. R 0.4 PERMISSIBLE ON ALL "SHARP" CORNERS.
3. RECOMMENDED MATING BLADE 2.8 X 0.81.
4. TERMINALS TO CRIMP AROUND AND RETAIN CAVITY SEAL 12015323 OR EQUIVALENT.
5. "PXX" INDICATES "P" PLUS LAST TWO DIGITS OF MAKE SERIES NUMBER (P01, P02, P03, ETC.).
6. DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.
7. FOR TERMINALS PACKAGED & STORED IN THE APPROVED MANNER, TARNISH ON SILVER PLATED SURFACES WILL NOT AFFECT THE PERFORMANCE OF THE PART.

-	-	0.406 X 30.56	-	-	12176390	A8	-	AG PLATED COPPER ALLOY	0.35-0.5	0.35-0.5	21	I03	2.4±0.2	19.95 +0.15/-0.4
-	-	0.406 X 30.56	-	-	12176389	A9	-	AG PLATED COPPER ALLOY	0.8-1	2.03-3.12	19	I01	3.2±0.4	19.95 +0.15/-0.4
-	-	0.406 X 30.56	-	-	33231919	01	AA	AG PLATED COPPER ALLOY	1-2	2.48-3.05	15	I03	3.7±0.4	19.95 +0.4
-	-	0.406 X 30.56	-	-	12176388	A8	-	AG PLATED COPPER ALLOY	2-3	2.45-3.80	13	I03	4±0.4	19.95 +0.15/-0.4
-	-	0.406 X 30.56	-	-	12176387	A9	-	AG PLATED COPPER ALLOY	3	3.49-3.65	12	I03	4.6±0.4	19.95 +0.15/-0.4
-	-	0.406 X 30.56	-	-	12129493	C8	-	TIN PLATED COPPER ALLOY	2-3	2.45-3.80	13	I03	4±0.4	19.95 +0.15/-0.4
-	-	0.406 X 30.56	-	-	12084201	E11	-	TIN PLATED COPPER ALLOY	0.35-0.5	1.84-2.51	21	I01	2.4±0.2	19.95 +0.15/-0.4
-	-	0.406 X 30.56	-	-	12077413	E11	-	TIN PLATED COPPER ALLOY	3	3.49-3.65	12	I03	4.6±0.4	19.95 +0.15/-0.4
-	-	0.406 X 30.56	-	-	12077412	E9	-	TIN PLATED COPPER ALLOY	1-2	2.48-3.05	15	I03	3.7±0.4	19.95 +0.15/-0.4
-	-	0.406 X 30.56	-	-	12077411	E11	-	TIN PLATED COPPER ALLOY	0.5-0.8+1.0	2.03-3.12	19	I01	3.2±0.4	19.95 +0.15/-0.4
-	-	0.406 X 32.54	-	-	12045639	D8	-	P1519027 425 TIN BRS EX HD SN PLTD	3	3.49-3.65	12	I02	4.6±0.4	19.95 +0.15/-0.4
-	-	0.406 X 32.54	-	-	12034454	F8	-	P1519027 425 TIN BRS EX HD SN PLTD	1-2	2.48-3.05	15	I02	3.7±0.4	19.95 +0.15/-0.4
-	-	0.406 X 32.54	-	-	12020648	H8	-	P1519027 425 TIN BRS EX HD SN PLTD	0.5-0.8	2.03-3.12	19	I01	3.2±0.4	19.95 +0.15/-0.4
PART	NO	REV	MAT'L SIZE	SPEC	PART NO	REV	N/P	MAT'L SPEC	SIZE (MM ²)	DIA	ID	TYPE	E	U
UNPLATED					PLATED					CABLE				

1 PROCESS SENSITIVE DIMENSION UNIMPROVED FINISHES IN 10 INDICATE REFERENCE DIMENSIONS AND 10 TOLERANCE LIMITS ARE ESTABLISHED TOLERANCE UNLESS OTHERWISE SPECIFIED DIMENSIONAL RANGE (MM) CHART D <table style="width: 100%; border-collapse: collapse;"> <tr> <td style="width: 33%; text-align: center;">FROM 0</td> <td style="width: 33%; text-align: center;">12</td> <td style="width: 33%; text-align: center;">> 12</td> </tr> <tr> <td style="text-align: center;">10/12</td> <td style="text-align: center;">10/12</td> <td style="text-align: center;">10/12</td> </tr> </table> ANGLE AND TOLERANCE 10°	FROM 0	12	> 12	10/12	10/12	10/12	LINE BREAKS THROUGH A PART NUMBER INDICATE THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING. PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING. CONTACT APPLIC SALES TO ASSURE AVAILABILITY OF PARTS. DWG TYPE PART DRAWING STYLE VOLUME (COP) D DISTR CODE UNLESS OTHERWISE SPECIFIED THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-1994 AS MODIFIED BY THE 2003 SUPPLEMENT TO DIMENSIONING AND TOLERANCING ADDENDUM 2001. SEPARATE PATTERNS OF FEATURES MAY BE ORDERED INDEPENDENTLY, REGARDLESS OF DATUM REFERENCES. ALL DIMENSIONS ARE IN MILLIMETERS REFERENCE THIRD ANGLE PROJECTION  DO NOT SCALE USE MATH DATA  NX
FROM 0	12	> 12					
10/12	10/12	10/12					

• APTIV • CONNECTION SYSTEMS WAREN, OH COPYRIGHT 1998 APTIV. ALL RIGHTS RESERVED. THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.									
DRAWING NUMBER					DATE				
DP1	APV01 JORGE IBARRA				29MY98				
APV02	OSCAR OCHOA				02JN98				
APV03	O. GALLEGOS				16JUL98				
APV04									
APV05	SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001								
MATERIAL SPEC SHEET									
DRAWING NAME									
TAXI TERM F M/P 280 SEALED									
DRAWING NUMBER									
12089195									
SIZE	SCALE	FRAME NO	SHEET NO	STO	REV	REV	REV	REV	REV
A0	1:1	1 OF 1	1 OF 1	R	10				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[12176388](#)