



ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33253554	01	CODE A	ALL PARTS VO / 11.3
33253557	01	CODE B	
33253560	01	CODE C	
33253563	01	CODE D	
33344639	01	CODE A	ALL PARTS NVO / 11.0
33344649	01	CODE B	
33344650	01	CODE C	
33344652	01	CODE D	

POSITION	1		2								3	4		5	
NAME	HOUSING		INSERT								HOUSING SEAL	SECONDARY LOCK		SLIDER	
MATERIAL	PBT GF30 FR17	PBT GF30	PBT GF30 FR17				PBT GF30				LSR 50 SHORE	PBT GF30 FR17	PBT GF30	PBT GF30 FR17	PBT GF30
COLOR:	BLACK	BLACK	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	REDDISH-BROWN	ORANGE	YELLOW	ORANGE	YELLOW
PART-NO.:	33248746	33343693	33249041	33249040	33249038	33249031	33344027	33344030	33344031	33344032	33248811	33248653	33343690	33248753	33343694
-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
-	1	-	1	-	-	-	-	-	-	-	1	1	-	1	-
-	1	-	-	1	-	-	-	-	-	-	1	1	-	1	-
-	1	-	-	-	1	-	-	-	-	-	1	1	-	1	-
-	1	-	-	-	-	1	-	-	-	-	1	1	-	1	-
-	-	1	-	-	-	-	1	-	-	-	1	-	1	-	1
-	-	1	-	-	-	-	-	1	-	-	1	-	1	-	1
-	-	1	-	-	-	-	-	-	1	-	1	-	1	-	1
-	-	1	-	-	-	-	-	-	-	1	1	-	1	-	1


DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
250C18	R	01				INITIAL RELEASE		K.FAR	P.NAJ	M.GRU
14MR19	R	01	AA		B7	REFERENCE HELLERMANN TYTON DWG-NO. ADDED		K.FAR	M.GRU	K.PIT
300C19	R	01	AB		G11	PART AVAILABILITY FOR PART NUMBERS 33344639, 33344649, 33344650, 33344652 UPDATED		P.NAJ	M.GRU	
280C20	R	01	AC		B7	HT DWG-NO: 18-0195-001-CSG WAS 17-0195-001-CSG		P.NAJ	M.GRU	




CODE A



CODE B




CODE C




CODE C



CODE D




CODE D



CODE D

NOTES	
-	ON MAIN VIEW ASSEMBLY 33253554 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK AND SLIDER IN OPEN POSITION
-	ASSEMBLY INSTRUCTION NO.: 35269106-CUS71 - PRELIMINARY ASSEMBLY 35269106-CUS72 - HARNESS ASSEMBLY 35269103-CUS73 - CAR ASSEMBLY 35269102-CUS73 - CAR ASSEMBLY
-	MATING PARTS: - 2 WAY 2.8 MALE PANEL MOUNT ASM DWG-NO.: 33254106 - BACKSHELL 90 DEG APTIV DWG-NO.: 33365444 (HT DWG-NO.: 17-2274-001-CSG) - BACKSHELL 180 DEG APTIV DWG-NO.: 33365244 (HT DWG-NO.: 17-1454-001-CSG) - ROTARY BACKSHELL 90 DEG APTIV DWG-NO.: 35024558 (HT DWG-NO.: 18-0195-001-CSG) - ROTARY BACKSHELL 180 DEG APTIV DWG-NO.: 35024559 (HT DWG-NO.: 17-0598-001-CSG) - PROTECTION CAP APTIV DWG-NO.: 35149887 (HT DWG-NO.: 17-2264-001-CSG)
-	MATING TERMINAL SYSTEM: - 2.8 TERMINAL DWG-NO.: 15446676 MAX WIRE CROSS SECTION: 2.5MM ²
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	TOOL CAVITY NUMBER
4	PART CAVITY NUMBER
5	MOVING DISTANCE OF SECONDARY LOCK
6	MOVING DISTANCE OF SLIDER



NOTE 1

NOTE 2

NOTE 3


NOTE 4

NOTE 5

NOTE 6

DIM TO CHECK		DIMENSIONAL RANGE (MM)															
FROM	TO	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	TOLERANCE UNLESS OTHERWISE SPECIFIED					
1	1	±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	±1.5	ANGULAR TOLERANCE ±2°					

SCALE:
1:1



• APTIV •

CONNECTION SYSTEMS
KRAKOW, POLAND

COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WLASNOSCIA APTIV I ZAWIERA POUFNE INFORMACJE. POWIELANIE, ROZPOWISZCZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIAZANYCH Z NIM DANYCH CAD, JAK ROWNIEZ PRZEKAZYWANIE INNYM JAKIEKOLWIEK ICH ZAWARTOSCI BEZ NADANIA WYRAZNYCH UPRAWNIEN, JEST ZABRONIONE.

DR	K.FARON	DATE	240C18
APVD1	P.NAJDUCH	250C18	
APVD2	M.GRUDZEWSKI	260C18	
APVD3			
APVD4			
APVD5			

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTORNIE PRZETWORZONE OKRESLA APTIV 10949001

SEE CHART

2 WAY 2.8
CTCS FEMALE ASSEMBLY

DRAWING NUMBER											
33253564											
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P					
A1	2:1	1 OF 1	1 OF 1	R	01	AC					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33253557](#)