



- | | | | | | | | | | | | | | | | | | |
|--|---|-----------|-------|-----------|-------|-----------|-------|-----|-----|------|-----|---|---|---|---|---|---|
| <p>A. PHYSICAL PARTS THROUGH PART NUMBER
 INDICATE WHICH PHYSICAL PARTS ARE NOT AVAILABLE
 PART NUMBERS THAT DO NOT HAVE A LIFETIME INDIcate THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.
 NOTE: APPLICABLE PARTS TO ASSEMBLY AVAILABLE, IF PARTS.</p> <p>NEW TYPE PART DRAWING</p> <p>TITLE</p> <p>VOLUME (OF) DIST. CODE</p> <p style="text-align: center;">UNLESS OTHERWISE SPECIFIED
 THIS DOCUMENT IS IN ACCORDANCE WITH ANSI Z39.18-1994
 PERMANENT PAPER REQUIREMENTS FOR THE PRODUCTION OF
 ELECTRONIC DRAWINGS. UNLESS OTHERWISE SPECIFIED, ALL
 DIMENSIONS ARE TO BE GAUGED SEPARATELY REGARDLESS OF DATA
 REPRESENTATION.</p> <p>ALL DIMENSIONS ARE IN MILLIMETERS</p> <p>REFERENCE:</p> <p>DATE: NO. OF TOLERANCE</p> <p>THIRD ANGLE PROJECTION DO NOT SCALE</p> <p>USE MATH DATA</p> <p style="text-align: right;">NX</p> | <p style="text-align: center; font-size: 2em; font-weight: bold;">•APTIV•</p> <p style="text-align: center;">CONNECTION SYSTEMS</p> <p style="text-align: center;">KARNOW, CH
 COPYRIGHT (1999) APTIV, ALL RIGHTS RESERVED.</p> <p>THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS AN
 CONFIDENTIAL INFORMATION AND IS TO BE USED FOR THE
 APPLICATION OF THE PRODUCT ONLY. IT IS NOT TO BE
 AS COMMUNICATION OF ANY MANNER TO OTHERS WITHOUT EXPRESS
 AUTHORIZATION. IT IS TO BE KEPT.</p> <p style="text-align: right;">DATE</p> <p>DR</p> <p>APPROV. J. BARKNICK 0256999</p> <p>APPROV. J. BARKNICK 0256999</p> <p>APPROV. J. SVETI 0356999</p> <p>APPROV. 0356999</p> <p>APPROV. 0356999</p> <p style="text-align: center;">SUBS (ANCES OF CONCEPT AND RECYCLED
 CONTENT) (SEE APTIV.COM) (APPROVED)</p> <p style="text-align: center;">SEE DRAWING</p> <p>DRAWING NUMBER</p> <p style="text-align: center; font-size: 3em; font-weight: bold;">5326694</p> <table border="1" style="width: 100%; border-collapse: collapse; text-align: center;"> <tr> <td style="width: 10%;">SIZE</td> <td style="width: 10%;">SCALE</td> <td style="width: 10%;">FRAME NO.</td> <td style="width: 10%;">DWT</td> <td style="width: 10%;">SHEET NO.</td> <td style="width: 10%;">SHEET</td> <td style="width: 10%;">REV</td> <td style="width: 10%;">REV</td> </tr> <tr> <td>A1X3</td> <td>1:1</td> <td>1</td> <td>0</td> <td>2</td> <td>1</td> <td>0</td> <td>1</td> </tr> </table> | SIZE | SCALE | FRAME NO. | DWT | SHEET NO. | SHEET | REV | REV | A1X3 | 1:1 | 1 | 0 | 2 | 1 | 0 | 1 |
| SIZE | SCALE | FRAME NO. | DWT | SHEET NO. | SHEET | REV | REV | | | | | | | | | | |
| A1X3 | 1:1 | 1 | 0 | 2 | 1 | 0 | 1 | | | | | | | | | | |

DRAWING NUMBER							
15326694							
SIZE	SCALE	FRAME NO	SHEET NO	STD	REV	N/P	
A1x3	5:1	2 OF 2	1 OF 2	R	31	-	

DIMENSIONAL RANGE (MM)		CHART	
FROM	TO		
> 0	> 20	> 30	> 100
> 20	> 30	> 100	> 150
		> 150	> 250
		> 250	> 300
TOLERANCE UNLESS OTHERWISE SPECIFIED			
+0.15	+0.2	+0.3	+0.4
		+0.5	+0.6
		+0.8	+1
ANGULAR TOLERANCE 12°			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[15326631](#)