






- ## NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. RECOMMENDED MATING BLADE THICKNESS 0.6 ± 0.03 MM OR 0.64 ± 0.03 MM
RECOMMENDED MATING BLADE WIDTH NOT TO EXCEED 1.2 MM
AND NO LESS THAN 0.61 MM.

3. MAXIMUM CURRENT CAPACITY IS 10 AMPS WITH 0.8 MM² COPPER CABLE.

4. CRIMP DIMENSION FROM THE BACK OF THE CORE WING (INCLUDES THE

- FLARE OUT FROM THE CORE WING) TO THE END OF THE INSULATION WING.



- 2.05 MM MAX WIDTH, 2.1 MM MAX HEIGHT FOR CABLE SIZE UP TO 1.9 MM
2.35 MM MAX WIDTH, 2.40 MM MAX HEIGHT FOR CABLE SIZE BETWEEN 1.8
2.67 MM MAX WIDTH, 2.67 MM MAX HEIGHT FOR CABLE SIZE BETWEEN 2.2

5. * DENOTES DIMENSIONS MADE AT CUT-OFF & CRIMP DIE.

6. PLUS ANGLE IS WING BOTTOM SURFACE ROTATED COUNTERCLOCKWISE AGAINST THE BOX BOTTOM SURFACE.

SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	21
	LAST NO. USED	19

MISSING SYMBOLS		DWG STATUS						ZONE	REVISION HISTORY	AUTH	DR	APVD	KFVQ	1	2
		DATE	STG	REV	N/P	CHG									
	1	7	18												
		28F19	R	01	-	-		ALL PARTS - RELEASED PART DRAWING	442472	LVD	RBS	OMS			
		26A19	R	02	-	-		3502397-98 - UPDATED PART AVAILABILITY	443031	JLL	JAA	OMS			
		17JN19	R	03	-	-		35027396 - UPDATED PART AVAILABILITY	43686H	GDB	JAA	OMS			
		29N019	R	04	-	-		35027396 - SIZE WAS 0.35-0.5 & DIA WAS 1.47-1.9; 35410017 - RELEASED	550373	JLL	JAA	OMS			
		06A1020	R	05	-	-		ALL PARTS - REMOVED CROSS HATCH TEXTURE & DIM #18 AND REVISED DIM #17	552177	EVV	EVV	RBS			
		29JN21	R	06	-	-		35410017 - UPDATED PART AVAILABILITY	556469	AGC	AGC	OMS			

REFERENCE	
THIRD ANGLE PROJECTION 	DO NOT SCALE USE MATH DATA 

• APTIV • CONNECTION SYSTEMS WARREN, OH COPYRIGHT 2019 APTIV, ALL RIGHTS RESERVED. THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.									
								DATE	
DR	APV01 LUIS VILLARREAL								28FE19
APV02	ROBERT B SNADER								01MR19
APV03	ROBERT B SNADER								01MR19
APV04									
APV05	SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 104949001								
MATERIAL SEE CHART									
DRAWING NAME TAXI TERM F OCS 1.2									
DRAWING NUMBER 13543112									
SIZE	SCALE	FRAME	1	SHEET	NO	STO	REV	N/P	
A0	10:1	1	OF	10	OF	R	06		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35072396](#)