










		6		5		4						
G ± 0.05	RECOMMENDED APPLICATION MILE BLADE THICKNESS EMPHÖHLE STIFT DICKE	MATERIAL	SURFACE OBERFLÄCHE	CROSS- SECTION QUERSCH. mm²	R	CRIMP TYPE	TERMINAL AND KONTAKT FIDELINUM.	PART REV	DATE DATUM	WEIGHT MASSE G	SEALED UNGESEALED	
0.2 MM	0.8 MM	CUNISI C19002 / C19100	FSN	150	1.45 ^{+0.3} _{-0.2}	2	13544.265	02	01A0U7	0.30	US	
				0.75 - 1.00	1.45 ^{+0.3} _{-0.2}	2	13544.265	02	01A0U7	0.28	US	
				0.35 - 0.50	1.45 ^{+0.3} _{-0.2}	2	13544.261	02	01A0U7	0.27	US	
			CUFE2P C19400	AU	150	1.45 ^{+0.3} _{-0.2}	2	15346006	02	01A0U7	0.30	US
					0.75 - 1.00	1.45 ^{+0.3} _{-0.2}	2	15345998	02	01A0U7	0.28	US
					0.35 - 0.50	1.45 ^{+0.3} _{-0.2}	2	15345992	02	01A0U7	0.27	US
		CUFE2P C19400		FSN	0.13	1.45 ^{+0.3} _{-0.2}	3	13976948	01	02A2U2	0.25	US
					0.13	1.45 ^{+0.3} _{-0.2}	3	13987183	01	02A2U2	0.26	S
					150	1.45 ^{+0.3} _{-0.2}	2	15346002	02	01A0U7	0.30	US
			CUFE2P C19400	FSN	0.75 - 1.00	1.45 ^{+0.3} _{-0.2}	2	15345994	02	01A0U7	0.28	US
					0.35 - 0.50	1.45 ^{+0.3} _{-0.2}	2	15345988	02	01A0U7	0.27	US
					2x0.35/ 2x0.50	1.45 ^{+0.3} _{-0.2}	1	15346009	02	01A0U7	0.29	US
CUFE2P C19400	FSN	0.13		1.45 ^{+0.3} _{-0.2}	3	13975445	01	25.4.12	0.25	US		
		0.13		1.45 ^{+0.3} _{-0.2}	3	13987178	01	28SE12	0.26	S		
		0.50 - 1.00		1.4 ^{+0.3} _{-0.2}	2	13720177	01	14A008	0.28	US		
	CUFE2P C19400	AU	0.20 - 0.35	1.4 ^{+0.3} _{-0.2}	2	13720176	01	14A008	0.27	US		
			0.50 - 1.00	1.4 ^{+0.3} _{-0.2}	2	13720178	01	14A008	0.28	US		
			0.20 - 0.35	1.4 ^{+0.3} _{-0.2}	2	13720181	01	14A008	0.27	US		
CUFE2P C19400		FSN	150	1.4 ^{+0.3} _{-0.2}	2	15153885	03	01A0U7	0.30	US		
			0.75 - 1.00	1.4 ^{+0.3} _{-0.2}	2	15414401	03	01A0U7	0.28	US		
			0.35 - 0.50	1.4 ^{+0.3} _{-0.2}	2	15414399	03	01A0U7	0.27	US		
	CUFE2P C19400	AU	0.13	1.4 ^{+0.3} _{-0.2}	3	13973666	01	02A2U2	0.25	US		
			0.13	1.4 ^{+0.3} _{-0.2}	3	13988120	01	28SE12	0.26	S		
			150	1.4 ^{+0.3} _{-0.2}	2	15457989	03	01A0U7	0.30	US		
CUFE2P C19400		FSN	0.75 - 1.00	1.4 ^{+0.3} _{-0.2}	2	15396705	04	01A0U7	0.28	US		
			0.35 - 0.50	1.4 ^{+0.3} _{-0.2}	2	15396704	04	01A0U7	0.27	US		
			2x0.35/ 2x0.50	1.4 ^{+0.3} _{-0.2}	1	15396706	04	01A0U7	0.29	US		
	CUFE2P C19400	FSN	0.13	1.4 ^{+0.3} _{-0.2}	3	13804.118	01	22A2P10	0.25	US		
			0.13	1.4 ^{+0.3} _{-0.2}	3	13987171	01	28SE12	0.26	S		

	J
	H
	G
	F
	E



TERMINALS TO BE SUPPLIED WOUND AS SHOWN
LIEFERZUSTAND SPULRICHTUNG

NOTES:
BEMERKUNG:

ENGAGE FOR
STECKKRAFT

ENGAGE FORCE: WITH GAPSIZE 0.2±0.05MM CHECKED WITH GAUGE PART-NO.: 10757844
STECKKRAFT : MIT SPALTMASS 0.2±0.05MM GEMESSEN MIT LEHRE PART-NO.: 10757844

PERMISSIBLE DISASSEMBLING TOOL PART-NO.:
ZULAESSIGES ENTRIEGELUNGSWERKZEUG PART-NO.:

CRIMP MANUFACTURING PARAMETERS AND TOOLING ACCORDING TO DELPHI-SPECIFICATION

CRIMPVERARBEITUNGSPARAMETER UND WERKZEUGE
GEMAESS DELPHI-SPECIFICATION

SLEEVE MATERIAL: X10CRNi188, SAE 301, DIN EN 105
UEBERFEDER MATERIAL: X10CRNi188, SAE 301, DIN EN 105

RETENTION FORCE SPRING TO BODY IN WITHDRAWAL DIRECT MINIMUM 110N.
REFER TO ESD# S1044201 FOR PULL TEST GEOMETRY.

HALTEKRAFT FEDER AN KONTAKTTEIL IN WIEDERRUF UNMITTELBAR MIN. 110N
SIEHE ESD# S1044201 FUER PULL TEST GEOMETRIE.

• A P T I V •									
CONNECTION SYSTEMS D-42119 WUPPERTAL									
COPYRIGHT 2007 APTIV ALL RIGHTS RESERVED.									
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED DATA, AS WELL AS COMMUNICATION OF THIS INFORMATION, IS PROHIBITED WITHOUT AUTHORIZATION. IS PROHIBITED.									
DIESE ZEICHNUNG IST EIGENTUM DER FIRMA APTIV UND ENTHÄLT APTIV VERTRAULICHE INFORMATIONEN DER REPRODUKTION, VERTEILUNG UND NUTZUNG DES DOKUMENTS ODER DESER ZUGESCHRIEBEN GUT DADEN ODER AUCH ALS KOMMUNIKATION VON BELIEBIGER INHALT ZU ANDEREN, IST OHNE BERECHTIGUNGSPERSONEN DURCH DIE APTIV UNZULASSIG.									
DR _____		DATE _____							
APV01 WIRTH		22NOV01							
APV02 CVASA		22NOV01							
APV02 WISNIEWSKI		11NOV01							
APV03 _____									
APV04 _____									
APV05 _____									
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10490001 POTENTIAL HAZARDOUS: NONE STORPE AND RECYCLINGWASTEL GEWISSAP APTIV 10490001									
MATERIAL _____		SEE CHART							
(DRAWING NAME)									
DSO 1.50 TERMINAL UNSEALED ; SEALED DSO 1.50 KONTAKT UNGEDICHTET ; GEDICHTET									
(DRAWING NUMBER)									
15396741									
SIZE A0 SCALE 1:1 FRAME NO 1 SHEET NO 1 OF 1 STG R REV R KOP AL									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15457989](#)