


















TYPE 1




TYPE II



NOTES	
1	NOT DIMENSIONED GEOMETRY HAS TO BE TAKEN FROM THE CORRESPONDING 3D DATA FILE
2	MATERIAL SPECIFICATION: SILICONE, AUTOLUBRICATION
3	TENSILE STRENGTH : RM MIN 6.2 N/MM ²
4	ELONGATION : 375% DIN 53504-S2
5	DUROMETER ORIGINAL: SHORE (A) 50±5 DIN53505
6	MEASURE ON TEST SLABS

SCALE
2:1



DWG TYPE PART DRAWING		DISTR CODE D
WEIGHT (GRI)		
VOLUME (CM ³)		
ROUTING		

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
SEE CHART

GD&T
ACCORDING TO:
ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT 

SCALE
USE MATH
DATA

• **APTIV** •

CONNECTION SYSTEMS
Chennai, India
COPYRIGHT 2021 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION OR
UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS
AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS
AUTHORIZATION, IS PROHIBITED.

		DATE
DR	SURESHKUMAR R	21SE2
APVD1	THOMAS B	21SE2
APVD2	THOMAS B	21SE2

APVD3	
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER AP 10949001	

SEE TABLE

DRAWING NAME

SINGLE WIRE SEAL

DRAWING NUMBER
1 3688485

SIZE A0	SCALE 10:1	FRAME NO 1 OF 1	SHEET NO 1 OF 1	STG R	REV 01
------------	---------------	--------------------	--------------------	----------	-----------

	DIMENSIONAL RANGE (MM)					CHART
☐ DIM TO CHECK	FROM	> 0	> 25	> 60	> 80	
☐ DIM FOR HELP	TO	25	60	80	> 80	
☐ THEORETIC DIM	TOLERANCE UNLESS OTHERWISE SPECIFIED					
	± 0.3		± 0.5	± 0.6	± 0.7	
	ANGULAR TOLERANCE $\pm 2^\circ$					

DO NOT
SCALE

USE MATH
DATA

UAD

NX

3	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[10737671](#)