



12		11	
NOTES			
-	ON MAIN VIEW ASSEMBLY 33308731 SHOWN (CODE A)		
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION		
-	ASSEMBLY INSTRUCTION NO.: 35269105-CUS71 - PRELIMINARY ASSEMBLY 35269105-CUS72 - HARNESS ASSEMBLY 35269102-CUS73 - CAR ASSEMBLY		
	MATING PARTS: - 4 WAY 2.8 FEMALE CONNECTOR ASM DWG-NO.: 35095833 - FIXING SLIDE APTIV DWG-NO.: 33308653 (IHT DWG-NO.: 17-0597-001-CSG) - BACKSHELL 90 APTIV DEG DWG-NO.: 35024558 (IHT DWG-NO.: 18-0195-001-CSG) - BACKSHELL 180 APTIV DEG DWG-NO.: 35024559 (IHT DWG-NO.: 17-0598-001-CSG) - PROTECTION CAP APTIV DWG-NO.: 35391874 (IHT DWG-NO.: 17-2270-001-CSG)		
-	MATING TERMINAL SYSTEM: - 2.8 TERMINAL DWG-NO.: 13548085 MAX WIRE CROSS SECTION: 2.5MM ²		
1	APTIV LOGO		
2	MATERIAL NAME ACCORDING TO VDA 260		
3	DATE INSERT		
4	TOOL CAVITY NUMBER		
5	INDEX REPLACEMENT INSERT		
6	PART CAVITY NUMBER		
7	MOVING DISTANCE OF SECONDARY LOCK		

MOUNTING CUT OUT
VERSION WITH POLARISATION



VERSION WITHOUT POLARISATION












REMARKS FOR MOUNTING CUT OUT:
- SHARP EDGES MUST BE COINED
- FOR POSSIBLE MOUNTING BRACKET THICKNESS AND CORRESPONDING FIXING SLIDES SEE CHART
- ☉: ENVELOPE REQUIREMENT - ACCORDING TO ISO 14405
- FOR METAL MOUNTING ELEMENTS SURFACE MUST MEET ROUGHNESS Ra MAX 1.8µm
- FOR PLASTIC MOUNTING ELEMENTS SURFACE MUST MEET MIN CLASS 24 ROUGHNESS FROM VDI 3400.


ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33308731	01	CODE A	ALL PARTS VO / 20,0
33308735	01	CODE B	
33308962	01	CODE C	
33308973	01	CODE D	
33346867	01	CODE A	ALL PARTS NVO / 19,5
33347789	01	CODE B	
33347791	01	CODE C	
33347794	01	CODE D	

POSITION		1								2		3	4	
NAME		HOUSING PANEL MOUNT								SECONDARY LOCK		SL SEAL	FIXING SEAL	
MATERIAL		PBT GF30 FR17				PBT GF30				PBT GF30 FR17	PBT GF30	LSR 50 SHORE	LSR 70 SHORE	
COLOR:		BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	ORANGE	YELLOW	REDDISH-BROWN	REDDISH-BROWN	
PART-NO.:		33308596	33308599	33308601	33308607	33346507	33347326	33347327	33347316	33308630	33346468	33283927	33308452	
-		-	---	---	---	---	---	---	---	---	---	---	---	
-		-	1	---	---	---	---	---	---	1	---	1	1	
-		-	---	1	---	---	---	---	---	1	---	1	1	
-		-	---	---	1	---	---	---	---	1	---	1	1	
-		-	---	---	---	1	---	---	---	1	---	1	1	
-		-	---	---	---	1	---	---	---	---	1	1	1	
-		-	---	---	---	---	1	---	---	---	1	1	1	
-		-	---	---	---	---	---	1	---	---	1	1	1	
-		-	---	---	---	---	---	---	1	---	1	1	1	

SHEET METAL THICKNESS		FIXING SLIDE APTIV/HT PART-NO.:		COLOR
-		PBT GF30 FR17	PBT GF30	-
1MM		33377706	33377708	NATURAL
1.5MM		33377700	33377704	GRAY
2MM		35067200	35067201	BLUE
2.5MM		33308600 / 151-02308	33347318 / 151-02309	RED
3MM		33308602 / 151-02304	33347319 / 151-02305	YELLOW
3.5MM		33308603 / 151-02306	33347321 / 151-02307	GRAY
4MM		33377696	33377698	GREEN



		DIMENSIONAL RANGE (MM)										CHART E1	
☐ DIM TO CHECK	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400		
☐ DIM FOR HELP	TO	TOLERANCE UNLESS OTHERWISE SPECIFIED											
☐ THEORETIC DIM		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2			
ANGULAR TOLERANCE ±2°													



DWG STATUS
DATE 250C18
STG R
REV 01
N/A
P/AA
CHG
ZONE
G11
E10
G10
G10
280C20
R
01
AC
G10

REVISION HISTORY
INITIAL RELEASE
REFERENCE HELLERMANN TYTON DWG-NO. ADDED
REFERENCE HELLERMANN TYTON PART-NO. ADDED
DRAWING REORGANIZATION
PROTECTION CAP APTIV DWG-NO.: 35391874
WAS 35274875
PART AVAILABILITY FOR PART NUMBERS 33346867,
3347789, 33347791, 33347794 UPDATED
HT DWG-NO: 18-0195-001-CSG WAS 17-0195-001-CSG

AUTH
P.NAJ
M.ZYR
M.GRU
K.FAR
M.GRU
K.PIT
P.NAJ
M.GRU
M.SKR
P.NAJ
M.GRU

DR
P.NAJ
M.ZYR
M.GRU
K.FAR
M.GRU
K.PIT
P.NAJ
M.GRU
M.SKR
P.NAJ
M.GRU

APVD
1
M.ZYR
M.GRU
K.PIT
M.SKR
M.GRU

APVD
2
M.ZYR
M.GRU
K.PIT
M.SKR
M.GRU

SCALE:
1:1

DWG TYP
PART DRAWING

WEIGHT (GR)
SEE CHART

VOLUME (CM³)

ROUTING

DISTR CODE
D

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
SEE CHART

GD&T
ACCORDING TO:
ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT
SCALE
USE MATH
DATA

DR
P.NAJ
DUCH

APVD1
M.ZYROMSKI

APVD2
M.GRUDZEWSKI

APVD3

APVD4

APVD5

DATE
240C18
250C18
260C18

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTORNIE PRZETWORZONE OKRESLA
APTIV 10949001

MATERIAL
SEE CHART

DRAWING NAME
4 WAY 2.8
CTCS PANEL MOUNT MALE ASSEMBLY

DRAWING NUMBER
35096050

SIZE
A1

SCALE
2:1

FRAME NO
1 OF 1

SHEET NO
1 OF 1

STG
R

REV
01

N/P
AC

CONTROLLED DOCUMENTS ARE ONLY AVAILABLE ON THE SERVER
Dwg: 35096050-CUS01-S01/01/AC
Data: 10302020,16:51,631pos,nr
Time: 16:52:34
Dots: 30-pod-20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33308962](#)