



12		NOTES		11	
-	ON MAIN VIEW ASSEMBLY 33308982 SHOWN (CODE A)				
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION				
-	ASSEMBLY INSTRUCTION NO.: 35269105-CUS71 - PRELIMINARY ASSEMBLY 35269105-CUS72 - HARNESS ASSEMBLY 35269102-CUS73 - CAR ASSEMBLY				
-	MATING PARTS: - 6 WAY 1.5 FEMALE CONNECTOR ASM DWG-NO.: 35096047 - FIXING SLIDE APTIV DWG-NO.: 33308653 (HT DWG-NO.: 17-0597-001-CSG) - BACKSHELL 90 DEG APTIV DWG-NO.: 35024558 (HT DG-NO.: 18-0195-001-CSG) - BACKSHELL 180 DEG APTIV DWG-NO.: 35024559 (HT DWG-NO.: 17-0598-001-CSG) - PROTECTION CAP APTIV DWG-NO.: 35391874 (HT DWG-NO.: 17-2270-001-CSG)				
-	MATING TERMINAL SYSTEM: - 1.5 TERMINAL DWG-NO.: 15396739 MAX WIRE CROSS SECTION: 1.0MM² RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1.5MM² - USE COMBINATION: TE TERMINAL: TAB 1.6, DWG NO.: 1703278-5 SEAL: 2112323-1 MAX INSULATION CRIMP DIMENSIONS: HEIGHT: 3.40; WIDTH: 3.40				
1	APTIV LOGO				
2	MATERIAL NAME ACCORDING TO VDA 260				
3	DATE INSERT				
4	TOOL CAVITY NUMBER				
5	INDEX REPLACEMENT INSERT				
6	PART CAVITY NUMBER				
7	MOVING DISTANCE OF SECONDARY LOCK				

MOUNTING CUT OUT
VERSION WITH POLARISATION












VERSION WITHOUT POLARISATION



ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33308982	01	CODE A	ALL PARTS VO / 20,1
33308909	01	CODE B	
33308910	01	CODE C	
33308911	01	CODE D	
33347865	01	CODE A	ALL PARTS NVO / 19,6
33347867	01	CODE B	
33347868	01	CODE C	
33347869	01	CODE D	


SHEET METAL THICKNESS	FIXING SLIDE APTIV/HT PART-NO.:	COLOR
-	PBT GF30 FR17 PBT GF30	-
1MM	33377706 33377708	NATURAL
1.5MM	33377700 33377704	GRAY
2MM	35067200 35067201	BLUE
2.5MM	33308600 / 151-02308 33347318 / 151-02309	RED
3MM	33308602 / 151-02304 33347319 / 151-02305	YELLOW
3.5MM	33308603 / 151-02306 33347321 / 151-02307	GRAY
4MM	33377696 33377698	GREEN

POSSIBILITY OF MOUNTING FROM BOTH DIRECTIONS



DIM TO CHECK	DIMENSIONAL RANGE (MM)	CHART
FROM TO	> 0 > 20 > 30 > 70 > 100 > 150 > 200 > 250 > 300 > 400	1 2 3 4 5 6 7 8 9 10
THEORETIC DIM	± 0.15 ± 0.2 ± 0.3 ± 0.4 ± 0.5 ± 0.6 ± 0.8 ± 1 ± 1.2	1 2 3 4 5 6 7 8 9 10

3		2		1	
DWG STATUS		ZONE		REVISION HISTORY	
DATE	STG	REV	N/P	CHG	
250C18	R	01	AA		INITIAL RELEASE
14MR19	R	01	AA		REFERENCE HELLERMANN TYTON DWG-NO. ADDED REFERENCE HELLERMANN TYTON PART-NO. ADDED DRAWING REORGANIZATION
150C19	R	01	AB		PROTECTION CAP APTIV DWG-NO.: 35391874 WAS 35274875 PART AVAILABILITY FOR PART NUMBERS 33347865, 33347867, 33347868, 33347869 UPDATED NOTES UPDATED
280C20	R	01	AC		HT DWG-NO: 18-0195-001-C56 WAS 17-0195-001-C56



• APTIV •

CONNECTION SYSTEMS
KRAKOW, POLAND

COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WLASNOSCIA APTIV I ZAWIERA POUFNE INFORMACJE POWELANE, ROZPOWISZCZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIAZANYCH Z NIM DANYCH CAD, JAK ROWNIEZ PRZEKAZYWANIE INNYM JAKIEJKOLWIEK ICH ZAWARTOSCI BEZ NADANIA WYRAZNYCH UPRAWNIEN, JEST ZABRONIONE.

DR	P.NAJDUCH	DATE	240C18
APVD1	M.ZYROMSKI		250C18
APVD2	M.GRUDZEWSKI		260C18
APVD3			
APVD4			
APVD5			

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTORNIE PRZETWORZONE OKRESLA APTIV 10949001

MATERIAL

SEE CHART

DRAWING NAME

6 WAY 1.5
CTCS PANEL MOUNT MALE ASSEMBLY

DRAWING NUMBER

35096163

SIZE	A1	SCALE	2:1	FRAME NO	1 OF 1	SHEET NO	1 OF 1	STG	R	REV	01	N/P	AC
------	----	-------	-----	----------	--------	----------	--------	-----	---	-----	----	-----	----

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33308982](#)