






CLOSED END VIEW
16MM CONDUIT


CLOSED END VIEW
10MM CONDUIT

CLOSED END VIEW
13MM CONDUIT



CLOSED END VIEW
NO CONDUIT



33321103 -FOR 10MM CONDUIT
SAME AS TYPE 16MM CONDUIT
EXCEPT AS SHOWN



33321104 -FOR 13MM CONDUIT
SAME AS TYPE 16MM CONDUIT
EXCEPT AS SHOWN



33321105
16MM CONDUIT

- NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR SHOWN INDICATED:
 - 1. DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEW MATH MODEL FOR PRECISE DIMENSIONS), FOR ALL OTHER DIMENSIONS NOT SHOWN BUT UTILIZED FOR TOOL BUILD, SEW MATH MODEL FOR PRECISE TOOL PATH DATA.
2. MATERIAL RECYCLING CODE PER ISO 11469, (1,5)X(11) CHARACTERS PA 66 LOCATED ON ANY EXTERIOR SURFACE.
3. THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR DEFECTS INCLUDING BUT NOT LIMITED TO: SCUFF MARKS, COLOR BLEMISHES, GATE VESTIGES, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER ENP. 4-3.CS.OI.EN.
4. REFERENCE MATERIAL COMPONENTS OR EQUIVALENT:
 - USE 15316895(H59005) & 15425612(H59015) ASSEMBLY DRAWINGS
5. (1,5)X(11) APTIV CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY.
6. APEX 2.8 10-WAY MALE AND FEMALE WIRE DRESSOVER
7. INTERCHANGEABLE TOOL FOR 10MM, 13MM, 16MM AND NO CONDUIT (COT) OPTIONS
8. USE ASSEMBLY MANUAL 33230150 FOR ADDITIONAL INFORMATION
9. ACCEPTANCE CRITERIA DEVIATIONS: 35 N·m for BACKSHELL LOCKED RETENTION AT WIRE EXIT POINT - 60 N·m for CONDUIT TO BACKSHELL RETENTION, 80 N·m for RETENTION OPPOSITE DIRECTION OF ENGAGE POSIT MOISTURE, 100 m·m for CONNECTOR TO BACKSHELL RETENTION UNDER SILENCE

33321105	04	AE	16 (M1889005)	16	5.883
33321104	04	AE	13 (M1889004)	13	5.974
33321103	04	AE	10 (M1889003)	10	6.031
33321102	04	AA	NO CONDUIT	NO CODE	5.721
PART NO	REV	N/P	CONDUIT SIZE mm	CODE	VOLUME CM³

DIMENSIONAL RANGE (MM)									CHART E1	
FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	
TO	20	30	70	100	150	200	250	300	400	
TOLERANCE UNLESS OTHERWISE SPECIFIED										
	+0.15	+0.2	+0.3	+0.4	+0.5	+0.6	+0.8	+1	+1.2	

PART NAMES THAT ENTER THROUGH A PART NUMBER
 INDICATE THAT PHYSICAL PARTS ARE NOT AVAILABLE
 FOR ORDERING.
 PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE
 THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.
 CONTACT ACTIVELY SALES TO ASSURE AVAILABILITY
 OF PARTS.

DWS TYPE
PART DRAWING


STYLE
 POLLINE (CM) DISTR CODE
SEE CHART **ID**

UNLESS OTHERWISE SPECIFIED
 THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-1994
 DIMENSIONING AND ANNOTATION PRACTICES
 FOR EXPRESSING DIMENSIONS, TOLERANCES, SURFACE TEXTURES,
 AND FINISHES. IT IS GRANTED SEPARATELY, REGARDLESS OF DATA
 REFERENCES.


ALL DIMENSIONS ARE IN MILLIMETERS

REFERENCE:

THIRD ANGLE
PROJECTION



DO NOT
USE MATH DATA





• APTIV •									
CONNECTION SYSTEMS									
KOREN, IN COPYRIGHT 2014 APTIV, ALL RIGHTS RESERVED. THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. NO REPRODUCTION, DISTRIBUTION OR UTILIZATION OF ANY INFORMATION OR TO BE RELEASED OR DISCLOSED AS WELL AS LOANING OR LENDING OF THIS DRAWING TO ANY OTHER PARTY WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.									
						DATE			
DW									
APR010 SAKTHIVEL M						07MR16			
APR010 SAKTHIVEL M						07MR16			
APR010 DECKARD DAVID J						07MR16			
APR014									
APR005									
SUBJECTS OF CONCERN AND RECYCLED CONTENT PER APTIV [034900]									
MATERIAL									
POLYIMIDE COATING BLACK									
DRAWING NAME									
TAXI COV CONN PROTECTIVE									
DRAWING NUMBER									
333200									
SIZE	SCALE	FRAME NO	SHEET NO	STC	REV	REP	DATE	BY	CHK

001133

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33321104](#)