
















TYPE 1




TYPE II



NOTES	
1	NOT DIMENSIONED GEOMETRY HAS TO BE TAKEN FROM THE CORRESPONDING 3D DATA FILE
2	MATERIAL SPECIFICATION: SILICONE, AUTOLUBRICATION
3	TENSILE STRENGTH : RM MIN 6.2 N/MM ²
4	ELONGATION : 375% DIN 53504-S2
5	DURUMETER ORIGINAL: SHORE(A) 50±5 DIN53505
6	MEASURE ON TEST SLABS

SCALE
2:1



DWG TYPE PART DRAWING		DISTR CODE D
WEIGHT (GRI)		
VOLUME (CM ³)		
ROUTING		

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
SEE CHART

© 2004 Blackwell Publishing Ltd

GD&T
ACCORDING TO:

ISO 1101

REFERENCE
ORIGINAL DESIGN

FIRST ANGLE PROJECT

DO NOT SCALE

• APTIV •

CONNECTION SYSTEMS

Chennai, India

THIS DRAWING IS THE PROPERTY OF ACTIV AND CONTAINS ACTIV
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION OR
UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS
AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS
AUTHORIZATION, IS PROHIBITED.

		DATE
DR	SURESHKUMAR R	21SE2
ARVD:	THOMAS R	21SE2

APVD2	THOMAS B	21SE2
APVD3		

APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER ARTICLE	

MATERIAL	SEE TABLE
----------	-----------

DRAWING NAME
SINGLE WIRE SEAL

DRAWING NUMBER
1 26 88485

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV
A0	1:1	1 OF 1	1 OF 1	B	0

2	1
---	---

SHARP CORNER TOLERANCE

	DIMENSIONAL RANGE (MM)					CHART
☐ DIM TO CHECK	FROM	> 0	> 25	> 60	> 80	> 80
☐ DIM FOR HELP	TO	25	60	80		
TOLERANCE UNLESS OTHERWISE SPECIFIED						
☐ THEORETIC DIM		±0.3	±0.5	±0.6	±0.7	
		ANGULAR TOLERANCE 12°				

DO NOT SCALE

USE MATH DATA	U
3	

--	--

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[10730124](#)