

12		NOTES		11	
-	ON MAIN VIEW ASSEMBLY 33308982 SHOWN (CODE A)				
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK IN OPEN POSITION				
-	ASSEMBLY INSTRUCTION NO.: 35269105-CUS71 - PRELIMINARY ASSEMBLY 35269105-CUS72 - HARNESS ASSEMBLY 35269102-CUS73 - CAR ASSEMBLY				
-	MATING PARTS: - 6 WAY 1.5 FEMALE CONNECTOR ASM DWG-NO.: 35096047 - FIXING SLIDE APTIV DWG-NO.: 33308653 (IHT DWG-NO.: 17-0597-001-CSG) - BACKSHELL 90 DEG APTIV DWG-NO.: 35024558 (IHT DG-NO.: 18-0195-001-CSG) - BACKSHELL 180 DEG APTIV DWG-NO.: 35024559 (IHT DWG-NO.: 17-0598-001-CSG) - PROTECTION CAP APTIV DWG-NO.: 35391874 (IHT DWG-NO.: 17-2270-001-CSG)				
-	MATING TERMINAL SYSTEM: - 1.5 TERMINAL DWG-NO.: 15396739 MAX WIRE CROSS SECTION: 1.0MM² RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1.5MM² - USE COMBINATION: TE TERMINAL: TAB 1.6, DWG NO.: 1703278-5 SEAL: 2112323-1 MAX INSULATION CRIMP DIMENSIONS: HEIGHT: 3.40; WIDTH: 3.40				
1	APTIV LOGO				
2	MATERIAL NAME ACCORDING TO VDA 260				
3	DATE INSERT				
4	TOOL CAVITY NUMBER				
5	INDEX REPLACEMENT INSERT				
6	PART CAVITY NUMBER				
7	MOVING DISTANCE OF SECONDARY LOCK				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33308909](#)