









TERMINAL, CABLE ALIGNMENT VIEWS
SCALE 10:1








STANDARD REELING



SPLICE AND REEL SPECIFICATIONS
SCALE 1:5



TYPE 102
SEALED
SAME AS TYPE 101
EXCEPT AS SHOWN

TYPE 101
UNSEALEDSECTION B-B
CONDUCTOR

SECTION C-C
INSULATION

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
- DIMENSIONS ARE TO FACE OF VIAL SHOW AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
USE WITH MODEL FOR PRECISION OF MEASUREMENTS
ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILT, USE WITH MODEL FOR PRECISE TOOL PATH DATA,
ALL ROOT 0.2
- “(XX)” INDICATES “PI” PLUS LAST TWO DIGITS OF MAKE DIE SERIES NUMBER
(PI = 3.14159265359) (XX = 10)
- “(11K)” CORPORATE BRAND STAMP TO BE LOCATED ON THIS
EXTERNAL SURFACE, VISIBLE AT FINAL ASSEMBLY.
OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE
“F” OR “FC” LOGO.
- TERMINAL SYMMETRICAL ABOUT CENTERLINE EXCEPT AS SHOWN.
- RECOMMENDED WARE BLADE THICKNESS PER USP STANDARD ECAW-001
- AFTER MANUFACTURE, DO NOT PROBE, TEST, OR OTHERWISE CONTACT THE
INTERNAL PROJECTION OR SPRING OR ANY MOVING PARTS OF THIS TERMINAL.
SEVERE DAMAGE CAN OCCUR, COMPROMISING THE PERFORMANCE OF THE
ELECTRIC INTERFACE.
- PLATING TYPE:
1. WASTE FIN. 1.27 - 2.54 MICROMETERS THICK
11. WASTE FIN. 1.27 - 3.81 MICROMETERS THICK
12. 0.05 - 0.10 MICROMETER THICK NICKEL UNDERPLATE
1.27 - 2.54 MICROMETERS THICK
13. 0.05 - 0.10 MICROMETER THICK
14. FINISH: DUCTILE NICKEL 1.27 - 2.54 MICROMETERS THICK
- PLATING TYPE: REFERENCE SHOWN ABOVE IS REFERENCE ONLY.
ALL PLATING REQUIREMENTS ARE CONTAINED IN APPLICABLE MATERIAL SPECIFICATION.

[illegible]

DRAWING NUMBER							
13949867							
SIZE	SCALE	FRAME NO	SHEET NO	STD	REV	N/P	
A1x4	15:1	2 OF 2	1 OF 2	R	13	-	
18			17				

SYMBOL DEFINITION		MISSING SYMBOLS		DATE
DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF INSPECTIONS REQUIRED	45	7-9-10 12-23 25-28 30-32 34 36-38 42-44 47-153 155-160 162-189 196	05MAR19
	LAST NO. USED	199		12APR19

7/17/93		2048		REVISION HISTORY		AUTH	
2	01	01	01	INITIAL DRAWING RELEASED		AKA/SPR	
2	01	02	01	1502107,1502150,1502151,1502540 AND 1502541 (CABLE) ALL PARTS - UPDATED MW, PASTE UP DUE TO REVEY AND ADDED INSULATION W/STAINLESS STEEL WIRE	421194	AKA/SPR	
4	03	01	01	33517385 - RELEASED	426201	00010000	
4	03	04	01	ALL PARTS - ADDED LABEL ON CABLE SAG, 1502150, 1502151, 1502152, 1502540, 1502541 CONDUCTOR & INSULATION W/STAINLESS STEEL WIRE AND 1502540 CHANGED CHARTER FROM ON DRUG TO 1502540 1502540,1502541,33517385 - AWO WIRE SAGE W/RE 25-25	426202	00010000	
4	05	01	01	15048898 - RELEASED	426903	AKA/SPR	
4	05	05	01	15021009,15024560,13517385 - AWO WIRE SAGE W/RE 25-25 ON DRUG	431062	00010000	
5	07	01	01	15050461 - UPDATED PART AVAILABILITY	431685	AKA/SPR	
5	07	01	01	13337933,13337934,13337935 - RELEASED	432766	00010000	
6	08	01	01	REVISIONS COMPLETED, PARTS PARTIALLY NOTED ON PDS 3337934	432767	00010000	
7	10	01	01	ALL PARTS - REDEMAN, ADDED "TERMINAL, 1502150, 1502151, 1502152, 1502540, 1502541 SPECIFICATIONS - VIEWS, REVEY LABEL NOTES AND CHART CHANGES	436019	00010000	
8	12	01	01	15050461 - UPDATED PART AVAILABILITY	440956	00010000	
8	12	01	01	13679700,15021507, 09 & 13339333	441252	AKA/SPR	
9	13	01	01	15048898 - 13337933 - RELEASED	552585	AKA/SPR	

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33337935](#)