









ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33308974	01	CODE A	ALL PARTS VO / 18,2
33308975	01	CODE B	
33308976	01	CODE C	
33308977	01	CODE D	
33346865	01	CODE A	ALL PARTS NVO / 17,6
33346862	01	CODE B	
33346860	01	CODE C	
33346858	01	CODE D	


POSITION	1		2								3	4		5	
NAME	HOUSING		INSERT								HOUSING SEAL	SECONDARY LOCK		SLIDER	
MATERIAL	PBT GF30 FR17	PBT GF30	PBT GF30 FR17				PBT GF30				LSR 50 SHORE	PBT GF30 FR17	PBT GF30	PBT GF30 FR17	PBT GF30
COLOR:	BLACK	BLACK	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	REDDISH-BROWN	ORANGE	YELLOW	ORANGE	YELLOW
PART-NO.:	33308598	33346472	33308629	33308631	33308633	33308636	33346487	33346489	33346490	33346491	33308450	33308623	33346470	33308449	33346481
-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
-	1	-	1	-	-	-	-	-	-	-	1	1	-	1	-
-	1	-	-	1	-	-	-	-	-	-	1	1	-	1	-
-	1	-	-	-	1	-	-	-	-	-	1	1	-	1	-
-	1	-	-	-	-	1	-	-	-	-	1	1	-	1	-
-	-	1	-	-	-	-	1	-	-	-	1	-	1	-	1
-	-	1	-	-	-	-	-	1	-	-	1	-	1	-	1
-	-	1	-	-	-	-	-	-	1	-	1	-	1	-	1
-	-	1	-	-	-	-	-	-	-	1	1	-	1	-	1


DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
250C18	R	01				INITIAL RELEASE		P.NAJ	M.ZYR	M.GRU
14MR19	R	01	AA		B7	REFERENCE HELLERMANN TYTON DWG-NO. ADDED		K.FAR	M.GRU	K.PIT
10FE20	R	01	AB		G11	PART AVAILABILITY FOR PART NUMBERS 33346865, 33346862, 33346860, 33346858 UPDATED		P.NAJ	M.GRU	
270C20	R	01	AC		B7	HT DWG-NO: 18-0195-001-CSG WAS 17-0195-001-CSG		P.NAJ	M.GRU	



NOTES	
-	ON MAIN VIEW ASSEMBLY 33308974 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK AND SLIDER IN OPEN POSITION
ASSEMBLY INSTRUCTION NO.:	
35269106-CUS71 - PRELIMINARY ASSEMBLY	
35269106-CUS72 - HARNESS ASSEMBLY	
35269103-CUS73 - CAR ASSEMBLY	
35269102-CUS73 - CAR ASSEMBLY	
MATING PARTS:	
- 4 WAY 2.8 MALE PANEL MOUNT ASM DWG-NO.: 35096050	
- 4 WAY 2.8 MALE STRAP MOUNT ASM DWG-NO.: 35096188	
- BACKSHELL 90 DEG APTIV DWG-NO.: 35024558	
(HT DWG-NO.: 18-0195-001-CSG)	
- BACKSHELL 180 DEG APTIV DWG-NO.: 35024559	
(HT DWG-NO.: 17-0598-001-CSG)	
- PROTECTION CAP APTIV DWG-NO.: 35149889	
(HT DWG-NO.: 17-2265-001-CSG)	
MATING TERMINAL SYSTEM:	
- 2.8 TERMINAL DWG-NO.: 15446676	
MAX WIRE CROSS SECTION: 2.5MM²	
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	TOOL CAVITY NUMBER
4	PART CAVITY NUMBER
5	MOVING DISTANCE OF SECONDARY LOCK
6	MOVING DISTANCE OF SLIDER

DIM TO CHECK		DIMENSIONAL RANGE (MM)															
FROM		> 0		> 20		> 30		> 70		> 100		> 150		> 200		> 250	
TO		> 20		> 30		> 70		> 100		> 150		> 200		> 250		> 300	
TOLERANCE UNLESS OTHERWISE SPECIFIED		±0.15		±0.2		±0.3		±0.4		±0.5		±0.6		±0.8		±1	
ANGULAR TOLERANCE		±2°															

DWG TYP PART DRAWING		DISTR CODE D
WEIGHT (GR) SEE CHART		
VOLUME (CM ³) ---		
ROUTING		
UNLESS OTHERWISE SPECIFIED		
GENERAL TOLERANCES ACCORDING TO: SEE CHART		
GD&T ACCORDING TO: ISO 1101		
REFERENCE		
FIRST ANGLE PROJECTION 		
DO NOT SCALE 		
USE MATH DATA 		



• APTIV •	
CONNECTION SYSTEMS KRAKOW, POLAND	
COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
TEN RYSUNEK JEST WŁASNOŚCIĄ APTIV I ZAWIERA PEŁNE INFORMACJE POWIĘLANE, ROZPOWISZCZANIE I WYKORZYSTYWANIE TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEJKOLWIEK ICH ZAWARTOŚCI BEZ NADANIA WYRAŹNYCH UPRAWNIEN, JEST ZABRONIONE.	
DR	P.NAJDUCH
APVD1	M.ZYROMSKI
APVD2	M.GRUDZEWSKI
APVD3	
APVD4	
APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001 SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIIE PRZETWORZONE OKREŚLA APTIV 10949001	
SEE CHART	
DRAWING NAME	
4 WAY 2.8 CTCS FEMALE ASSEMBLY	
DRAWING NUMBER	
35095833	
SIZE	A1
SCALE	2:1
FRAME NO	1 OF 1
SHEET NO	1 OF 1
STG	R
REV	01
N/P	AC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33308975](#)