




KEY PRODUCT CHARACTERISTICS					
SAFETY/COMPLIANCE		FIT/FUNCTION		TOTAL ON DRAWING	0
S/C CHECKPOINTS		F/F CHECKPOINTS		LAST NO. USED	0
NO. & TYPE	DESCRIPTION	RATIONALE	PTS	ZONE	
-	-	-	-	-	-

ENGAGE FORCE STECKKRAFT INI	X ₂	X ₁	L _{pin}	L ₁	L ₂	L ₁	L _{1B}	L _{1A}	R ₁ ± 0.1	R ₁ ± 0.1	R _{1B} ± 0.1	R _{1A} ± 0.1	H ₂ ± 0.2	H ₁ ± 0.2	H _{1B} ± 0.2	H _{1A} ± 0.2	B ₂ ± 0.2	B ₁ ± 0.2	B _{1B} ± 0.2	B _{1A} ± 0.2	WEIGHT GEWICHT (g)
2.5 ± 1	0.2	0.2	16	5.7	1.75	3.25	1.5	1.5	0.8	.	0.4	0.4	1.60	.	1.40	1.50	1.90	.	1.35	1.45	0.136
2.5 ± 1	0.2	0.2	16	5.7	2	3.0	.	.	0.9	0.60	.	.	2.10	1.70	.	.	2.15	1.65	.	.	0.143
2.5 ± 1	0.2	0.2	16	6.1	2	3.0	.	.	0.9	0.75	.	.	2.95	2.25	.	.	2.50	2.20	.	.	0.154
2.5 ± 1	0.2	0.2	16	6.1	2	3.0	.	.	1.2	0.90	.	.	3.95	2.75	.	.	3.75	2.50	.	.	0.160
2.5 ± 1	0.2	0.2	16	6.1	2	3.0	.	.	1.2	0.90	.	.	3.95	3.05	.	.	3.75	2.80	.	.	0.167

ENGAGE FORCE STECKKRAFT INI	X ₂	X ₁	L _{pin}	L ₁	L ₂	L ₁	L _{1B}	L _{1A}	R ₁ ± 0.1	R ₁ ± 0.1	R _{1B} ± 0.1	R _{1A} ± 0.1	H ₂ ± 0.2	H ₁ ± 0.2	H _{1B} ± 0.2	H _{1A} ± 0.2	B ₂ ± 0.2	B ₁ ± 0.2	B _{1B} ± 0.2	B _{1A} ± 0.2	WEIGHT GEWICHT (g)
2.5 ± 1	0.2	0.2	16	5.7	1.75	3.25	1.5	1.5	0.8	.	0.4	0.4	1.60	.	1.40	1.50	1.90	.	1.35	1.45	0.136
2.5 ± 1	0.2	0.2	16	5.7	2	3.0	.	.	0.9	0.60	.	.	2.10	1.70	.	.	2.15	1.65	.	.	0.143
2.5 ± 1	0.2	0.2	16	6.1	2	3.0	.	.	0.9	0.75	.	.	2.95	2.25	.	.	2.50	2.20	.	.	0.154
2.5 ± 1	0.2	0.2	16	6.1	2	3.0	.	.	1.2	0.90	.	.	3.95	2.75	.	.	3.75	2.50	.	.	0.160
2.5 ± 1	0.2	0.2	16	6.1	2	3.0	.	.	1.2	0.90	.	.	3.95	3.05	.	.	3.75	2.80	.	.	0.167

ENGAGE FORCE STECKKRAFT INI	X ₂	X ₁	L _{pin}	L ₁	L ₂	L ₁	L _{1B}	L _{1A}	R ₁ ± 0.1	R ₁ ± 0.1	R _{1B} ± 0.1	R _{1A} ± 0.1	H ₂ ± 0.2	H ₁ ± 0.2	H _{1B} ± 0.2	H _{1A} ± 0.2	B ₂ ± 0.2	B ₁ ± 0.2	B _{1B} ± 0.2	B _{1A} ± 0.2	WEIGHT GEWICHT (g)
3.0 ± 1	0.2	0.2	16	5.7	1.75	3.25	1.5	1.5	0.8	.	0.4	0.4	1.60	.	1.40	1.50	1.90	.	1.35	1.45	0.136
3.0 ± 1	0.2	0.2	16	5.7	2	3.0	.	.	0.9	0.60	.	.	2.10	1.70	.	.	2.15	1.65	.	.	0.143
3.0 ± 1	0.2	0.2	16	6.1	2	3.0	.	.	0.9	0.75	.	.	2.95	2.25	.	.	2.50	2.20	.	.	0.154
3.0 ± 1	0.2	0.2	16	6.1	2	3.0	.	.	1.2	0.90	.	.	3.95	2.75	.	.	3.75	2.50	.	.	0.160
3.0 ± 1	0.2	0.2	16	6.1	2	3.0	.	.	1.2	0.90	.	.	3.95	3.05	.	.	3.75	2.80	.	.	0.167

MATERIAL THICKNESS MATERIALDÜCKE	SURFACE OBERFLÄCHE	MATERIAL WERKSTOFF	CABLE-TYPE LTG.-TYP	CROSS SECTION QUERSCH.	VERSION AUSFUEHR.	POS	SINGLE P/N EINZELTEIL	ASSEMBLY P/N ZUSAMMENBAU	PART REV	DATE DATUM
0.2± 0.005	FSn3	CuSn4	FLMRY-A	0.08-0.18	UNSEALED	1	13948571	13948572	03	12MR14
0.15± 0.005	FSn3	CuNi35Ti1Mg	FLRY	0.22-0.35	UNSEALED	2	13948562	13959129	03	12MR14
0.2± 0.005	FSn3	CuSn4	FLRY	0.5-0.75	UNSEALED	1	13959112	13959126	04	09MY17
0.15± 0.005	FSn3	CuNi35Ti1Mg	FLRY	1.0	UNSEALED	2	13948562	35506842	01	07AP21
0.2± 0.005	FSn3	CuSn4	FLRY	1.5	UNSEALED	1	13959109	13959123	05	09MY17
0.15± 0.005	FSn3	CuNi35Ti1Mg	FLRY	1.5	UNSEALED	2	13948562			


MATERIAL THICKNESS MATERIALDÜCKE	SURFACE OBERFLÄCHE	MATERIAL WERKSTOFF	CABLE-TYPE LTG.-TYP	CROSS SECTION QUERSCH.	VERSION AUSFUEHR.	POS	SINGLE P/N EINZELTEIL	ASSEMBLY P/N ZUSAMMENBAU	PART REV	DATE DATUM
0.2± 0.005	FSn3	CuSn4	FLMRY-A	0.08-0.18	UNSEALED	1	13948571	13959133	03	12MR14
0.15± 0.005	g-Ag	CuNi35Ti1Mg	FLRY	0.22-0.35	UNSEALED	2	13959102	13959131	03	12MR14
0.2± 0.005	FSn3	CuSn4	FLRY	0.5-0.75	UNSEALED	1	13959110	13959128	04	09MY17
0.15± 0.005	FSn3	CuNi35Ti1Mg	FLRY	1.0	UNSEALED	2	13959102	35506851	01	07AP21
0.2± 0.005	FSn3	CuSn4	FLRY	1.5	UNSEALED	1	13959109	13959125	05	09MY17
0.15± 0.005	g-Ag	CuNi35Ti1Mg	FLRY	1.5	UNSEALED	2	13959102			

MATERIAL THICKNESS MATERIALDÜCKE	SURFACE OBERFLÄCHE	MATERIAL WERKSTOFF	CABLE-TYPE LTG.-TYP	CROSS SECTION QUERSCH.	VERSION AUSFUEHR.	POS	SINGLE P/N EINZELTEIL	ASSEMBLY P/N ZUSAMMENBAU	PART REV	DATE DATUM
0.2± 0.005	FSn3	CuSn4	FLMRY-A	0.08-0.18	UNSEALED	1	13948571	13959132	03	30AU19
0.15± 0.005	sel. Au	CuNi35Ti1Mg	FLRY	0.22-0.35	UNSEALED	2	13959103	13959130	03	30AU19
0.2± 0.005	FSn3	CuSn4	FLRY	0.5-0.75	UNSEALED	1	13959110	13959127	04	30AU19
0.15± 0.005	sel. Au	CuNi35Ti1Mg	FLRY	1.0	UNSEALED	2	13959103	35506865	01	07AP21
0.2± 0.005	FSn3	CuSn4	FLRY	1.5	UNSEALED	1	13959109	13959124	05	30AU19
0.15± 0.005	sel. Au	CuNi35Ti1Mg	FLRY	1.5	UNSEALED	2	13959103			

(SAD) (06) (SAC)

L-SHAPE VERSION ONLY FOR PART-NO.:
L-SHAPE VARIANTE NUR FÜR PART-NR.:
13948572; 13959132; 13959133

BASIC APPLICATION / STANDARD VARIANTE



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[13959129](#)