







TYPE 202
20-35 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 208
20-35 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 212
12-19 MM²
SAME AS TYPE 205
EXCEPT AS SHOWN




TYPE 216
12-19 MM²
SAME AS TYPE 209
EXCEPT AS SHOWN




TYPE 203
20-35 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 204
20-35 MM²
SAME AS TYPE 20
EXCEPT AS SHOWN




TYPE 205
12-19 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 209
8 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 210
20-35 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 213
20-35 MM²
SAME AS TYPE 201
EXCEPT AS SHOWN




TYPE 214
12-19 MM²
SAME AS TYPE 205
EXCEPT AS SHOWN




TYPE 206
12-19 MM²
SAME AS TYPE 20
EXCEPT AS SHOWN








TYPE 207
20-35 MM²
SAME AS TYPE 20
EXCEPT AS SHOWN



TYPE 211
20-35 MM.
SAME AS TYPE 20
EXCEPT AS SHOWN



TYPE 215
12-19 MM²
SAME AS TYPE 205
EXCEPT AS SHOWN



SECTION
SCALE

NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS), FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 2. FOR TERMINALS WITH STOCK THICKNESS OF 1.3MM OR GREATER
AND TOOLING PRODUCED AFTER 01A1U4 REFER TO ADDITIONAL
TOLERANCE CHART.
- | | |
|----|--|
| 20 | 3. HEX NUT MUST WITHSTAND A MINIMUM PUSH OUT FORCE OF 800 N. |
| 34 | 4. HEX NUT MUST FREELY ROTATE WHEN A MIN TORQUE VALUE OF 2 NM
IS APPLIED. |

35084281	02	AB	216	12-19	5	35084278	32765653	90°	
35084280	02	AA	215	12-19	5	35084279	32765652	90°	
350956168	02	AA	214	12-19	5	350956167	32765653	90°	
33302801	02	AB	210	20-35	2	33302800	32765653	90°	
33302804	02	AB	212	12-19	5	33302799	32765653	90°	
33302803	02	AB	211	20-35	2	33302802	32765653	90°	
33302821	02	AB	210	20-35	2	33302820	32765653	90°	
33302802	02	AB	210	20-35	2	33302819	32765653	90°	
33291202	03	AB	208	20-35	2	33291201	32765653	60°	
33276570	03	AB	207	20-35	2	33276562	32765653	90°	
33276569	04	AB	206	12-19	5	33276561	33276563	90°	
33276568	03	AA	205	12-19	5	33276560	32765653	90°	
33276567	04	AA	204	20-35	2	33276559	32765653	90°	
33276566	03	AA	203	20-35	2	33276558	33276563	90°	
33276565	03	AA	202	20-35	2	33276557	32765653	90°	
33276564	04	AA	201	20-35	2	33276556	32765653	90°	
PART NO	REV	N/P	TYPE	SIZE	MMF1	ID	TERMINAL	NUT	W

TOLERANCE CHART FOR TERMINALS			
WITH A STOCK THICKNESS OF 1.3MM OR GREATER AND TOOLING PRODUCED AFTER 01/14			
DIMENSIONAL RANGE IMMI			
BLANKED DIMS			
FROM	0	>12	ANGULAR
TOLERANCE UNLESS OTHERWISE SPECIFIED			
	±0.15	±0.3	±2°
STAMPING DIE DIMS			
FROM	0	2	ANGULAR
	2	10	>10
TOLERANCE UNLESS OTHERWISE SPECIFIED			
	±0.15	±0.3	±0.4
POST PRODUCTION DIMS			
FROM	0	2	ANGULAR
	2	10	>10
TOLERANCE UNLESS OTHERWISE SPECIFIED			
	±0.15	±0.3	±0.4
			5° - 7°

20		PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)		CHART	
FROM	0		
TO	12	> 12	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
+0.1		+0.2	
ANGULAR TOLERANCE ±2°			

INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE (OR ORDERING)	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING, BUT MAY BE SUBJECT TO ASSURE AVAILABILITY IN PARTS.	
IND TYPE	
PART DRAWING	
STYLE	
KOLINE (CMT)	DISTR CODE
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14-1994 AS MINIMUM TO THE FOLLOWING DIMENSIONS AND TOLERANCES. DIMENSIONS AND TOLERANCES OF FEATURES MAY BE GAUGED SEPARATELY. REMOVALS OF DATA REPRESENTED BY DIMENSIONED FEATURES ARE SUBJECT TO REVIEW.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	 

•APTIV• CONNECTION SYSTEMS WARREN, OH COPYRIGHT 1975 APTIV, ALL RIGHTS RESERVED. THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS CONTENT OR ANY PART THEREOF WITHOUT THE WRITTEN PERMISSION OF APTIV IS PROHIBITED. UNLESS OTHERWISE INDICATED, THIS DRAWING IS UNCLASSIFIED.			
DRAWING			DATE
DR			
APPROV: J. M. LUIS TAPIA	300015		
APPROV: J. WILLIAM	300015		
APPROV: BENATO GONZALEZ	300015		
APPROV:			
SUBSTANCES OF CONCERN AND RELEVANT CONTENT FOR APTIV (H490401)			
MOTHER: SEE CHART			
ORDERING NAME: TAXI ASM TERM RING HEX NUT SUN			
DRAWING NUMBER: 33128259			
SIZE: A1x3	4:1	1 OF 2	2 OF 2
DATE: 11-1-75	TIME: 10:10	BY: R	DR: 10

A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL
 DOES NOT REQUIRE INSPECTION. IT MAY BE
 CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.

TOTAL NO OF INSPECTIONS REQUIRED	48
LAST NO. USED	42

DATE	STO	REV	N/P	CH	REVISION HISTORY	DATE	BY	APP'D
26/03/15	R	01	-	-	ALL PARTS - RELEASED PART DRAWING	413044	JTV	JWJ/MS
22/JA/16	R	02	-	-	ALL PARTS - REVISED TERMINAL	413896	JTV	JTV/MS
22/JA/16	R	03	-	-	13318316 - RELEASED AND 33276567 & 33276569 - REVISED TERMINAL	432309	AHR	JWJ/MS
27SE/16	R	04	-	-	ALL AVAILABLE PARTS - PSD WAS N/A, ADDED CABLE 532 COLUMB AND DIM #343 33302801 & 33302803-B5 - RELEASED	434288	AHR	JWJ/MS
19/0C/16	R	05	-	-	ALL PARTS - REDIMENSIONED OF ALL TYPES: REMOVED DIMS #2,21 & 22; REVISED SECTION A-4 AND DIMS #22, 23, 24	435039	JWJ	JWJ/LES
05/JA/17	R	06	-	-	ALL PARTS - UPDATED PART AVAILABILITY	435274	AHJ	LES/LES
24/JA/17	R	07	-	-	ALL PARTS - UPDATED TERM TO LATEST REV	435493	AHJ	LES/LES
01/FE/17	R	08	-	-	ALL PARTS - PSD WAS 19, ADDED DIM 1-32 @ 0.005	435581	LES	LES/MSR
28/FE/17	R	09	-	-	ALL PARTS - ADDED "1D" COLUMN ON CHART AND 35050168 - RELEASED	435721	JWJ	JWJ/LES
15/MR/17	R	10	-	-	35056168 & 33276566 - WERE #6 CABLE 1D AND 33276567, 66 & 64 - WERE #4 CABLE 1D	436004	NRN	NRN/MSR
30/MR/17	R	11	-	-	ALL PARTS - DIM B.52 -> O.3 WAS B.52	436188	LES	LES/MSR
22/M/17	R	12	-	-	35040280-B1 - RELEASED	436434	JVR	JWJ/LES
29/M/17	R	13	-	-	35056168 - REVISED GRAPHICS	436846	GLB	GLB/LES
07/AI/18	R	14	-	-	ALL PARTS - UPDATED TERMINAL TO LATEST REVISION	439920	LVD	JAE/LES
16/AI/18	R	15	-	-	35049281 WAS 02, 35048928 WAS 02, 35056168 WAS 02, 33800268 WAS 02, 33380264 WAS 02, 33380283 WAS 02, 33380281 WAS 02, 33391002 WAS 03, 33276567 WAS 03, 33276569 WAS 04, 33276568 WAS 03, 33276567 WAS 04, 33276568 WAS 03, 33276565 WAS 03, 33276564 WAS 03 FOR AUTH NUMBER 439920	440424	AHJ	AHJ/LES
10/SE/18	R	16	-	-	ALL PARTS - UPDATED TO LATEST REVISION: 33276564-65, 67, 69 - 70, 33291202, 33318316, 33380281, 83 - 85, 35042491 - UPDATED PART AVAILABILITY	440947	AHJ	AHJ/LES
13/SE/18	R	17	-	-	33380283, 35042491, 33380284, 85, 33380281, 33383816, 33291202, 33276570, 33276569, 33276567, 33276564, 65 - UPDATED PART AVAILABILITY	441056	LES	LES/MSR
14/AJ/18	R	18	-	-	ALL PARTS - PUSH OUT MEASUREMENT WAS 110N, ADDED MEASUREMENT LABEL, DETAIL "B" AND Ø9.1 @ 0.1, WAS Ø9.1, 11	443566	AHJ	AHJ/OMS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33276570](#)