




ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT	-	---	---	---	---	---	---	---	---	---	---	---	---	---	---
33342277	01	CODE A	ALL PARTS VO / 34,0	-	1	---	1	---	---	---	---	---	---	1	1	---	1	---
33342279	01	CODE B		-	1	---	---	1	---	---	---	---	---	1	1	---	1	---
33342280	01	CODE C		-	1	---	---	---	1	---	---	---	---	1	1	---	1	---
33342281	01	CODE D		-	1	---	---	---	---	1	---	---	---	1	1	---	1	---
33347876	01	CODE A	ALL PARTS NVO / 33,0	-	---	1	---	---	---	1	---	---	---	1	---	1	---	1
33347893	01	CODE B		-	---	1	---	---	---	---	1	---	---	1	---	1	---	1
33348731	01	CODE C		-	---	1	---	---	---	---	---	1	---	1	---	1	---	1
33348732	01	CODE D		-	---	1	---	---	---	---	---	---	1	1	---	1	---	1



NOTES					
- ON MAIN VIEW ASSEMBLY 33342277 SHOWN (CODE A)					
- DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK AND SLIDER IN OPEN POSITION					
ASSEMBLY INSTRUCTION NO.:					
35269106-CUS71 - PRELIMINARY ASSEMBLY					
35269106-CUS72 - HARNESS ASSEMBLY					
35269103-CUS73 - CAR ASSEMBLY					
35269102-CUS73 - CAR ASSEMBLY					
MATING PARTS:					
- 18 WAY 1.5 MALE PANEL MOUNT ASM DWG-NO.: 35195557					
- 18 WAY 1.5 MALE STRAP MOUNT ASM DWG-NO.: 35195558					
- BACKSHELL 90 DEG APTIV DWG-NO.: 35024552					
- (HT DWG-NO.: 17-2277-001-CSG)					
- BACKSHELL 180 DEG APTIV DWG-NO.: 35024553					
- (HT DWG-NO.: 17-1491-001-CSG)					
- PROTECTION CAP APTIV DWG-NO.: 35149890					
- (HT DWG-NO.: 17-2268-001-CSG)					
MATING TERMINAL SYSTEM:					
- 1.5 TERMINAL DWG-NO.: 15432214					
MAX WIRE CROSS SECTION: 1.0MM²					
RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE					
- CROSS SECTION 1.5MM² - USE COMBINATION:					
TE TERMINAL: MCP 1.5, DWG NO.: 1418884-3					
SEAL: 964972-1					
MAX INSULATION CRIMP DIMENSIONS:					
HEIGHT: 3.40; WIDTH: 3.30					
1	APTIV LOGO				
2	MATERIAL NAME ACCORDING TO VDA 260				
3	TOOL CAVITY NUMBER				
4	PART CAVITY NUMBER				
5	MOVING DISTANCE OF SECONDARY LOCK				
6	MOVING DISTANCE OF SLIDER				

DIMENSIONAL RANGE (MM)	FROM	TO	1	2	3	4	5	6	7	8	9	10	11	12
> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	> 500	> 600	> 700	> 800	> 900
±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	±1.5	±2	±2.5	±3	±4	±5

SCALE:
1:1



DWG. TYP.	PART DRAWING	DISTR. CODE
WEIGHT (GR)	SEE CHART	
VOLUME (CM³)	---	
ROUTING		
UNLESS OTHERWISE SPECIFIED		
GENERAL TOLERANCES ACCORDING TO:		
SEE CHART		
GD&T ACCORDING TO:		
ISO 1101		
REFERENCE		
FIRST ANGLE PROJECTION		
DO NOT SCALE		
USE MATH DATA		

• APTIV •			
CONNECTION SYSTEMS KRAKOW, POLAND			
COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.			
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.			
TEN RYSUNEK JEST WŁASNOŚCIĄ APTIV I ZAWIERA PEŁNĄ INFORMACJĘ POWIĘLANĄ, ROZPOWISZCZANĄ I WYKORZYSTYWANĄ. TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANYCH INNYM JAKIEKOLWIEK ICH ZAWARTOŚCI, BEZ NADANIA WYRAŹNYCH UPRAWNIEN, JEST ZABRONIONE.			
DR	A.RAJEEV	DATE	27N018
APVD1	P.NAJDUCH	28N018	
APVD2	M.GRUDZEWSKI	29N018	
APVD3			
APVD4			
APVD5			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001 SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIIE PRZETWORZONE OKREŚLA APTIV 10949001			
MATERIAL			
SEE CHART			
DRAWING NAME			
18 WAY 1.5 CTCS FEMALE ASSEMBLY			
DRAWING NUMBER			
35195559			
SIZE	A1	SCALE	2:1
FRAME NO	1 OF 1	SHEET NO	1 OF 1
STG	R	REV	01
N/P	AB		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[33342277](#)