









35665780	01	COPPER	$\varnothing 5.63 \pm 0.1$	SILVER	M6488 4mm ²	0.092
35665796	01	COPPER	$\varnothing 5.33 \pm 0.1$	SILVER	M6488 3mm ²	0.091
35230978	01	COPPER	$\varnothing 5.90 \pm 0.1$	SILVER	JASO 3mm ²	0.093
35230980	01	COPPER	$\varnothing 6.13 \pm 0.1$	SILVER	M6488 5mm ²	0.094
35230979	02	COPPER	$\varnothing 5.63 \pm 0.1$	SILVER	M6488 4mm ²	0.092
35226475	01	COPPER	$\varnothing 5.33 \pm 0.1$	SILVER	M6488 3mm ²	0.091
PART NO	REV	MATERIAL	DIM. - A	PLATING	CABEL SIZE	VOLUME CM ³

A8
A8

SYMBOL DEFINITION

A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.

TOTAL NO OF
INSPECTIONS
REQUIRED

6




LAST NO.
USED

6

MISSING SYMBOLS

NO MISSING
SYMBOL NUMBER

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD1	APVD2
DATE	STG	REV	N/P	CHG						
23SE19	R	01	-	-		CREATED PART DRAWING	444580	WZM	TY	WZM
16DE19	R	02	-	-		UPDATED ATTRIBUTE	444947	WZM	TY	WZM
09AU22	R	03	-	-	A8	ADDED PART NUMBERS- 35665796 & 35665780	447992	VA	DY	TY



SECTION A - A

NOTES:

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. THIS PART USED IN ASSEMBLY DRAWING: 35214364.
3. PLATING:



UNDERPLATE: THICKNESS OF NICKEL SHALL BE
1.5 μ m - 4 μ m PER ASTM B-689, TYPE 1, CLASS X.
OVERPLATE: THICKNESS OF SILVER SHALL BE 3 μ m-6 μ m PER
ASTM B-700, TYPE 3, GRADE B, CLASS N.
ANTI TARNISH TREATMENT PER DELPHI M5815 SPECIFICATION
REQUIREMENTS. ANY COATING BRAND OTHER THAN EVABRITE
MUST BE APPROVED BY APITV.

4. PART MUST BE FREE OF MICRO CRACK, BURRS, SHARP EDGE, OIL, GREASE OR OTHER CONTAMINANTS.
5. ALL DIMENSIONS ARE AFTER PLATING.
6. COMPONENTS MUST BE PACKAGED IN A SEALED BAG.

5 PROCESS SENSITIVE DIMENSION

DIMENSIONS ENCLOSED IN () INDICATE
REFERENCE DIMENSIONS AND NO TOLERANCE
LIMITS ARE ESTABLISHED

DIMENSIONAL RANGE (MM)								CHART M	
FROM TO	> 0 6	> 6 30	> 30 70	> 70 120	> 120 160	> 160 200	> 200 250	> 250 315	> 315 400
TOLERANCE UNLESS OTHERWISE SPECIFIED									
	+0.1	+0.2	+0.3	+0.4	+0.45	+0.55	+0.7	+0.85	+1.05
ANGULAR TOLERANCE ±1°									

LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT ACTIV SALES TO ASSURE AVAILABILITY OF PARTS.	
DWG TYPE	
PART DRAWING	
STYLE	
VOLUME (CM³)	DISTR CODE 
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-2009, SEE DELPHI ENGINEERING DESIGN STANDARD B6.1017 FOR ISO 1101:2004 RECONCILIATION REQUIREMENTS.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION 	DO NOT SCALE USE MATH DATA  

• A P T I V •									
Copyright 2019 APTIV. ALL RIGHTS RESERVED.									
CHennai, India									
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINING APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.									
								DATE	
DR									
APVD1		WENZHENG MA						23SE19	
APVD2		TIMON YU						23SE19	
APVD3		WENZHENG MA						23SE19	
APVD4									
APVD5									
SUBSTANCES OF CONCERN AND RECYCLED CONTENT MATERIAL 10949001									
MATERIAL SEE CHARTS									
DRAWING NAME									
TAXI SLEV BUSHING ID= OD=									
DRAWING NUMBER									
35242832									
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P			
A1	10:1	1 OF 1	1 OF 1	R	03				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35230980](#)