









35665780	01	COPPER	$\varnothing 5.63 \pm 0.1$	SILVER	M6488 4mm ²	0.092
35665796	01	COPPER	$\varnothing 5.33 \pm 0.1$	SILVER	M6488 3mm ²	0.091
35230978	01	COPPER	$\varnothing 5.90 \pm 0.1$	SILVER	JASO 3mm ²	0.093
35230980	01	COPPER	$\varnothing 6.13 \pm 0.1$	SILVER	M6488 5mm ²	0.094
35230979	02	COPPER	$\varnothing 5.63 \pm 0.1$	SILVER	M6488 4mm ²	0.092
35226475	01	COPPER	$\varnothing 5.33 \pm 0.1$	SILVER	M6488 3mm ²	0.091
PART NO	REV	MATERIAL	DIM. - A	PLATING	CABEL SIZE	VOLUME CM ³

SYMBOL DEFINITION

A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL
 DOES NOT REQUIRE INSPECTION. IT MAY BE
 CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.

TOTAL NO OF
INSPECTIONS
REQUIRED

6




LAST NO.
USED

6

MISSING SYMBOLS

NO MISSING
SYMBOL NUMBER

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD1	APVD2
DATE	STG	REV	N/P	CHG						
23SE19	R	01	-	-		CREATED PART DRAWING	444580	WZM	TY	WZM
16DE19	R	02	-	-		UPDATED ATTRIBUTE	444947	WZM	TY	WZM
09AU22	R	03	-	-	A8	ADDED PART NUMBERS- 35665796 & 35665780	447992	VA	DY	TY



SECTION A - A


NOTES:

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. THIS PART USED IN ASSEMBLY DRAWING: 35214364.
3. PLATING:

UNDERPLATE: THICKNESS OF NICKEL SHALL BE
1.5 μ m - 4 μ m PER ASTM B-689, TYPE 1, CLASS X.
OVERPLATE: THICKNESS OF SILVER SHALL BE 3 μ m-6 μ m PER
ASTM B-700, TYPE 3, GRADE B, CLASS N.
ANTI TARNISH TREATMENT PER DELPHI M5815 SPECIFICATION
REQUIREMENTS. ANY COATING BRAND OTHER THAN EVABRITE
MUST BE APPROVED BY APITV.

4. PART MUST BE FREE OF MICRO CRACK, BURRS, SHARP EDGE, OIL, GREASE OR OTHER CONTAMINANTS.
5. ALL DIMENSIONS ARE AFTER PLATING.
6. COMPONENTS MUST BE PACKAGED IN A SEALED BAG.

		5		PROCESS SENSITIVE DIMENSION	
		DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)		CHART M			
FROM	>	>	>	>	>
	6	30	120	160	250
	6	30	120	160	250
TOLERANCE UNLESS OTHERWISE SPECIFIED					
	+0.1	+0.2	+0.3	+0.4	+0.5
ANGULAR TOLERANCE ±1°					

LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT SALES TO ASSURE AVAILABILITY OF PARTS.	
DWG TYPE	
PART DRAWING	
STYLE	
VOLUME (CM ³)	DISTR CODE
	D
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-2009, SEE DELPHI ENGINEERING DESIGN STANDARD 06-2017 FOR ISO 1101:2004 RECONCILIATION REQUIREMENTS.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE
	USE MATH DATA
	 

• APTIV •									
CONNECTION SYSTEMS Chennai, India COPYRIGHT 2019 APTIV. ALL RIGHTS RESERVED.									
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA DATA, AS WELL AS COMMUNICATION OF THIS DOCUMENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.									
								DATE	
DR									
APVD1		WENZHENG MA					23SEP19		
APVD2		TIMON YU					23SEP19		
APVD3		WENZHENG MA					23SEP19		
APVD4									
APVD5									
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001									
MATERIAL SEE CHARTS									
DRAWING NAME TAXI SLEV BUSHING ID= 0D=									
DRAWING NUMBER 35242832									
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P			
A1	10:1	1 OF 1	1 OF 1	R	03				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35230979](#)