





|                                           |                                                                                                 |                  |                   |                    |                     |                      |                      |
|-------------------------------------------|-------------------------------------------------------------------------------------------------|------------------|-------------------|--------------------|---------------------|----------------------|----------------------|
| DIN ISO 2768                              | Tolerance Class Fine (m)                                                                        |                  |                   |                    |                     |                      |                      |
| Linear Dimensions except for broken edges | Permissible deviations for basic size range (mm)                                                |                  |                   |                    |                     |                      |                      |
|                                           | 0.5 *) up to 3                                                                                  | over 3 up to 6   | over 6 up to 30   | over 30 up to 120  | over 120 up to 400  | over 400 up to 1000  | over 1000 up to 2000 |
|                                           | ±0.1                                                                                            | ±0.1             | ±0.2              | ±0.3               | ±0.5                | ±0.8                 | ±1.2                 |
| Broken edges (radii, chamfers)            | Permissible deviations for basic size range (mm)                                                |                  |                   |                    |                     |                      |                      |
|                                           | 0.5 *) up to 3                                                                                  | over 3 up to 6   | over 6 up to 30   | over 30 up to 120  | over 120 up to 400  | over 400 up to 1000  | over 1000 up to 2000 |
|                                           | ±0.2                                                                                            | ±0.2             | ±0.5              | ±0.5               | ±1                  | ±1                   | ±1                   |
| Angular dimensions                        | Permissible deviations for ranges of lengths, in mm, of the shorter side of the angle concerned |                  |                   |                    |                     |                      |                      |
|                                           | up to 10                                                                                        | over 10 up to 50 | over 50 up to 120 | over 120 up to 400 | over 400 up to 1000 | over 1000 up to 2000 | over 2000 up to 4000 |
|                                           | ±1°                                                                                             | ±0° 30'          | ±0° 20'           | ±0° 10'            | ±0° 5'              | ±0° 5'               | ±0° 5'               |


\*) For nominal sizes below 0.5mm, the deviations shall be indicated adjacent to the relevant nominal sizes).

| TYPE        | ASSEMBLY | CODING TYPE | HOUSING  |         | TPA      |            | INTERFACE SEAL (RED) | CPA             |
|-------------|----------|-------------|----------|---------|----------|------------|----------------------|-----------------|
|             |          |             | P/N0     | COLOR   | P/N0     | COLOR      |                      |                 |
| WITH CPA    | 33318607 | A           | 33318615 |         | 33401229 | ROYAL BLUE | 33376563             | 33219398 (GRAY) |
|             | 33318608 | B           | 33318616 | BLACK   | 33401230 | BROWN      |                      |                 |
|             | 33318609 |             | 33318617 |         | 33401231 | LT GRAY    |                      |                 |
|             | 35072591 | C           | 35076902 | LT GRAY | 35076903 | BLACK      |                      |                 |
|             | 33318610 | D           | 33318618 | BLACK   | 33401232 | RED        |                      |                 |
|             | 35335595 | A           | 33318615 |         | 33401229 | ROYAL BLUE |                      |                 |
|             | 35335596 | B           | 33318616 | BLACK   | 33401230 | BROWN      |                      |                 |
|             | 35335597 | C           | 33318617 |         | 33401231 | LT GRAY    |                      |                 |
|             | 35335598 | D           | 33318618 |         | 33401232 | RED        |                      |                 |
|             | 33318611 | A           | 33318615 |         | 33401229 | ROYAL BLUE |                      |                 |
| WITHOUT CPA | 33318612 | B           | 33318616 | BLACK   | 33401230 | BROWN      | -                    | -               |
|             | 33318613 | C           | 33318617 |         | 33401231 | LT GRAY    |                      |                 |
|             | 35072592 |             | 35076902 | LT GRAY | 35076903 | BLACK      |                      |                 |
|             | 33318614 | D           | 33318618 | BLACK   | 33401232 | RED        |                      |                 |



| CABLE SEAL |             |                 |                 |               |            |                 |
|------------|-------------|-----------------|-----------------|---------------|------------|-----------------|
| TYPE       | PART NUMBER | MVL PART NUMBER | WIRE SIZE (mm²) | INSULATION(Ø) | COLOR      | MATERIAL        |
| LONG       | 33513680    | F310400         | 0.3 ~ 0.35      | 1.2 ~ 1.5     | RED        | SILICONE RUBBER |
|            | 33511838    | F410400         | 0.5 ~ 0.85      | 1.6 ~ 1.9     | GRAY       |                 |
|            | 33513681    | F599700         | 1.0 ~ 1.5       | 2.0 ~ 2.4     | YELLOW     |                 |
| SHORT      | 33318278    | -               | 0.3 ~ 0.35      | 1.2 ~ 1.6     | GRAY       | SILICONE RUBBER |
|            | 33318279    | -               | 0.5 ~ 0.85      | 1.6 ~ 1.9     | LIGHT GRAY |                 |
|            | 33318275    | -               | 1.0 ~ 1.5       | 1.9 ~ 2.4     | BLACK      |                 |
| LONG       | 33268526    | -               | 0.3 ~ 0.35      | 1.2 ~ 1.5     | BLUE       | FLUORO SILICONE |
|            | 33366680    | -               | 0.3 ~ 0.35      | 1.2 ~ 1.6     | BLUE       |                 |
|            | 33366681    | -               | 0.5 ~ 0.85      | 1.6 ~ 1.9     | GREEN      |                 |
| SHORT      | 33366679    | -               | 1.0 ~ 1.5       | 1.9 ~ 2.4     | BROWN      | FLUORO SILICONE |

| SYMBOL DEFINITION                                                                                                                      |                                   | MISSING SYMBOLS          |  |
|----------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------|--------------------------|--|
| A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING. | TOTAL NO. OF INSPECTIONS REQUIRED | NO MISSING SYMBOL NUMBER |  |
|                                                                                                                                        | 4                                 |                          |  |
|                                                                                                                                        | LAST NO. USED                     |                          |  |
|                                                                                                                                        | 4                                 |                          |  |



| ISOMETRIC VIEW |                    |                    |
|----------------|--------------------|--------------------|
|                | CODE A (SCALE 2:1) | CODE A (SCALE 2:1) |
| OPTION         | WITH CPA           | WITHOUT CPA        |
|                |                    |                    |
| DELPHI         | PART NUMBER        | 33318607 35335595  |
|                | PART REVISION      | 01                 |

| ASSOCIATED PARTS    |             |                 |           |
|---------------------|-------------|-----------------|-----------|
| FEMALE TERMINAL     | PART NUMBER | WIRE SIZE (mm²) | TYP (AWG) |
| TIN                 | 54001864    | 0.75 ~ 1.25     | 16        |
|                     | 54002006    | 0.3 ~ 0.5       | 20        |
| SILVER STRIPE, SPOT | F731400     | 0.75 ~ 1.25     | 16        |
|                     | F931400     | 0.3 ~ 0.5       | 20        |
| GOLD STRIPE, SPOT   | 54001863    | 0.75 ~ 1.25     | 16        |
|                     | 54002005    | 0.3 ~ 0.5       | 20        |
| TIN SILVER          | 54001866    | 0.75 ~ 1.25     | 16        |
|                     | 54002007    | 0.3 ~ 0.5       | 20        |

| DWG STATUS |     | ZONE |     | REVISION HISTORY |                                                                 | AUTH |     | DR  |     | APVD |  |
|------------|-----|------|-----|------------------|-----------------------------------------------------------------|------|-----|-----|-----|------|--|
| DATE       | STG | REV  | N/P | CHG              |                                                                 |      |     |     |     |      |  |
| 11JA16     | R   | 01   | -   | -                | INITIAL RELEASE                                                 | -    | KBK | KBK | PJH |      |  |
| 15JL16     | R   | 02   | -   | -                | INTERFACE SEAL DESIGN MODIFIED HOUSING LATCH DESIGN MODIFIED    | -    | SYK | JJY | PJH |      |  |
| 19OC16     | R   | 03   | -   | D5               | ADDED CABLE SEAL PART NUMBER                                    | -    | SYK | JJY | PJH |      |  |
| 07NO16     | R   | 04   | -   | -                | ADDED DUMMY SEAL (DARK GRAY)                                    | -    | SYK | JJY | PJH |      |  |
| 09JN17     | R   | 05   | -   | -                | ADDED HOUSING COLOR (GRAY) / TPA COLOR (BLACK)                  | -    | SYK | SJW | PJH |      |  |
| 06DE17     | R   | 06   | -   | -                | ADDED NOTES 5, MODIFIED TABLE OF CABLE SEAL, DELETED DUMMY SEAL | -    | SYK | SJW | PJH |      |  |
| 08AP19     | R   | 07   | -   | -                | ADDED PART NO. WITH NEW CPA (LT GRAY)                           | -    | SYK | SJW | PJH |      |  |

NOTES:

- TOLERANCE MUST MEET DIN ISO 2768(m)
- TEST SPECIFICATION PER HKMC : ES91500-00
- ALLOWED WIRE RANGE : 0.3mm² TO 1.25mm² (JASO WIRE)
- APPLICABLE TERMINAL : APEX1.2 FEMALE TERMINAL
- APPLICABLE MATERIAL OF SEAL IS ONLY SILICONE RUBBER FOR HKMC

DWG TYP: PART DRAWING

WEIGHT (GRI):

VOLUME (CM³):

ROUTING:

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES ACCORDING TO:

GD&T ACCORDING TO:

REFERENCE:

THIRD ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA

•APTIV•

CONNECTION SYSTEMS

Copyright 2016 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

|       |                |      |        |
|-------|----------------|------|--------|
| DR    | KIM, BEOM KYU  | DATE | 11JA16 |
| APVD1 | KIM, BEOM KYU  |      | 11JA16 |
| APVD2 | KIM, BEOM KYU  |      | 11JA16 |
| APVD3 | PARK, JOO HYUN |      | 11JA16 |
| APVD4 |                |      |        |
| APVD5 |                |      |        |

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001

MATERIAL:

DRAWING NAME: 2WAY FEMALE ASSEMBLY

DRAWING NUMBER: 33318603

|      |      |       |     |          |        |          |        |     |   |     |    |     |   |
|------|------|-------|-----|----------|--------|----------|--------|-----|---|-----|----|-----|---|
| SIZE | A2x3 | SCALE | 4:1 | FRAME NO | 1 OF 2 | SHEET NO | 1 OF 1 | STG | R | REV | 07 | N/P | - |
|------|------|-------|-----|----------|--------|----------|--------|-----|---|-----|----|-----|---|



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33318612](#)