












NOTES:	
1. Modèle représenté en gamme 2 (1.4 à 2mm²) Model display in range 2 (1.4 to 2mm²)	
2. (xx) Côte non tolérancée, pour information (xx) No toleranced dimension, given for information	
3. Conditionement: PU 131 Packaging: PU 131	
4. Specification de sertissage: FE-CS 14-006 Crimping specification: FE-CS 14-006	
NOMBRE DE DIMENSIONS NUMEROTEES QUANTITY OF NUMBERING DIMENTIONS	
54	
Numéro non utilisé Numbering not used	
5-9 16-19 34-39 44-49 58-59 65-69	
Dernier numéro utilisé last number used	
76	

8		7		6		5									
ETAT / STATE		REFERENCES / PART-NUMBERS													
		SIDE BY SIDE				SWS		SIDE BY SIDE		SWS		SIDE BY SIDE		SWS	
Pré-étamé / Pre-tinned 1 to 3 µm Sn		33400435	01	33501792	01	35174381	01	33512109	01	35174382	01	33512190	01	35174383	01
Post-argenté/Post-silvered 3 to 5 µm Ag		33405986	01	33405987	01	/		33405988	01	/		33405989	01	/	
Post-doré / Post gilded 0.4µm Au		33405985	01	33522699	01	/		33522701	01	/		33522703	01	/	
Post-doré / Post gilded 0.80µm Au		35330156	01	35330157	01	/		35330158	01	/		35330159	01	/	
Poids sans bande porteuse Weight without strip (gr)		0.29		0.32				0.34				0.36			
Gamme / Range		0		1				4				2			
Section / Gauge		0.13 To 0.22		0.35 To 0.70				0.75 To 1.30				1.40 To 2.00			
Ø Isolant / Ø Insulation		0.95 To 1.35		1.25 To 1.70				1.60 To 2.30				2.00 To 2.90			
A±0.2		1.75		2.60				2.75				3.10			
Al±0.2		1.60		/				/				/			
B±0.2		1.70		2.20				2.86				3.50			
Bl±0.2		1.50		/				/				/			
C±0.2		0.31		0.75				0.75				0.75			
D±0.3 Mesurande		2.10		3.05		4.30		3.72		4.50		4.60		5.00	
E±0.2		1.90		3.03		4.15		3.71		4.50		4.60		4.70	
F±0.2		0.61		0.80		1.35		1		1.35		1.30		1.35	
K		-0.10		0.35		-0.35		-0.05		-0.50		-0.5		-0.60	
L		0.20		0.45		0.45		0.30		0.30		0.20		0.20	



DWG STATUS		ZONE		REVISION HISTORY		AUTH		DR		APVD		APVD	
DATE	STG	REV	N/P	CHG									
13AP18	R	01			FILE TRANSLATED FROM MVL SYSTEM REBRANN IN NX ADDED SWS TERMINAL			L.DOM	S.BOS	P.CAP			
03JN19		02			UPDATED SWS WINGS (D MESURANDE; SIZE 28b) ADDED GOLD VERSION (THICKNESS 1.27 µm Au)			L.DOM	S.BOS	P.CAP			
31JL19		02	AA		UPDATED SWS WINGS (DIMENSION D) REMOVED POST GILDED 1.27 µm Au			L.DOM	S.BOS	P.CAP			
14OC19		02	AB		ADDED POST GILDED 0.80µm Au			L.DOM	S.BOS	P.CAP			
31JA20		02	AC		RELEASED GILDED TERMINAL P/N 35330157/ 35330158			L.DOM	A.ELM	S.BOS			
28AP20		02	AD		ADDED SHEET 3			L.DOM	A.ELM	S.BOS			



• APTIV •

CONNECTION SYSTEMS
Eperron, France
COPYRIGHT 2014 APTIV. ALL RIGHTS RESERVED.
THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND
UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL
AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS
AUTHORIZATION, IS PROHIBITED.

CE PLAN EST LE PROPRIETE DE DELPHI CORPORATION ET CONTIENT DES
INFORMATIONS DELPHI CONFIDENTIELLES. LA REPRODUCTION, LA DISTRIBUTION
ET L'UTILISATION DE CE DOCUMENT OU DE SES DONNEES MATHÉMATIQUES CAO,
AINSI QUE LA COMMUNICATION DE TOUT CONTENU À AUTRUI, SANS AUTORISATION
EXPRESSE EST INTERDITE.

DR	L DOMERGUE	DATE	04FE13
APVD1	F FAURIE		22AU14
APVD2	S LACOTE		22AU14
APVD3	Patrice CAPPE		22AU14
APVD4			
APVD5			

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
MATIERES PROSCRITES ET CONTENU RECYCLABLE SEION
DELPHI 10949001

MATERIAL
SEE TABLE

DRAWING NAME
1.5 X 0.8 MALE TERMINAL

SICMA 4

DRAWING NUMBER
33521740

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	5:1	1 OF 1	1 OF 1	R	02	AD

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35174382](#)