









ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33343499	01	CODE A	ALL PARTS V0 / 24,4
33343508	01	CODE B	
33343688	01	CODE C	
33343686	01	CODE D	
33350336	01	CODE A	ALL PARTS NVO / 23,7
33350418	01	CODE B	
33350416	01	CODE C	
33350413	01	CODE D	

POSITION	1		2								3	4		5	
NAME	HOUSING		INSERT								HOUSING SEAL	SECONDARY LOCK		SLIDER	
MATERIAL	PBT GF30 FR17	PBT GF30	PBT GF30 FR17				PBT GF30				LSR 50 SHORE	PBT GF30 FR17	PBT GF30	PBT GF30 FR17	PBT GF30
COLOR:	BLACK	BLACK	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	REDDISH-BROWN	ORANGE	YELLOW	ORANGE	YELLOW
PART-NO.:	33338835	33349754	33342254	33342255	33342256	33342258	33349768	33349764	33349760	33349755	33339449	33342246	33350091	33338837	33350047
-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
-	1	-	1	-	-	-	-	-	-	-	1	1	-	1	-
-	1	-	-	1	-	-	-	-	-	-	1	1	-	1	-
-	1	-	-	-	1	-	-	-	-	-	1	1	-	1	-
-	1	-	-	-	-	1	-	-	-	-	1	1	-	1	-
-	-	1	-	-	-	-	1	-	-	-	1	-	1	-	1
-	-	1	-	-	-	-	-	1	-	-	1	-	1	-	1
-	-	1	-	-	-	-	-	-	1	-	1	-	1	-	1
-	-	1	-	-	-	-	-	-	-	1	1	-	1	-	1


DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
06DE18	R	01				INITIAL RELEASE		K.FAR	P.NAJ	M.GRU
15MR19	R	01	AA		B7	REFERENCE HELLERMANN TYTON DWG-NO. ADDED		K.FAR	M.GRU	K.PIT
11FE20	R	01	AB		G11	PART AVAILABILITY FOR PART NUMBERS 33350336, 33350418, 33350416, 33350413 UPDATED		P.NAJ	M.GRU	



NOTES	
-	ON MAIN VIEW ASSEMBLY 33343499 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK AND SLIDER IN OPEN POSITION
ASSEMBLY INSTRUCTION NO.:	
-	35269106-CUS71 - PRELIMINARY ASSEMBLY
-	35269106-CUS72 - HARNESS ASSEMBLY
-	35269103-CUS73 - CAR ASSEMBLY
-	35269102-CUS73 - CAR ASSEMBLY
MATING PARTS:	
-	8 WAY 2.8 MALE STRAP MOUNT ASM DWG-NO.: 35123487
-	BACKSHELL 90 DEG APTIV DWG-NO.: 33390631 (HT DWG-NO.: 17-2276-001-CSG)
-	BACKSHELL 180 DEG APTIV DWG-NO.: 33390632 (HT DWG-NO.: 17-1486-001-CSG)
-	PROTECTION CAP APTIV DWG-NO.: 35149888 (HT DWG-NO.: 17-2267-001-CSG)
MATING TERMINAL SYSTEM:	
-	2.8 TERMINAL DWG-NO.: 15446676
-	MAX WIRE CROSS SECTION: 2.5MM ²
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	TOOL CAVITY NUMBER
4	PART CAVITY NUMBER
5	MOVING DISTANCE OF SECONDARY LOCK
6	MOVING DISTANCE OF SLIDER

		DIMENSIONAL RANGE (MM)									CHART E1	
DIM TO CHECK	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	> 400	
	TO	20	30	70	100	150	200	250	300	400		
DIM FOR HELP	TOLERANCE UNLESS OTHERWISE SPECIFIED											
		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2		
THEORETIC DIM	ANGULAR TOLERANCE ±2°											

DWG. TYP	PART DRAWING	DISTR. CODE	D
WEIGHT (GRI)	SEE CHART		
VOLUME (CM ³)	---		
ROUTING			
UNLESS OTHERWISE SPECIFIED			
GENERAL TOLERANCES ACCORDING TO:			
SEE CHART			
GD&T ACCORDING TO:			
ISO 1101			
REFERENCE			
FIRST ANGLE PROJECTION			
DO NOT SCALE			
USE MATH DATA			



• APTIV •

CONNECTION SYSTEMS

KRAKOW, POLAND

COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WŁASNOŚCIĄ APTIV I ZAWIERA PEŁNĄ INFORMACJĘ POWIĘLANĄ, ROZPOWISZCZANĄ I WYKORZYSTYWANĄ. TEGO DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH CAD, JAK RÓWNIEŻ PRZEKAZYWANIE INNYM JAKIEJKOLWIEK ICH ZAWARTOŚCI BEZ NADANIA WYRAŹNYCH UPRAWNIEN, JEST ZABRONIONE.

			DATE
DR	K.FARON		05DE18
APVD1	P.NAJDUCH		06DE18
APVD2	M.GRUDZEWSKI		07DE18
APVD3			
APVD4			
APVD5			
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001 SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIIE PRZETWORZONE OKREŚLA APTIV 10949001			
MATERIAL			
SEE CHART			
DRAWING NAME			
8 WAY 2.8 CTCS FEMALE ASSEMBLY			
DRAWING NUMBER			
35123486			
SIZE	A1	SCALE	2:1
FRAME NO	1 OF 1	SHEET NO	1 OF 1
STG	R	REV	01
N/P	AB		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33343499](#)