


CAVITY	TERMINAL	CROSS SECTION	PART-NO.:	MATERIAL	SURFACE
7-10	MTS 0.64	0.35-0.5 mm <sup>2</sup>	15440183	X12CrNi 177 CuNiSi	AU
11-32	MTS 0.64	0.35-0.5 mm <sup>2</sup>	15440179	X12CrNi 177 CuNiSi	SN


PART-NO.:	PART-REV	DATE	MATERIAL	SIMILAR TO RAL
15536566	02	26FE19	PBT-GF20 BLK	9011

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
07MR13	R	01				INITIAL RELEASE		P.LES	M.MLE	M.SKR
26FE19	R	02	--		E6	LOCKING FEATURE CHANGED		K.ZDZ	P.LES	M.SKR



PART CAVITY NUMBER / FORMAT  
ACCORDING TO DIN 1451; H=1.0 MM;  
LETTERS 0.15 MM RECESSED



TOOL CAVITY NUMBER / FORMAT  
ACCORDING TO DIN 1451; H=1.2 MM  
LETTERS 0.15 MM RAISED



DATE INSERT SIMILAR FIRM HASCO Z 485/6/1;  
HAS TO BE THE MANUFACTURING DATE



MATERIAL NAME ACCORDING TO VDA 260 /  
FORMAT ACCORDING TO DIN 1451; H=1.6 MM


**REMARKS:**

- MAXIMUM DRAFT ANGLE 0°30'
- LETTERS AND ENGRAVINGS 0.1 MM RAISED  
SIGN PLANE 0.1 MM RECESSED
- SPC : STATISTICAL PROCESS CONTROL
- MATING PARTS:  
COVER+LEVER 32 WAY DWG-NO.: 15536575


A LINE DRAWN THROUGH A PART NUMBER  
INDICATES THAT PHYSICAL PARTS ARE NOT  
AVAILABLE FOR ORDERING.

PART NUMBERS THAT DO NOT HAVE A LINE  
PRESENT INDICATE THAT PHYSICAL PARTS  
ARE AVAILABLE FOR ORDERING.

CONTACT APTIV SALES TO ASSURE  
AVAILABILITY OF PARTS.



SCALE:  
1 : 1



DWG TYP PART DRAWING		DISTR CODE
WEIGHT (GR)	3.86	D
VOLUME (CM <sup>3</sup> )	2.61	
ROUTING		


UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES  
ACCORDING TO:  
SEE CHART


GD&T  
ACCORDING TO:  
ISO 1101

REFERENCE

FIRST ANGLE PROJECTION



DO NOT  
SCALE  
USE MATH  
DATA



# • APTIV •

CONNECTION SYSTEMS  
KRAKOW, POLAND

COPYRIGHT 2013 APTIV. ALL RIGHTS RESERVED.  
**REVISED 2013**

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV  
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND  
UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL  
AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS  
AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WLASNOSCIA APTIV I ZAWIERA POUFNE  
INFORMACJE POWIELANIE, ROZPOWSZECHNIANIE I WYKORZYSTYWANIE TEGO  
DOKUMENTU LUB ZWIAZANYCH Z NIM DANYCH CAD, JAK ROWNIEZ PRZEKAZYWANIE  
INNYM JAKIEJKOLWIEK ICH ZAWARTOSCI, BEZ NADANIA WYRAZNYCH  
UPRAWNIEN, JEST ZABRONIONE

		DATE
DR	P.LESNIAK	06MR13
APVD1	M.MLECZKO	07MR13
APVD2	M.SIKORA	08MR13
APVD3		
APVD4		
APVD5		

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001  
SUBSTANCJE NIEBEZPIECZNE I POWTORNIE PRZETWORZONE OKRESLA  
APTIV 10949001

MATERIAL  
SEE CHART

DRAWING NAME  
INSERT MTS 0.64 FOR RECEPTACLE HOUSING  
32 WAY FOR VOLVO

DRAWING NUMBER  
**15536567**

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A2	5:1	1 OF 1	1 OF 1	R	02	

KEY PRODUCT CHARACTERISTICS					
	SAFETY/COMPLIANCE		FIT/FUNCTION	TOTAL ON DRAWING	0
	S/C CHECKPOINTS		F/F CHECKPOINTS	LAST NO. USED	0
NO & TYPE	DESCRIPTION	RATIONALE		PTS	ZONE
-	-	-		-	-

DIM TO CHECK	DIMENSIONAL RANGE (MM)										CHART	E1	
	FROM	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300			
( ) DIM FOR HELP	TO	20	30	70	100	150	200	250	300	400			
<input type="checkbox"/> THEORETIC DIM		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2			
		TOLERANCE UNLESS OTHERWISE SPECIFIED											
		ANGULAR TOLERANCE ±2°											

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15536566](#)