














NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SURFID FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
2. THIS PART USED IN ASSEMBLY SEE CHART.
3. SUITABLE TERMINAL SYSTEM CTS/MCON/MLK 1.2 LL.
4. MAX. WIRE SIZE RANGE 1.0 MM2. FOR CAVITY-Ø 3.55MM.
5. ASSEMBLY MANUAL REFER TO 35126449-CUS72-S01.
6. INTERFACE REFER TO USCAR-EWCAP 120-S-003-1-201/202.
7. FOR APPLICATION DATA SEE THE INDIVIDUAL APPLICATION DRAWINGS.

[illegible]

DIMENSIONAL RANGE (MM)								CHART M	
FROM	> 0	> 6	> 30	> 70	> 120	> 160	> 200	> 250	> 315
TO	6	30	70	120	160	200	250	315	400
TOLERANCE UNLESS OTHERWISE SPECIFIED									
	±0.1	±0.2	±0.3	±0.4	±0.45	±0.55	±0.7	±0.85	±1.05
ANGULAR TOLERANCE ±'									

NOTES THAT PHYSICAL PARTS ARE NOT AVAILABLE
FOR ORDERING

ITEMS THAT DO NOT HAVE A LINE PRESENT INDICATE
THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING,
BUT MAY BE ORDERED SEPARATELY TO ASSURE AVAILABILITY
PARTS.

DATE AND TIME
FILE NO.

PART DRAWING

LINE CODE DISTR CODE

UNLESS OTHERWISE SPECIFIED

THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-1994
AND THE FIRST ANGLE OF ORIENTATION AND
PERSPECTIVE OR CROSS SECTION. SEPARATE PATTERNS OF
LINES MAY BE ORDERED SEPARATELY REGARDLESS OF DATA
PERFECTNESS.

ALL DIMENSIONS ARE IN MILLIMETERS

FIRST ANGLE PROJECTION

DISTR CODE

USE MATH DATA

NX

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35126370](#)