






ASSEMBLY-NO.:	PART-REV	CODING	MATERIAL/WEIGHT
33342277	01	CODE A	ALL PARTS V0 / 34,0
33342279	01	CODE B	
33342280	01	CODE C	
33342281	01	CODE D	
33347876	01	CODE A	ALL PARTS NVO / 33,0
33347893	01	CODE B	
33348731	01	CODE C	
33348732	01	CODE D	

POSITION	1		2								3	4		5	
NAME	HOUSING		INSERT								HOUSING SEAL	SECONDARY LOCK		SLIDER	
MATERIAL	PBT GF30 FR17	PBT GF30	PBT GF30 FR17				PBT GF30				LSR 50 SHORE	PBT GF30 FR17	PBT GF30	PBT GF30 FR17	PBT GF30
COLOR:	BLACK	BLACK	BLACK	GRAY	GREEN	BLUE	BLACK	GRAY	GREEN	BLUE	REDDISH-BROWN	ORANGE	YELLOW	ORANGE	YELLOW
PART-NO.:	33283299	33347534	33325413	33325415	33325414	33325416	33347490	33347493	33348057	33348109	33285522	33325394	33347489	33283297	33347474
-	---	---	---	---	---	---	---	---	---	---	---	---	---	---	---
-	1	---	1	---	---	---	---	---	---	---	1	1	---	1	---
-	1	---	---	1	---	---	---	---	---	---	1	1	---	1	---
-	1	---	---	---	1	---	---	---	---	---	1	1	---	1	---
-	1	---	---	---	---	1	---	---	---	---	1	1	---	1	---
-	---	1	---	---	---	---	1	---	---	---	1	---	1	---	1
-	---	1	---	---	---	---	---	1	---	---	1	---	1	---	1
-	---	1	---	---	---	---	---	---	1	---	1	---	1	---	1
-	---	1	---	---	---	---	---	---	---	1	1	---	1	---	1

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
28NO18	R	01				INITIAL RELEASE		A.RAJ	P.NAJ	M.GRU
15MR19	R	01	AA		B6	REFERENCE HELLERMANN TYTON DWG-NO. ADDED		K.FAR	M.GRU	K.PIT
27OC20	R	01	AB		G11 B6	PART AVAILABILITY FOR PART NUMBERS 33347876, 33347893, 33348731, 33348732 UPDATED NOTES UPDATED		P.NAJ	M.GRU	



SCALE:
1 : 1




NOTES	
-	ON MAIN VIEW ASSEMBLY 33342277 SHOWN (CODE A)
-	DELIVERED CONDITION AS ON MAIN VIEWS - SECONDARY LOCK AND SLIDER IN OPEN POSITION
-	ASSEMBLY INSTRUCTION NO.: 35269106-CUS71 - PRELIMINARY ASSEMBLY 35269106-CUS72 - HARNESS ASSEMBLY 35269103-CUS73 - CAR ASSEMBLY 35269102-CUS73 - CAR ASSEMBLY
-	MATING PARTS: - 18 WAY 1.5 MALE PANEL MOUNT ASM DWG-NO.: 35195557 - 18 WAY 1.5 MALE STRAP MOUNT ASM DWG-NO.: 35195558 - BACKSHELL 90 DEG APTIV DWG-NO.: 35024552 (HT DWG-NO.: 17-2277-001-CSG) - BACKSHELL 180 DEG APTIV DWG-NO.: 35024553 (HT DWG-NO.: 17-1491-001-CSG) - PROTECTION CAP APTIV DWG-NO.: 35149890 (HT DWG-NO.: 17-2268-001-CSG)
-	MATING TERMINAL SYSTEM: - 1.5 TERMINAL DWG-NO.: 15432214 MAX WIRE CROSS SECTION: 1.0MM ² RECOMMENDATION FOR 1.5 TERMINAL WITH WIRE CROSS SECTION 1.5MM ² - USE COMBINATION: TE TERMINAL: MCP 1.5, DWG NO.: 1418884-3 SEAL: 964972-1 MAX INSULATION CRIMP DIMENSIONS: HEIGHT: 3.40; WIDTH: 3.30
1	APTIV LOGO
2	MATERIAL NAME ACCORDING TO VDA 260
3	TOOL CAVITY NUMBER
4	PART CAVITY NUMBER
5	MOVING DISTANCE OF SECONDARY LOCK
6	MOVING DISTANCE OF SLIDER

A LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.

PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.

CONTACT APTIV SALES TO ASSURE AVAILABILITY OF PARTS.



☐ DIM TO CHECK	DIMENSIONAL RANGE (MM)										CHART E1																		
	FROM TO	> 0 20	> 20 30	> 30 70	> 70 100	> 100 150	> 150 200	> 200 250	> 250 300	> 300 400																			
☐ DIM FOR HELP	TOLERANCE UNLESS OTHERWISE SPECIFIED																												
☐ THEORETIC DIM	<table><tr><td>+0.15</td><td>+0.2</td><td>+0.3</td><td>+0.4</td><td>+0.5</td><td>+0.6</td><td>+0.8</td><td>+1</td><td>+1.2</td></tr><tr><td colspan="9">ANGULAR TOLERANCE ±2°</td></tr></table>											+0.15	+0.2	+0.3	+0.4	+0.5	+0.6	+0.8	+1	+1.2	ANGULAR TOLERANCE ±2°								
+0.15	+0.2	+0.3	+0.4	+0.5	+0.6	+0.8	+1	+1.2																					
ANGULAR TOLERANCE ±2°																													

DWG TYP PART DRAWING		DISTR CODE D
WEIGHT (GR)	D	
SEE CHART		
VOLUME (CM³)		

ROUTING		

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:
SEE CHART

GD&T
ACCORDING TO:
ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT
SCALE
USE MATH
DATA

CAD

 NX

• **A P T I V** •

CONNECTION SYSTEMS
KRAKOW, POLAND

COPYRIGHT 2018 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND
UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL
AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS
AUTHORIZATION, IS PROHIBITED.

TEN RYSUNEK JEST WŁASNOŚCIĄ APTIV I ZAWIERA POUFNE
INFORMACJE. POWIELANIE, ROZPOWSZECZANIE I WYKORZYSTYWANIE TEGO
DOKUMENTU LUB ZWIĄZANYCH Z NIM DANYCH C.A.D., JAK RÓWNIEŻ PRZEKAZYWANIE
INNYM JAKIEJKOLWIEK ICH ZAWARTOŚCI, BEZ NADANIA WYRAZNYCH
UPRAWNIENI, JEST ZABRONIONE

	DATE
DR A. RAJEEV	27N018
APVD1 P. NAJDUCH	28N018
APVD2 M. GRUDZEWSKI	29N018
APVD3	
APVD4	
APVD5	

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV 10949001
SUBSTANCJE NIEBEZPIECZNE I POWTÓRNIĘ PRZETWORZONE OKRESŁA
APTIV 10949001

SEE CHART

DRAWING NAME

18 WAY 1.5
CTCS FEMALE ASSEMBLY

DRAWING NUMBER

35195559						
SIZE A1	SCALE 2:1	FRAME NO 1 OF 1	SHEET NO 1 OF 1	STG R	REV 01	N/P AB

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33342280](#)