







SYMBOL DEFINITION		MISSING SYMBOLS	
	A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	12
		LAST NO. USED	10


DWG STATUS					ZONE		REVISION HISTORY			AUTH	DR	APVD	APVD
DATE	STG	REV	N/P	CHG									
29JL05	R	01	-	-			15459045 - MOVED TO TAXI; ALL PARTS - RELEASED			270573	AKJ	AKJ	RC
04NO05	R	02	-	-			ALL PARTS - ADDED TYPE 101			273978	MM	MM	RC
12JL06	R	03	-	-			ALL PARTS - UPDATED PDM ATTRIBUTES			282292	MM	MM	RC
28AU06	R	04	-	-			15429045 - ADDED 13549070 RESISTOR & REMOVED 15455931 TERM/RESISTOR ASM 13534887 - RESISTOR WAS 13534629; 13534888 - RESISTOR WAS 13534630; 13534889 - RESISTOR WAS 13534631; 13534890 - RESISTOR WAS 13534632; 13534891 - RESISTOR WAS 13534633; 13534892 - RESISTOR WAS 13534634; 13534893 - RESISTOR WAS 13534635; 13534894 - RESISTOR WAS 13534636; 13534895 - RESISTOR WAS 13534637; ALL PARTS - REMOVED TERM/RESISTOR ASM HEADER FROM THE CHART			283575	EES	EES	GR
20SE06	R	05	-	-			ALL PARTS - UPDATED PDM ATTRIBUTES			284867	JTZ	FRG	REB
11JN07	R	06	-	-			ALL PARTS - REVISED TERMINAL GRAPHICS TO LATEST REVISION			401644	RH	RH	GR
10SE08	R	07	-	-			ALL PARTS - ADDED SLEEVE 13662530 TO ASM			405877	JS	JS	KDM
17SE10	R	08	-	-			ALL PARTS - SLEEVE P/N 13816192 WAS 13662530			411972	AGM	JVM	JCO
27MY11	R	09	-	-			13853078 & 13853079 - RELEASED			414404	FPE	RGC	FPE
20JL11	R	10	-	-			ALL PARTS - SLEEVE WAS 13816192			414858	HRS	HRS	VMR
29JL11	R	11	-	-			ALL PARTS - SLEEVE WAS 13662530			414977	HRS	HRS	QAF
24OC11	R	12	-	-			13923432 & 13924569 - RELEASED			415734	AJP	JAA	DAB
07NO11	R	13	-	-			13923432 - REVISED			416077	DAB	PTB	DAB
03FE12	R	14	-	-			13924569 - REVISED			416975	EGH	EGH	EGH
22JA13	R	15	-	-			15510071 - RELEASED; 13923432 & 13853078 - UPDATED PART AVAILABILITY			421178	JTV	JTV	EDA
28MR13	R	16	-	-			15510071 - UPDATED PART AVAILABILITY			421939	EDA	EDA	EDA
09SE14	R	17	-	-			33183322, 33183323 - RELEASED			427519	AHG	MEA	MEA
03SE15	R	18	-	-			33284011 - RELEASED 13924569 - WAS TYPE 103			430755	AHY	AHY	JFF
03AP18	R	19	-	-			35199153 - RELEASED			439413	GDH	JAA	LMV
19JN18	R	20	-	-			35199153 - UPDATED PART AVAILABILITY			440190	JGO	JAA	LMV
21MY19	R	21	-	-			35351504 - RELEASED			443326	AHG	AHG	DS
13FE20	R	22	-	-			35351504 - UPDATED PART AVAILABILITY			551003	AHY	AHY	DS



TYPE 102  
SAME AS TYPE 101 EXCEPT  
AS SHOWN



TYPE 101



#### NOTES

- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION. (SEE MATH MODEL FOR PRECISE DIMENSIONS.) FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

- REFERENCE MATING COMPONENTS OR EQUIVALENT:

CONNECTOR 13510085  
TERMINAL 15326426, FEMALE TERMINAL MUST HAVE GOLD PLATED TERMINAL CONTACT AREA.

- MATERIAL RECYCLING CODE PER ISO 11469. (2,3)X(0,1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.

- CORPORATE BRAND TO BE APPLIED TO PRODUCT DESIGN PER THE LATEST REVISION OF ESD S1085201.

- THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-CS-01.

35351504	01	AA	102	15455930	13589068	13816192	7320	-	POLYESTER COMPOUND GRAY	6.182
35199153	01	AA	102	15455930	35199148	13816192	499	-	POLYESTER COMPOUND BLACK	6.182
33284011	01	-	102	15455930	33277834	13816192	39	-	POLYESTER COMPOUND GRAY	6.182
33183323	01	AA	102	15455930	33183321	13816192	-	1200	POLYESTER COMPOUND BLACK	5.859
33183322	01	AA	102	15455930	33183320	13816192	-	2700	POLYESTER COMPOUND BLACK	5.859
15510071	01	AB	102	15455930	15510135	13816192	2700	-	POLYESTER COMPOUND BLACK	5.859
13924569	01	AC	102	15455930	13921531	13816192	18	-	POLYESTER COMPOUND BLACK	5.859
13923432	02	AB	102	15455930	13923431	13816192	8	-	POLYESTER COMPOUND BLACK	5.859
13853079	01	AC	102	15455930	13853076	13816192	39	-	POLYESTER COMPOUND GRAY	5.859
13853078	01	AD	102	15455930	13853075	13816192	3,000	-	POLYESTER COMPOUND BLUE	5.859
13534895	04	AE	102	15455930	13589069	13816192	12,700	-	POLYESTER COMPOUND BLACK	5.859
13534894	04	AE	102	15455930	13589068	13816192	7320	-	POLYESTER COMPOUND BLACK	5.859
13534893	04	AE	102	15455930	13589067	13816192	3160	-	POLYESTER COMPOUND BLACK	5.859
13534892	04	AE	102	15455930	13589066	13816192	1820	-	POLYESTER COMPOUND BLACK	5.859
13534891	04	AE	102	15455930	13589065	13816192	1150	-	POLYESTER COMPOUND BLACK	5.859
13534890	04	AE	102	15455930	13589064	13816192	715	-	POLYESTER COMPOUND BLACK	5.859
13534889	04	AE	102	15455930	13589063	13816192	453	-	POLYESTER COMPOUND BLACK	5.859
13534888	04	AE	102	15455930	13589062	13816192	255	-	POLYESTER COMPOUND BLACK	5.859
13534887	04	AE	102	15455930	13589061	13816192	115	-	POLYESTER COMPOUND BLACK	5.862
15429045	04	AE	101	15455930	13589070	13816192	121	-	POLYESTER COMPOUND BLACK	5.846
PART NO	REV	N/P	TYPE	TERMINAL	RESISTOR	SLEEVE (2 PLCS)	RESISTANCE VALUE (OHMS ± 1%)	RESISTANCE VALUE (OHMS ± 5%)	MATERIAL SPECIFICATION AND COLOR	VOLUME CM³

DIMENSIONAL RANGE (MM)		TOLERANCE UNLESS OTHERWISE SPECIFIED						CHART E		
FROM	TO	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300
		20	30	70	100	150	200	250	300	400
TOLERANCE UNLESS OTHERWISE SPECIFIED										
		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2
AND A-2 TOLERANCE ±0.2										

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)  
[13534895](#)