








NOTE	SPECIFICATIONS
1	FEMALE CONNECTOR ACCORDING TO APTIV SPECIFICATION: CAQE TBD
2	FEMALE CONNECTOR ACCORDING TO: -TEMPERATURE CLASS TX -ENGINE VIBRATOR CLASS VX -SEALING CLASS EX
3	USER'S MANUAL: 13543894-CUS74-S01
4	DELIVERY CONNECTOR WEIGHT : SEE TABLE
5	NO WAFER HINGE OR WAFER HINGE BROKEN ALLOWED
6	VISUAL DEFECTS ON NO FUNCTIONNAL AREAS ALLOWED
△	MATERIAL NAME
△	TOOL CAVITY NUMBER
△	INDEX REPLACEMENT INSERT
△	PART CAVITY NUMBER
△	SUPPLIER LOGO
△	REPLACEMENT INSERT BLANK
△	DATE INSERT

DWG. TYP CUSTOMER PART DRAWING	
WEIGHT (GR)	DISTR CODE
SEE CHART	D
VOLUME (CM³)	
ROUTING	
UNLESS OTHERWISE SPECIFIED	
GENERAL TOLERANCES ACCORDING TO: SEE CHART	
GD&T ACCORDING TO: ISO 1101	
REFERENCE	
FIRST ANGLE PROJECTION	
DO NOT SCALE USE MATH DATA	

• APTIV •

CONNECTION SYSTEMS
Chennai, India
COPYRIGHT 2021 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND
UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL
AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS
AUTHORIZATION, IS PROHIBITED.

DR	P.BALAJI	DATE	18N021
APVD1	LAGUETTE MAURICE		18N021
APVD2	LAGUETTE MAURICE		18N021
APVD3			
APVD4			
APVD5			


SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV
10949001

MATERIAL
SEE TABLE

DRAWING NAME
RECEPTACLE HOUSING 2 WAY
FOR MQS 0.63


DRAWING NUMBER
13543894

SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	5:1	1 OF 1	1 OF 1	R	01	



ASSOCIATED PARTS (FOR INFORMATION)						
DESCRIPTION	APTIV P/N	WIRE SECTION	DIAMETER OF WIRE SIZE			
MATING PART	13543904	-	-			
MQS 0.63 FEMALE TERMINAL	-	0.75mm²	1.9			
RECEPTACLE HOUSING 2 WAY	D	1	13543893	0.0067	PBT GF10	VIOLET
	C	1	13543891	0.0067	PBT GF10	BLUE
	A	2	13605737	0.0067	PBT GF10	YELLOW
	A	2	13605736	0.0067	PBT GF10	BLACK
	A	1	13543888	0.0067	PBT GF10	YELLOW
DESCRIPTION	CODE	VERSION	APTIV PART NUMBER	WEIGHT (kg)	MATERIAL	COLOR

○ DIM TO CHECK	DIMENSIONAL RANGE (MM)	CHART	E1
FROM TO	> 0 > 20 > 30 > 70 > 100 > 150 > 200 > 250 > 300 > 400		
1) DIM FOR HELP			
□ THEORETIC DIM	±0.15 ±0.2 ±0.3 ±0.4 ±0.5 ±0.6 ±0.8 ±1 ±1.2		
	TOLERANCE UNLESS OTHERWISE SPECIFIED		
	ANGULAR TOLERANCE ±2°		



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13605736](#)