

Technical drawing of the 'L' model lamp, showing front and side views with dimensions.

Front View (Left): Shows the lamp's profile with a height dimension of (17.3).

Side View (Right): Shows the lamp's depth with a width dimension of (12.5) and a height dimension of 13.8. A detail callout (25.2) is shown at the top right.

• **AP**
 2017

SECONDARY LOCKING
 IN END LOCKED POSITION
 ZWEITE KONTAKTSICHERUNG
 IN ENDRASTSTELLUNG



SCALE / MASSSTAB:
 2:1

SCALE / MASSSTAB: 2:1

33.55

15.25

6.3



26.JUL22	R	02	AD	613 614	DIW./ MASS. 13.8. KODED/ HINZUG: REASON: KODED/ FOLGERUNG HINZUG - WISSUNG DIMENSION.../ FEHLERDE BEWASSUNG...	C.ELI	O.HAC	SYS
----------	---	----	----	------------	--	-------	-------	-----

SCALE / MASSSTAB:

1
•
1

DWG TYPE		DISTR CODE
PART DRAWING		
WEIGHT (GR)	D	
2.2		
VOLUME (CM³)		

ROUTING		

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:

SEE CHART
SIEHE TABELLE

GD&T
ACCORDING TO:

ISO 1101

10/10

REFERENCE
PART DRAWING

FIRST ANGLE PROJECT

DO NOT SCALE

USE MATH DATA	U
---------------	---

• **APTIV** •

CONNECTION SYSTEMS
D-42119 WUPPERTAL

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAIN
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIB
UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH D
AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT

AUTHORIZATION, IS PROHIBITED.

DIESE ZEICHNUNG IST EIGENTUM DER FIRMA APTIV UND ENTHÄLT
VERTRAULICHE INFORMATIONEN. DIE REPRODUKTION, VERTEILUNG
ODER NUTZUNG DIESES DOKUMENTES ODER DEREN ZUGEHÖRIGEN CAD-DATEN
OHNE EINE SCHRIFTLICHE BERECHTIGUNG VON APTIV WIRD ALS
VERGEGENSTÄNDLICHE VERLETZUNG ANGESEHEN. FÜR WEITERE
DETAILS ZU DEN RECHTSMÄSSIGEN VERFAHRENEN, DIE APTIV
GEGEN VERLETZUNGEN EINLEITET, SIEHE DIE APTIV UNZULÄSSIGKEITEN-
POLITIK.

DR	W. TARNAWSKI	1
APVDI	O. HACKEL	18

APVD2	M.SIKORA	2
APVD3		
APVD4		

APVD5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV POTENTIELL GEFÄHRLICHE STOFFE UND REZYKLATANT GEMAESS APTIV 10949001	

MATERIAL	SEE CHART / SIEHE TABELLE
----------	---------------------------

DRAWING NAME

TAB HOUSING 4 WAY
FOR MTS 0.64

FLACHSTECKERGEHAEUSE 4 POL
FUER MTS 0.64

DRAWING NUMBER
1 354 39 36

SIZE A0	SCALE 5:1	FRAME NO 1 OF 1	SHEET NO 1 OF 1	STO R
------------	--------------	--------------------	--------------------	----------

REMARKS:

- KEYING A / OPTION 1 DRAWN
- DELIVERY STATUS AS DRAWN
- LETTERS AND ENGRAVINGS RAISED
- SIGN PLANE RECESSED
- SPC: STATISTICAL PROCESS CONTROL
- MAXIMUM CABLE CROSS SECTION 0.75 MM²
- MAXIMUM INSULATION CABLE DIAMETER 1.9 MM
- TERMINAL: MICRO TERMINAL SYSTEM 0.64;
- BASIC APPLICATION SEE DWG-NO.: 1350602
- MATING PART:
- RECEPTACLE HOUSING 4 WAY DWG-NO.: 13543933

BEMERKUNGEN:

- CODIERUNG A / VARIANTE 1 GEZEICHNET
- ANLIEFERUNGSGUSTZUSTAND WIE GEZEICHNET
- SCHRIFTEN UND GRAVUREN ERHABEN
- SCHRIFTFLÄCHE VERTIEFT
- SPC: STATISTISCHE PROZESSKONTROLLE
- MAX. ZULÄSSIGER LEITUNGSÜBERSCHREIT 0,75 MM²
- MAX. AUSSENDURCHMESSER (ISOLIERUNG) 1,9 MM
- ① - KONTAKTSYSTEM: MICRO TERMINAL SYSTEM 064;
STANDARD SYSTEM SIEHE ZCHG-NR.: 13580602
- PASSENDES GEGENSTÜCK:
FLACHTECHHÜLLSENGEHÄUSE 4 POL., ZCHG-NR.: 13543933

				SHARP CORNER TOLERANCE							
☐ DIM TO CHECK PRIEMASSE	DIMENSIONAL RANGE (MM)								CHART		
	FROM TO	> 0 20	> 20 30	> 30 70	> 70 100	> 100 150	> 150 200	> 200 250	> 250 300		
☐ DIM FOR HELP HILFSSASSE	TOLERANCE UNLESS OTHERWISE SPECIFIED										
☐ THEORETIC DIM THEORE. MASSE		±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1		
ANGULAR TOLERANCE 12°											

CONTROLLED DOCUMENTS ARE ONLY AVAILABLE ON THE SERVER

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[33120609](#)