


3						2		1			
DWG STATUS						ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG							
24N021	R	01				INITIAL RELEASE		P.BAL	M.LAG	M.LAG	

3D VIEW



SCALE 1:1

DWG. TYP		D
CUSTOMER PART DRAWING		
WEIGHT (GR)	DISTR CODE	
SEE CHART		
VOLUME (CM ³)		

ROUTING		

UNLESS OTHERWISE SPECIFIED

GENERAL TOLERANCES
ACCORDING TO:

SEE CHART

GD&T
ACCORDING TO:

ISO 1101

REFERENCE

FIRST ANGLE PROJECTION

DO NOT SCALE

USE MATH DATA	CA	NX
---------------	----	----

•A P T I V•

CONNECTION SYSTEMS

Chennai, India

COPYRIGHT 2021 APTIV. ALL RIGHTS RESERVED.

THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV
CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND
UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL
AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS
AUTHORIZATION, IS PROHIBITED.

DR		P.BALAJI		DATE		
APVD1		LAGUETTE MAURICE		24N021		
APVD2		LAGUETTE MAURICE		24N021		
APVD3						
APVD4						
APVD5						
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER APTIV J0949001						
MATERIAL						
SEE CHART						
DRAWING NAME						
COVER 10 WAY FOR MTS AND MQS 0.63						
DRAWING NUMBER						
13543547						
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P
A1	5:1	1 OF 1	1 OF 1	R	01	




NOTE	SPECIFICATIONS
1	FEMALE CONNECTOR ACCORDING TO APTIV SPECIFICATION: CAGE TBD
2	FEMALE CONNECTOR ACCORDING TO: -TEMPERATURE CLASS TX -ENGINE VIBRATOR CLASS VX -SEALING CLASS EX
3	USER'S MANUAL: 13590051-CUS76-S01
4	DELIVERY CONNECTOR WEIGHT : SEE TABLE
5	NO WAFER HINGE OR WAFER HINGE BROKEN ALLOWED
6	VISUAL DEFECTS ON NO FUNCTIONNAL AREAS ALLOWED
	MATERIAL NAME
	TOOL CAVITY NUMBER
	INDEX REPLACEMENT INSERT
	PART CAVITY NUMBER
	SUPPLIER LOGO
	REPLACEMENT INSERT BLANK
	DATE INSERT

		SHAFT CORNER TOLERANCE										
		CHART E										
☐ DIM TO CHECK	DIMENSIONAL RANGE (MM)	FROM TO	> 0	> 20	> 30	> 70	> 100	> 150	> 200	> 250	> 300	
☐ DIM FOR HELP	TOLERANCE UNLESS OTHERWISE SPECIFIED											
☐ THEORETIC DIM			±0.15	±0.2	±0.3	±0.4	±0.5	±0.6	±0.8	±1	±1.2	
		ANGULAR TOLERANCE ±2°										

ASSOCIATED PARTS (FOR INFORMATION)	
DESCRIPTION	APTIV P/N
MATING PART	13590063
INSERT 10 WAY FOR MTS/MQS 0.63	13543543

COVER 10 WAY	E	13567789	0.0013	PBT GF20	GREEN
	D	13567788	0.0013	PBT GF20	VIOLET
	C	13567787	0.0013	PBT GF20	BLUE
	B	13567786	0.0013	PBT GF20	NATURE
	A	13543546	0.0013	PBT GF20	BLACK
DESCRIPTION	CODE	APTIV PART NUMBER	WEIGHT (kg)	MATERIAL	COLOR

COVER 10 WAY	
APTIV P/N	CODING
13543546	CODING - A
13567786	CODING - B
13567787	CODING - C
13567788	CODING - D
13567789	CODING - E



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[13567786](#)