




SYMBOL DEFINITION		MISSING NUMBERS
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF SYMBOLS ON DRAWING	8
	LAST NO. USED	8

DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR	APVD1	APVD2
DATE	STG	REV	N/P						
170C00	R	21	-	-	ALL ACTIVE PARTS - ADDED REVISION COLUMN PER 148574	204031	RVP	RVP	RC
03AU04	R	22	-	-	02977253 - MAT'L SPEC WAS R-67550; 02973778 - MAT'L SPEC WAS PM-661-001; & 06288219 - MAT'L SPEC WAS R-71753; ALL ACTIVE PARTS - REVISED NOTES	257213	TLD	TLD	ET
27SE05	R	23	-	-	06288219 - MAT'L SPEC WAS M3592002	272768	CCV	FRG	ET
12MR07	R	24	-	-	06288219 - OBSOLETE	400766	JBD	JAA	JBS



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - MATERIAL RECYCLING CODE PER ISO 11469. (.080)X(.004) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
 - REFERENCE MATING COMPONENTS OR EQUIVALENT:
CONNECTOR 02973779
 - (.080)X(.004) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.
 - ENVIRONMENTAL PROTECTION ACCORDING TO OPEL SPECIFICATION QU 000 001-CADMIUM

06288219	08	AA	OBSOLETE	M3592024 PA66 HS IM CRM	-
02989922	G	-	OBSOLETE	R-67662 - A.B.S. (NAT)	MUST BE MADE IN MOLD #M-1
02977253	08	-	-	M2097001 PP IM BLK	SEE NOTE #5
02973778	08	-	-	M2097002 PP IM NAT	-
PART NO	REV	N/P	STATUS	MATERIAL SPECIFICATION AND COLOR	REMARKS

(N/A) PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (IN)	CHART H
FROM 0 TO .750	>.750 >1.250 >2.750 >4.000
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±.005 ±.010 ±.012 ±.016 ±.020	
ANGULAR TOLERANCE ±2°	

DWG TYPE
PART DRAWING

STYLE


VOLUME (CM³)
DISTR CODE
D

UNLESS OTHERWISE SPECIFIED
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2018 GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.

ALL DIMENSIONS ARE IN INCHES

THIRD ANGLE PROJECTION

DO NOT SCALE
USE MATH DATA



DELPHI
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE
WARREN, OH

DR

DATE

APVD1 TOM MUDREY 21N060

APVD2 DON THIRY 04AU66

APVD3 LUBERT 10AU66

APVD4

APVD5

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001

MATERIAL
SEE CHART

DRAWING NAME
TAXI CONN F 56 SERIES

DRAWING NUMBER
02977252

SIZE A1

SCALE NONE

FRAME NO 1 OF 1

SHEET NO 1 OF 1

STG R

REV 24

N/P -

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[02977253-B](#)