




MISSING SYMBOLS
NO MISSING SYMBOL NUMBER

	H
b	
c	
d	
e	



2X 6
2X 2.52 +0.3 TYP

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

1. AUSTEMPER TO ROCKWELL "15N" 81.5 - 83.5
2. ZINC PLATE AND CLEAR CHROMATE TREATMENT PER POS 1065-15 (GM-4345-M CODE 3K 32/8).
3. PLATE WITH 1 COAT STALGUARD BLACK (DRY). FINISH MUST WITHSTAND 400 HOURS MINIMUM TO RED RUST IN NEUTRAL SALT FOG EXCEPT FOR "SHARP" EDGES.
4. PLATE PER DX551245-P ZINC WITH CLEAR TRIVALENT CHROME AND TOPCOAT.

3		PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)		CHART 6	
FROM TO	0 12	> 12	
TOLERANCE UNLESS OTHERWISE SPECIFIED			
	±0.15	±0.3	
ANGULAR TOLERANCE ±2°			

DWG TYPE		PART DRAWING	
STYLE			
VOLUME (CM³)		DISTR CODE	
		D	
UNLESS OTHERWISE SPECIFIED			
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE GW GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE GAGED SEPARATELY REGARDLESS OF DATUM REFERENCES.			
ALL DIMENSIONS ARE IN MILLIMETERS			
REFERENCE			
THIRD ANGLE PROJECTION		DO NOT SCALE	
		  NX	
		USE MAT DATA	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[13571424](#)