







SYMBOL DEFINITION			MISSING SYMBOLS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.	TOTAL NO OF INSPECTIONS REQUIRED	13	NO MISSING SYMBOL NUMBER	
			LAST NO. USED	
			10	

CWS STATUS				REVISION HISTORY				AUTH		DR		APV/D	
DATE	STG	REV	W/R	CHG	ZONE								
20JN12	R	01	-	-		WAS PE235739 AND RELEASED PART DRAWING		418582	AHT	JAA	APR		
26JN12	R	01	AA	-		CREATED TOOL QUALIFICATION DRAWING		418662	AGM	AGM	APR		
06AU12	R	01	AB	-		REVISED GRAPHICS		419112	JCF	MAB	APR		
31AU12	R	01	AC	-		UPDATED PDM ATTRIBUTES		419502	APR	APR	APR		
06SE12	R	01	AD	-		UPDATED DIM (55.01) WAS 55.01, DIM (45.52) WAS 45.52, DIM (86.57) WAS 86.57, DIM (39.52) WAS 39.52, DIM (76.28) WAS 76.28, DIM (106.02) WAS 106.02, DIM (22) WAS 22, DIM (0.75) WAS 0.75, ADDED DIM 4X R 4.5 AND ADDED NOTE 3.		419567	APR	APR	APR		
20SE12	R	01	AE	-		UPDATED DELPHI LOGO & RECYCLING CODE POSITION & UPDATED NOTES		419720	APR	APR	APR		
05FE13	R	01	AF	-		UPDATED PDM ATTRIBUTES		421352	APR	APR	APR		



SECTION A - A



- NOTES
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:
DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION (SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
 - MATERIAL RECYCLING CODE PER ISO 11469. (2.3)X(0.1) CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE.
 - (2.3)X(0.1) DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION FOR EXISTING TOOLING MAY BE *PED*.
 - THIS PRODUCT IS NOT CATEGORIZED AS AN APPEARANCE ITEM, MINOR IMPERFECTIONS INCLUDING, BUT NOT LIMITED TO, FLOW MARKS, COLOR BLEMISHES, GATE VESTIGE, AND SOFT FLASH THAT DO NOT AFFECT THE FIT, FORM, OR FUNCTION OF THE PART ARE PERMISSIBLE PER DPNP-4.7-CS-01.
 - DIMS 10 & 8 MUST BE MEASURED WHILE GROMMET SITING ON TOP OF ASSM FORMED BY: 13781987 AND 15494614.

PROCESS SENSITIVE DIMENSION			
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED			
DIMENSIONAL RANGE (MM)	CHART	C	
FROM	>0	>25	>60
TO	25	60	80
TOLERANCE UNLESS OTHERWISE SPECIFIED			
±0.3 ±0.5 ±0.6 ±0.750			
ANGULAR TOLERANCE 12°			

THIRD ANGLE PROJECTION		DO NOT SCALE	
USE MATH DATA		NX	

DELPHI DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE WARREN, OH COPYRIGHT 2012 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DATE	
DR	
APV/D1	MA, ANTONIETA HDZ
APV/D2	J.S. ALVARADO
APV/D3	ALEJANDRA PAYAN
APV/D4	
APV/D5	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10944930	
MATERIAL ETHYLENE PROPYLENE DIENE BLACK	
DRAWING NAME GROM CONN	
DRAWING NUMBER 13957208	
SIZE	AD
SCALE	2:1
FRAME NO	1 OF 1
SHEET NO	1 OF 1
STG	R
REV	01
W/R	AF

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[13957208](#) [13957208-B](#)