








M
L
I
H
G
F
E
D
C
B
A


BODY HOLE FOR CONNECTOR
Durchgangslach fuer Steckverbinder



NOTES / Bemerkungen:	
1	COMPANY LOGOTYPE Firmenlogo
2	ASSEMBLY PART-NO. ; SEE TABLE Baugruppenteilnr.; siehe Tabelle
3	REVISION INDEX OF ASSEMBLY Teileaenderungsindex der Baugruppe
4	IDENTIFICATION OF MATERIAL ACC. TO VDA 260 Materialkennzeichnung nach VDA 260
5	DATE CLOCK Datumsuhr
6	MOLD CAVITY IDENTIFICATION Nestmarkierung
7	CAVITY IDENTIFICATION Kammer - Nummerierung
8	COUNTRY OF MANUFACTURE Herstellerland
9	MANUFACTURER CODE Herstellercode
10	ONLY THE GERMAN LANGUAGE SHALL BE BINDING Nur der deutsche Text ist bindend



3D VIEW / 3D Ansicht
M 1:1



DESIGNATION Benennung	MVL-PART-NO. MVL-Teilnr.	DELPHI-PART-NO. DELPHI-Teilnr.	WIRE CROSS SECTION [mm ²] Leitungsquerschnitt [mm ²]	MATERIAL / SURFACE Werkstoff / Oberflaeche	MVL-PART-NO. MVL-Teilnr.	DELPHI-PART-NO. DELPHI-Teilnr.	FOR INSULATION- Ø [mm] fuer Isolations- Ø [mm]	COLOR Farbe
4x FEMALE TERMINAL HPCS 2.8mm	Sn VERSIONS	-	-	-	6 099 40 07	10779160	BLIND PLUG Blindstopfen	GREEN gruen
		6 001 30 11	10789196	0.35	CONTACT BODY/ Grundkoerper: CuCrSiTi (K75) SURFACE/ Oberflaeche: 1-3µm Sn	6 099 40 15	1.2 - 2.0	BLUE blau
		6 001 30 31	10789197	0.5 - 1.0		6 099 40 23	2.0 - 2.7	RED-BROWN rotbraun
		6 001 30 41	10781054	1.5		6 099 40 34	2.7 - 2.9	YELLOW gelb
	Ag VERSIONS	-	-	-	HOOD/ Ueberfeder: X10 CrNi 18 8 / BLANK	6 099 40 15	1.2 - 2.0	BLUE blau
		6 001 33 12	33511491	0.35		6 099 40 23	2.0 - 2.7	RED-BROWN rotbraun
		6 001 33 32	33511957	0.5 - 1.0		6 099 40 34	2.7 - 2.9	YELLOW gelb
		6 001 33 42	13548633	1.5		6 099 40 15	1.2 - 2.0	BLUE blau
	SnTop VERSIONS	-	-	-	CONTACT BODY/ Grundkoerper: CuCrSiTi (K75) SURFACE/ Oberflaeche: 1-2µm Ag passivate	6 099 40 23	2.0 - 2.7	RED-BROWN rotbraun
		F125410	33515099	0.35		6 099 40 34	2.7 - 2.9	YELLOW gelb
		F225410	33515098	0.5 - 1.0		6 099 40 15	1.2 - 2.0	BLUE blau
		F325410	33515097	1.5		6 099 40 23	2.0 - 2.7	RED-BROWN rotbraun
	AgTop VERSIONS	-	-	-	HOOD/ Ueberfeder: X10 CrNi 18 8 / BLANK	6 099 40 34	2.7 - 2.9	YELLOW gelb
		F125410	33515099	0.35		6 099 40 15	1.2 - 2.0	BLUE blau
		F225410	33515098	0.5 - 1.0		6 099 40 23	2.0 - 2.7	RED-BROWN rotbraun
		F325410	33515097	1.5		6 099 40 34	2.7 - 2.9	YELLOW gelb

F391800	A	13853167	01	11.1	3	I	SEAL Dichtung	LSR SILICON	ORANGE Orange
					2	I	TPA Kontaktsicherung	PBT GF10	VIOLET violette
					1	I	4W FEMALE HOUSING 4pol. Buchsengehaeuse	PBT	BLACK schwarz
PART-NO. Teile-Nr.	REV. INDEX	PART-NO. Teile-Nr.	REV. INDEX	WEIGHT Gewicht [g]	ITEM Position	QUANTITY Menge	NAME Benennung	MATERIAL Material	COLOUR Farbe
MVL		DELPHI							

14-01461	-	INITIAL RELEASE
ECN-NO. ECN-NUMBER	POSITION	CHANGE DESCRIPTION AENDERUNGSBESCHREIBUNG
PRODUCT SPEC. PRODUKT-SPEZ.	PACKAGING SPEC. VERPACKUNGS-SPEZ.	APPLICATION SPEC. ANWENDUNGS-SPEZ.
COPYRIGHT DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISED THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS CONTENT OR ANY PART THEREOF, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED. DELPHI CORPORATION SHALL BE RESPONSIBLE FOR ANY VIOLATION OF THIS POLICY.		
TOLERANCES TOLERANZEN	±0.1	±2*
DATE DATUM	NAME NAME	TITLE TITEL
CREATED BY ERSTELLT VON	20140902	V CHOCKALINGAM
MODIFIED BY MODIFIZIERT VON	20140903	M WIELTHER
CHECKED BY GEPRUEFT VON	20140903	KHANS MUELLER
APPROVED BY GEBILDET VON	20140903	CHRISTOPHER KERN
FILE NAME DOK.-NAME	PCC078884	
4W SEALED FEMALE CONNECTOR		
4W SEALED FEMALE CONNECTOR		
PCC078884		
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE		
PCC078884		
SERIAL RELEASED		
None		

EUR COA 112 P23 PDS

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[F225410](#) [F325410](#)