


PARTIAL VIEW
SECTION A-A
UNSEALED CONSTRUCTION










SECTION A-A
SEALED CONSTRUCTION




SECTION B-B
FOR SEALED AND UNSEALED
CONSTRUCTION CORE GRIP




SECTION B-B
CORE GRIP
DOUBLE WIRE




SEALED CONSTRUCTION
SECTION C-C




SECTION C-C
UNSEALED CONSTRUCTION




SECTION C-C
UNSEALED CONSTRUCTION
DOUBLE WIRE




| | | | | | | | | | |
|---|---|---|---|---|---|---|---|---|---|
| 16 | .18 - .80 \| .50 | B | 4.45 \| 3.90 | D | Y | | | |
| 14 | .34 - 1.60 \| .50 | B | 4.45 \| 3.90 | D | Y | | | |
| 12 | .72 - 3.10 \| 2.65 | B | 5.13 \| 4.80 | D | Y | | | |
| 10 | 1.85 \| 2.45 | B | 6.10 \| 5.70 | D | Y | | | |
| 17 | .22 \| .22 \| 4.57 \| .65 | B | 3.68 \| 2.49 | B | N | | | |
| | .22 \| .50 \| 4.57 \| .70 | B | 3.68 \| 2.55 | B | N | | | |
| | .34 \| .22 \| 4.57 \| .65 | B | 4.00 \| 3.45 | B | N | | | |
| | .34 \| .50 \| 4.57 \| .80 | B | 4.00 \| 3.60 | B | N | | | |
| | .18 \| .50 \| 4.57 \| .80 | B | 4.25 \| 3.80 | B | N | | | |
| 16 | .18 - .80 \| .50 | D | 4.45 \| 3.90 | C | N | | | |
| | .34 - 1.60 \| .50 | D | 4.45 \| 3.90 | C | N | | | |
| 13 | .18 \| .18 \| 4.57 \| .70 | B | 4.68 \| 4.40 | B | N | | | |
| | .34 \| .18 \| 4.57 \| .70 | B | 4.68 \| 4.40 | B | N | | | |
| | .34 \| .34 \| 4.57 \| .70 | B | 4.68 \| 4.40 | B | N | | | |
| 12 | .72 - 3.10 \| 2.65 | B | 5.85 \| 5.30 | D | N | | | |
| 11 | --- | | | | | | | | |
| 10 | 1.85 \| 2.45 | B | 4.60 \| 3.70 | D | N | | | |
| GRIP CODE | WIRE SIZE | CM | CH | CRIMP STYLE | CM | CH | CRIMP STYLE | CABLE SEAL | |
| | | CONDUCTOR | | INSULATION | | | | | |
| | | CRIMP SPECIFICATIONS (MM) (REFERENCE ONLY) | | | | | | | |

• SEE CHARTED P/N'S FOR APPROPRIATE WIRE SPECIFICATION

SEE F.C. INTERLOCK PRODUCT EVALUATION LAB 44PC3 TERMINAL CRIMP GUIDELINES• FOR CRIMP HEIGHT, WIDTH AND PULL FORCE REQUIREMENTS. NOT CRIMPING TO THESE GUIDELINES MAY RESULT IN ELECTRICAL OR MECHANICAL FAILURES.

CRIMP TOLERANCES FOR BOTH CONDUCTOR AND INSULATION CRIMPS TO BE AS FOLLOWS:

CM CRIMP WIDTH ±0.08
CH CRIMP HEIGHT ± 0.05

CRIMP SPECIFICATIONS

## INSERTION AND REMOVAL FORCES

| | INSERTION | 1ST REMOVAL | 10TH REMOVAL |
|---|---|---|---|
| TERMINAL WITHOUT GREASE | (16.0-9.0 N) | 12.0 N MIN. | 12.0 N MIN. |
| TERMINAL WITH GREASE | (4-7.5 N) | 12.0 N MIN. | 12.0 N MIN. |

•INSERTION AND REMOVAL FORCES PER ABOVE CHART ARE TO BE TAKEN USING A CAVITY GAGE PER PF-2 INTERLOCK DWG. NO TO BE SPECIFIED). FORCE MEASUREMENTS TO BE TAKEN AUTOMATICALLY AT A RATE OF 10±4in/min USING MECHANICAL TESTING MACHINE. TERMINAL MUST BE HELD RIGIDLY IN PLACE AND ALLOW THE RECEPTACLE TERMINAL TO FLOAT FREELY PER F.C. INTERLOCK DWG. (TBD). GAGE BLADE MUST ENTER THE RECEPTACLE TERMINAL AT A MINIMUM 5.5mm

QUALITY ASSURANCE REQUIREMENTS PER CHRYSLER PS 7300: 2

④ INDICATES IN-PROCESS INSPECTION FOR MANUFACTURING DIMENSIONS† OR SPECIFICATIONS:

WIRING FABRICATORS MUST PURCHASE FROM SOURCES SHOWN.

CABLE SEALS SHOWN ON CHART DWG 64801100

CABLE SEALS TO BE PURCHASED FROM APPROVED SOURCES SHOWN LOCTITE/ LOCTITE CONNECTOR SEALS

ITEM ③ MATERIAL 0.25MM(0.010") C17200 TWO-TEMPER BERYLLIUM COPPER ALLOY. TENSILE STRENGTH 413-482 Mpa ELONGATION 1N 51 mm: 20 MIN.

ITEM ④ MATERIAL 0.254MM(0.010") C70260 TWO-TEMPER NICKEL SILICON COPPER ALLOY. TENSILE STRENGTH 482-551 Mpa ELONGATION 1N 51 mm: 15 MIN.

THIS DRAWING REPLACES DAIMLER CHRYSLER DRAWING 64801083.

VIEW NOT TO SCALE

PACKAGING: PANCAKE REELS WITH PAPER INTERLEAF

NOTE: CUSTOMER REQUEST FOR REWIND PARTS WILL INCLUDE AN "RWC" AT THE END OF THE PART NUMBER. EXAMPLE: 14-0.5 BLU-SPT-RWC JMS-1025-709MC-OPTION 2

THIS PART NUMBERING SYSTEM WILL BE AVAILABLE FOR ALL B.O.M. PART NUMBERS CHARTED TO THE LEFT IN CHART.

EXCEPTION TO PF-9600

1. TERMINAL IS RATED AT 50 AMPS @ 55°ROA OPEN BENCH TESTED PER PF-752.
2. TERMINAL IS RATED AT 31 AMPS @ 20°ROA PER PF-9600.




MATING BLADE VIEW

| CHARTED CABLE SEALS | | | | | |
|---|---|---|---|---|---|
| 18 | E0001906 | X-1053-005 | YELLOW | MIL-I23A | WS-8288 |
| 16 | E0001905 | X-1053-004 | ORANGE | MIL-I23A | WS-8288 |
| 14 | E0001904 | X-1053-003 | LT. BLUE | MIL-I23A | WS-8288 |
| 12 | 7158-3136-60 | X-1067-002 | GREEN | MIL-I23A | WS-8288 |
| 10 | E0001902 | X-1053-001 | RYL BLUE | APPROVED WIRE SPEC. | APPROVED WIRE SPEC. |
| WIRE SIZE | FEDRAL PART NO. | J.S.T. PART NO. | COLOR | FORD | CHRYSLER |

| | | | | | | | | |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Aptiv:

54001623 54001623-L