



Chrysler


CODING A / POPULATED TO VARIANT CONN. IV PIN CAVITY: CLOSED BOSCH PART NUMBER: 6002600212 FCI PART NUMBER: F38220 Au Plating THICKNESS 0.5 μm MIN.		Mechanical Code For Header									
		CODE STATUS	I	V	V	II	II	I	I	I	I
		Dim "X"	0	0	0	0	0	0	0	0	0
FCI Mating Component Part No	Description	Key Code									
F847100	104 Way Terminal Carrier Holder and Wire Dress Cover with Lever	A									
F571710	32 Way Terminal Carrier Left										
F471710	32 Way Terminal Carrier Right										
F781710	20 Way Terminal Carrier Holder with CPN	A									
F061710	20 Way Terminal Carrier										



CODE B / POPULATED 70		Mechanical Code For Header	
VARIANT CONN_VI		CODE	V I V I I I I I
PIN CAVITY: CLOSED		STATUS	0 0 0 0 1 0 1 0
BSCCH PART NUMBER: 6002BE0235		Dim "X"	0 0 0 0 0 7 0 0
FCI PART NUMBER: F482200			
AU PLATING THICKNESS 0.5um MIN.			
FCI Mating Component Part No.	Description	Key Code	
F947100	104 Way Terminal Carrier Holder and Wire Dress Cover with Lever	B	
F577100	52 Way Terminal Carrier Left		
F477100	52 Way Terminal Carrier Right		
F767100	20 Way Terminal Carrier Holder with CPA	A	
D067100	20 Way Terminal Carrier		




CODING C / POPULATED 70		Mechanical Code For Header	
VARIANT COM. VI		CODE	V V V I I I I I I I
PIN CAVITY: CLOSED		STATUS	0 0 0 0 1 1 1 1
BOSCH PART NUMBER: 6002B0236		Dim "X"	0 0 0 0 0 7 0 7
FCI PART NUMBER: F337200			
Aw PLATING THICKNESS 0.5µm MIN.			
FCI Mating Component Part No	Description	Key Code	
F057100	104 Key Terminal Carrier Header and Wire Dress Cover with Lever	C	
F577100	52 Key Terminal Carrier Left		
F477100	52 Key Terminal Carrier Right		
F767100	20 Key Terminal Carrier Header with CPA	A	
F067100	20 Key Terminal Carrier		




CODING D / POPULATED TO VARIANT CONN_V1 PIN CAVITY: CLOSED BOSCH PART NUMBER: 6002BE0237 FCI PART NUMBER: F437200 Au PLATING THICKNESS 0.5µm MIN.		Mechanical Code For Header				
STATUS	V	I	V	I	I	I
CAGE CODE	0	0	1	0	0	0
Dim "X"	0	0	0	0	0	0

FCI Mating Component Part No	Description	Key Code
F157100	104 Key Terminal Carrier Holder and Wire Dress Cover with Lever	D
F577100	52 Key Terminal Carrier Left	
F477100	52 Key Terminal Carrier Right	
F767100	20 Key Terminal Carrier Holder with CPA	A




CODING A / POPULATED 86										Mechanical Code For Header			
VARIANT CONN.CMAX													
PIN CAVITY: CLOSED													
BOSCH PART NUMBER: 6002B0222										CODE			
FCI PART NUMBER: F537700										STATUS			
Au PLATING THICKNESS 0.5um MIN.										Dim "X" 0 0 0.7 0 0.			
FCI Mating Component Part No. Description										Key Code			
F847100 104 Way Terminal Carrier Holder and Wire Dress Cover with Laser										A			
F57100 30 Way Terminal Carrier Left													
F407100 30 Way Terminal Carrier Right													
F767100 20 Way Terminal Carrier Holder with CPA										A			
F067100 20 Way Terminal Carrier													




CODING B / POPULATED 86		Mechanical Code	
VARIANT CONN.CMAX		For Header	
PIN CAVITY: CLOSED		CODE	V IV I II I
BOSCH PART NUMBER: 600720E0238		STATUS	0 0 1 1 0
FCI PART NUMBER: F637000		Dim "X"	0 0 7.0 0 0
Au PLATING THICKNESS 0.5um MIN.			


FCI Mating Component Part No	Description	Key Code
F947100	104 Moy Terminal Carrier Holder and Wire Dress Cover with Lever	B
F577100	92 Moy Terminal Carrier Left	
F477100	50 Moy Terminal Carrier Right	
F767100	20 Moy Terminal Carrier Holder with CPA	A
F067100	20 Moy Terminal Carrier	




CODING A / POPULATED IIII		Mechanical Code For Header	
VARIANT CONN VS		CODE STATUS	V I V I I I I I I I
PIN CAVITY: CLOSED		III	I I I I I I I I
BOSCH PART NUMBER: 6002BE0226		Dim	X 0 0 70 7 0 7 0 7 0
FCI PART NUMBER: F447200			
Au PLATING THICKNESS 0.5µm MIN.			




CODING B : POPULATED 77 VARIANT : CON_V2 PIN CAVITY : OPEN BOSCH PART NUMBER : 6002B0223 TCI PART NUMBER : F93200 Aw PLATING THICKNESS 0.0002 IN.	NEW GRIPPER AREAS ADDED FOR THIS VARIANT	Mechanical Code For Header CODE V IV III II I STATUS 0 1 0 1 0 Dim "X" 0 0.7 0 0 0															
<table border="1"> <thead> <tr> <th>TCI Mating Component Part No</th> <th>Description</th> <th>Key Code</th> </tr> </thead> <tbody> <tr> <td>F145600</td> <td>100 Wt Terminal Carrier Holder and Wire Dress Cover with Lever</td> <td rowspan="3">B</td> </tr> <tr> <td>F135600</td> <td>52 Wt Terminal Carrier (Left)</td> </tr> <tr> <td>F235600</td> <td>52 Wt Terminal Carrier (Right)</td> </tr> <tr> <td>F047100</td> <td>20 Wt Terminal Carrier Holder with CPA</td> <td rowspan="2">A</td> </tr> <tr> <td>F937100</td> <td>20 Wt Terminal Carrier</td> </tr> </tbody> </table>	TCI Mating Component Part No	Description	Key Code	F145600	100 Wt Terminal Carrier Holder and Wire Dress Cover with Lever	B	F135600	52 Wt Terminal Carrier (Left)	F235600	52 Wt Terminal Carrier (Right)	F047100	20 Wt Terminal Carrier Holder with CPA	A	F937100	20 Wt Terminal Carrier		
TCI Mating Component Part No	Description	Key Code															
F145600	100 Wt Terminal Carrier Holder and Wire Dress Cover with Lever	B															
F135600	52 Wt Terminal Carrier (Left)																
F235600	52 Wt Terminal Carrier (Right)																
F047100	20 Wt Terminal Carrier Holder with CPA	A															
F937100	20 Wt Terminal Carrier																




COUING C / POPULATED 93 VARIANT CONN.V3 P1N CAVITY: OPEN BOSCH PART NUMBER: 6002BE0224 FCI PART NUMBER: F047100 Au PLATING THICKNESS 0.8µm MIN.		NEW GRIPPER AREAS ADDED FOR THIS VARIANT.		Mechanical Code For Header			
				V	IV	III	II
				STATUS	0	1	0
				Dim "X"	0	0.7	0



COUING A / POPULATED I/O VARIANT CONN_V4 PIN CAVITY: OPEN BOSCH PART NUMBER: 60020E0225 FC1 PART NUMBER: F342700 Au PLATING THICKNESS 0.8um MIN.		<table border="1"> <tr> <th colspan="6">Mechanical Code For Header</th> </tr> <tr> <th>CODE</th> <th>V</th> <th>IV</th> <th>I</th> <th>II</th> <th>III</th> </tr> <tr> <td>STATUS</td> <td>0</td> <td>1</td> <td>1</td> <td>0</td> <td>1</td> </tr> <tr> <td>Dim "X"</td> <td>0</td> <td>0.70</td> <td>7.0</td> <td>0</td> <td>0</td> </tr> </table>	Mechanical Code For Header						CODE	V	IV	I	II	III	STATUS	0	1	1	0	1	Dim "X"	0	0.70	7.0	0	0
Mechanical Code For Header																										
CODE	V	IV	I	II	III																					
STATUS	0	1	1	0	1																					
Dim "X"	0	0.70	7.0	0	0																					
FC1 Mating Component Part No.	Description	Key Code																								
F627100	104 Key Terminal Carrier Holder and Wire Dress Cover with Lexar	A																								
F627100	32 Key Terminal Carrier Left																									
F527100	32 Key Terminal Carrier Right																									
F047100	20 Key Terminal Carrier Holder with CPA	A																								
F937100	20 Key Terminal Carrier																									




CODING A / POPULATED III		Mechanical Code				
VARIANT CON.V5		For Header				
PIN CAVITY: OPEN		CODE	V	IV	III	II
BOSCH PART NUMBER: 6002BE268		STATUS	0	1	1	0
FCI PART NUMBER: 1815300		Dim "X"	0	0.70	7.0	0
Au PLATING THICKNESS 0.8µm MIN.						




CODING D / POPULATED I01		Mechanical Code	
VARIANT XXX		For Header	
PIN CAVITY: OPEN		V	IV III II I
BOSCH PART NUMBER: 6002BE033		STATUS	0 1 1 1
FCI PART NUMBER: F66970		Dim 'X'	0 70 70 70 7
Av PLATING THICKNESS 0.8um MIN.			

NEW GRIPPER AREAS ADDED FOR THIS VARIANT.


ICI Tooling Component Part No	Description	Key Code
F927100	104 Yaw Terminal Carrier Holder and Wire Dress Cover with Lever	D
F427100	52 Yaw Terminal Carrier Left	
F527100	52 Yaw Terminal Carrier Right	
F047100	20 Yaw Terminal Carrier Holder with CPA	A





CODING B / POPULATED IO VARIANT CONN.V4 PIN CAVITY: OPEN BOSCH PART NUMBER: 6002BE0241 FCI PART NUMBER: FJ47200 AU PLATING THICKNESS 0.8µm MIN.		Mechanical Code For Header
	CODE	V I V III II I
	STATUS	I O O O O
	Dim	"X".0 ".7" 0
ICI Mating Component Part No. Description	Key Code	
F145600 104 Way Terminal Carrier Holder and Wire Dress Cover with Lever	B	
F135600 52 Way Terminal Carrier Left		
F235600 52 Way Terminal Carrier Right		
F047100 26 Way Terminal Carrier Holder with CPA	A	
F937100 26 Way Terminal Carrier		



CODING E / POPULATED IIII		Mechanical Code	
VARIANT XXX		For Header	
PIN CAVITY: OPEN		CODE	
BOSCH PART NUMBER: 6002BE0334		V I I I I I I I	
FCI PART NUMBER: 7679370		STATE	
Au PLATING Thickness 0.8µm MIN.		0 0 0 0 0 0 0 0	
Dim 'X' 0 0.70 0.70 0.70			
FCI Mating Component Part No./Description			Key Code
F037100	104 Way Terminal Carrier Holder and Wire Dress Cover with Lever		
F427100	50 Way Terminal Carrier Left	E	
F527100	50 Way Terminal Carrier Right		
F047100	20 Way Terminal Carrier Holder with CPA		
F937100	20 Way Terminal Carrier	A	



CODING C / POPULATED I01		Mechanical Code	
VARIANT COM V4		For Header	
P/N CAVITY: OPEN		C	V IV III II I
BOSCH PART NUMBER: 6002B0242		STATUS	1 0 0 0
FCI PART NUMBER: F24200		Dim	'X' 0.7 0 0 0 0
Au PLATING THICKNESS 0.8µm MIN.			



UNUSED/DEPOPULATED PINS

Mechanical Code For Header					
CODE STATUS	V	IV	III	II	I
Dim 'X'	0	0	0	0	1

0 - ABSENCE OF MECHANICAL CODE (I, II, III, IV OR V)
1 - PRESENCE OF MECHANICAL CODE (I, II, III, IV OR V)

[illegible]

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[F931300](#) [F947100](#) [F767100](#) [F577100](#) [F067100](#) [F847100](#) [F477100](#)