


DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD 1	APVD 2
DATE	STG	REV	N/P	CHG						
20SE99	-	01	-	-		CLEARED REVISION COLUMN REVISED NOTES & GRAPHICS	195715	JHH	JHH	RJ
19MY00	-	02	-	-		ALL PARTS - CREATED SOLID MODELS & REVISED INSPECTION SYMBOLS	200225	FRG	GGI	MW
22OC01	-	03	-	-		ALL PARTS - UPDATED PDM ATTRIBUTES	215725	JMR	JMR	MW
16AP02	-	04	-	-		DIM F WAS +/-0.1 & UPDATED FORMAT	223829	RAB	RAB	MD
06N002	R	05	-	-		12177007 - UPDATED PDM ATTRIBUTES	232853	TLD	TLD	MJD
03JA03	R	06	-	-		12177007 & 12129361 - 2X 3.9500.15 WAS 2X 3.9500.1	235051	TLD	TLD	RF
12FE04	R	07	-	-		12177007 & 12129361 - REVISED CHART ADDED MATERIAL SPEC COLUMN	251019	CTR	JAA	MD
25AP13	R	08	-	-		12177007 & 12129361 - CABLE SIZE WAS 0.35	422257	ORA	JAA	JFF
18SE14	R	09	-	-		DIMENSION AND NOTE CLARIFICATIONS	427671	MM	JMS	JDD
30OC14	R	10	-	-		12177007 & 12129361: 2X 0.1 MIN SEE NOTE B WAS 2X 0.25 MIN; ADDED NOTE B.	428085	MM	MM	JDD
14NO16	R	11	-	-		12129361 & 12177007 - UPDATED PDM ATTRIBUTES	434891	JVM	JVM	LES



- | | |
|---|------------------|
| A LINE DRAWN THROUGH A PART NUMBER
INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE
FOR ORDERING. | |
| PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE
THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING. | |
| CONTACT DELPHI SALES TO ASSURE AVAILABILITY
OF PARTS. | |
| DWG TYPE | |
| PART DRAWING | |
| STYLE | |
| VOLUME (GM ³) | DISTR CODE |
| | D |
| UNLESS OTHERWISE SPECIFIED | |
| THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5-1994
AS AMENDED BY THE GM GLOBAL DIMENSIONING AND
TOLERANCING ADDENDUM - 1997. ALL GEOMETRIC TOLERANCES
AND RELATED DATUMS APPLY. IF'S, RULE #1 (PERFECT FORM AT
MMC) DOES NOT APPLY, WHEN RELATIONSHIP BETWEEN FEATURES
IS ESTABLISHED BY ORIENTATION OR LOCATION TOLERANCES.
SEPARATE POSITION CALLOUTS MAY BE GAGED SEPARATELY,
REGARDLESS OF DATUM REFERENCE. | |
| ALL DIMENSIONS ARE IN MILLIMETERS | |
| REFERENCE | |
| THIRD ANGLE
PROJECTION | DO NOT
SCALE |
| | USE MATH
DATA |
| | |
| | |

<h1 style="text-align: center;">DELPHI</h1> <p style="text-align: center;">DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE</p> <p style="text-align: center;">WARREN, OH</p> <p style="text-align: center;">COPYRIGHT 1988 DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED.</p> <p style="text-align: center;">REVISED 2016</p> <p style="text-align: center;">THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.</p>									
								DATE	
DR									
APVD1 ROGER WAYT								01FE88	
APVD2 TOM NADASKY								14MY88	
APVD3 JOHN YURTIN								26MY88	
APVD4									
APVD5									
SUBSTANCE OF CONCERN AND RECYCLED CONTENT PER DELPHI-A 10949001									
MATERIAL SEE CHART									
DRAWING NAME									
TAXI TERM F MIC/P 064 LOCKING LANCE									
DRAWING NUMBER									
12092439									
SIZE	SCALE	FRAME NO	SHEET NO	STG	REV	N/P			
A1	10:1	1 OF 1	1 OF 1	R	11	-			

12177007	A12	-	0.35-0.5	1.63 MAX	22	GOLD PLATED HIGH PERF COPPER ALLOY	GOLD	2.1 +/-0.2
12129361	A12	-	0.35-0.5	1.63 MAX	22	TIN PLATED HIGH PERF COPPER ALLOY	TIN	2.1 +/-0.2
12092440	H3	-	0.35	1.63 MAX	22	-	TIN	2.1
PART NO	REV	N/P	SIZE (MM²)	DIA	ID	MAT'L SPEC	CONTACT INTERFACE	F
				CABLE				

10		PROCESS SENSITIVE DIMENSION
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED		
DIMENSIONAL RANGE (MM)		CHART
FROM	0	> 12
TO	12	
TOLERANCE UNLESS OTHERWISE SPECIFIED		
	±0.1	±0.2
ANGULAR TOLERANCE ±2°		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)
[12129361](#)