

SYMBOL DEFINITION		
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL () DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON THE INDIVIDUAL COMPONENT DRAWING.		
TOTAL NO OF INSPECTIONS REQUIRED	9	
LAST NO. USED	14	

MISSING SYMBOLS	
5-9	

DWG STATUS				ZONE	REVISION HISTORY	AUTH	DR
DATE	STG	REV	N/P				
10DE02	R	01	-	-	WAS PE068949 AND RELEASED	234532	EE
06AU03	R	02	-	-	15476168 WAS PE068952 AND RELEASED; UPDATED PDM ATTRIBUTES	243974	ADH
15DE03	R	03	-	-	ALL PARTS - REMOVED ASM DIMS (2 PLCS), UPDATED PDM ATTRIBUTES	249883	EE
21JN04	R	04	-	-	15476168 - REVISED GRAPHICS	256228	EE
12JA05	R	05	-	-	ALL PARTS - ADDED NOTE #5	263105	CCV
10MY05	R	06	-	-	13519885 - RELEASED	267888	BL
12AP10	R	07	-	-	13519885 - INACTIVE	410478	JRL
24OC11	R	08	-	-	ALL ACTIVE PARTS - UPDATED PDM ATTRIBUTES	415860	MA
06JA12	R	09	-	-	15455571 & 15476168 - ADDED TARNISH NOTE	416635	MA
03AU12	R	10	-	-	ALL PARTS - DIM 10 WAS 7.42 ± 0.08 AND UPDATED MAT'L CALLOUT	419113	AH
30MY13	R	11	-	-	ALL PARTS - ADDED "PREFERRED MAT'L SIZE" COLUMN	422691	CAF
01AU13	R	12	-	-	13519885 - SIZE MMF WAS 0.8-1 AND CABLE DIA WAS 2.3 -1.7	423439	YVH
04NO13	R	13	-	-	13519885 - REVISION 02AB WAS 03 AUTH NUMBER 422691; 13519885 - SIZE MMF WAS 0.8-1 AND CABLE DIA WAS 2.3 -1.7	424486	YVH
17FE14	R	14	-	-	13519885 - CABLE 1D WAS 17	425566	YVH
					13519885 - UPDATED PART AVAILABILITY		

14
STAMP 'PXX' ON UNDERSIDE IN THIS AREA
0.8 MIN HIGH CHARACTERS PER NOTE #7
CHARACTERS MUST BE POSITIONED IN
DIRECTION SHOWN OR AT 180° TO DIRECTION
SHOWN

10
7.42
+0.08
-0.2


1
STAMP CABLE I.D. (SEE CHART) ON UNDERSIDE
IN THIS AREA WITH 0.8 MIN. HIGH NUMBERS

11
8.9 ± 0.15

12 (L)

13
B₁

TYPE 101



FOR SEAL INFORMATION SEE
DRAWING 12010295 SHEET #2

0.75 ± 0.75

25.3 MAX

NOTES

- * DENOTES DIMENSIONS MADE AT CUT-OFF AND CRIMP DIE.
- RECOMMENDED MATING BLADE: WIDTH 6.4/6.2, THICKNESS 0.83/0.77 & LENGTH 8.4/8.6.
- MATING TERMINAL TBD OR EQUIVALENT
- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

- PACKAGING REQUIREMENTS:
A. TERMINALS ON REELS TO USE SILVER SAYER NT TARNISH PAPER INTERLEAF.
B. TERMINALS ON REELS TO BE PACKAGED IN PASSIVATED CARDBOARD BOXES.
- DO NOT PROBE, TEST OR OTHERWISE CONTACT THE INTERIOR REGION (THE
SPRING OR ANY MOVING PART) OF THIS TERMINAL. SEVERE DAMAGE CAN
OCCUR, COMPROMISING THE PERFORMANCE OF THE ELECTRICAL INTERFACE.
- "PXX" INDICATES "P" PLUS LAST TWO DIGITS OF MAKE DIE
SERIES NUMBER (P01, P02, P03, ETC).
- TARNISH CAN BE DEVELOP IF TERMINALS ARE EXPOSED TO THE
ENVIRONMENT, TARNISH WILL NOT AFFECT FIT/FUNCTION OF THE PART.

PROCESS SENSITIVE DIMENSION	
DIMENSIONS ENCLOSED IN () INDICATE REFERENCE DIMENSIONS AND NO TOLERANCE LIMITS ARE ESTABLISHED	
DIMENSIONAL RANGE (MM)	CHART D
FROM 0 TO 12	>12
TOLERANCE UNLESS OTHERWISE SPECIFIED	
±0.1	±0.2
ANGULAR TOLERANCE 22°	

LINE DRAWN THROUGH A PART NUMBER INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE FOR ORDERING.	
PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.	
CONTACT DELPHI SALES TO ASSURE AVAILABILITY OF PARTS.	
DWG TYPE	PART DRAWING
BTITLE	
VOLUME (CM)	DISTR CODE
	D
UNLESS OTHERWISE SPECIFIED	
THIS DOCUMENT IS IN ACCORDANCE WITH ASME Y14.5M-1994 AS AMENDED BY THE 2003 GLOBAL DIMENSIONING AND TOLERANCING ADDENDUM-2001. SEPARATE PATTERNS OF FEATURES MAY BE SHOWN SEPARATELY REMOVED OF DATUM REFERENCES.	
ALL DIMENSIONS ARE IN MILLIMETERS	
REFERENCE	
THIRD ANGLE PROJECTION	DO NOT SCALE
USE MATH DATA	NX

DELPHI	
DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE	
WARREN, OH	
COPYRIGHT 2002 DELPHI CORPORATION AND/OR ITS AFFILIATES ALL RIGHTS RESERVED.	
THIS DRAWING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA DATA AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHER WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED.	
DR	
APV01 E. SEIDEL	101
APV02 E. SEIDEL	101
APV03 E. HAROLDSON	111
APV04	
APV05	
SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001	
MATERIAL SEE CHART	
DRAWING NAME TAXI TERM F GT 630 SEALED	
DRAWING NUMBER 15455570	
SIZE A1	SCALE 5:1
FRAME NO 1 OF 1	SHEET NO 1 OF 1
SYN	R

TERMINAL, SEAL AND CABLE ALIGNMENT VIEW

13519885	02	AE	0.38 X 29.09	0.38 X 29.76	AG PLATED COPPER ALLOY	0.8 - 1	18	2.3 - 1.7	101	21.35	3.1
15476168	02	AA	0.38 X 29.09	0.38 X 29.76	AG PLATED COPPER ALLOY	4 - 6	10	4.3 - 3.4	101	21.35	5.8
15455571	02	AA	0.38 X 29.09	0.38 X 29.76	AG PLATED COPPER ALLOY	2 - 3	13	3.2 - 2.5	101	21.35	4.2
PART NO	REV	N/P	PREFERRED MAT'L SIZE	ALTERNATIVE MAT'L SIZE	MAT'L SPEC	SIZE (MM)	ID	DIA	TYPE	(L)	B ₁ ± 0.2
			PLATED		CABLE						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[15476168](#)