


SECTION B-B



SECTION C-C

- ## NOTES

1. UNLESS OTHERWISE SPECIFIED AND/OR INDICATED:

DIMENSIONS ARE TO FACE OF VIEW SHOWN AND  
AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION  
(SEE MATH MODEL FOR PRECISE DIMENSIONS). FOR ALL  
OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL  
BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.

2. RECOMMENDED MATING BLADE THICKNESS  $0.6 \pm 0.03$  MM OR  $0.64 \pm 0.03$  MM  
RECOMMENDED MATING BLADE WIDTH NOT TO EXCEED 1.2 MM  
AND NO LESS THAN 0.61 MM.

3. MAXIMUM CURRENT CAPACITY IS 10 AMPS WITH 0.8 MM<sup>2</sup> COPPER CABLE.

4. CRIMP DIMENSION FROM THE BACK OF THE CORE WING (INCLUDES THE FLARE OUT FROM THE CORE WING) TO THE END OF THE INSULATION WING.

- 2.05 MM MAX WIDTH, 2.1 MM MAX HEIGHT FOR CABLE SIZE UP TO 1.9 MM

- 2.35 MM MAX WIDTH, 2.40 MM MAX HEIGHT FOR CABLE SIZE BETWEEN 1.86 TO 2.25 MM O.D.  
2.67 MM MAX WIDTH, 2.67 MM MAX HEIGHT FOR CABLE SIZE BETWEEN 2.25 TO 2.40 MM O.D.

5. \* DENOTES DIMENSIONS MADE AT CUT-OFF & CRIMP DIE.

6. PLUS ANGLE IS WING BOTTOM SURFACE ROTATED COUNTERCLOCKWISE AGAINST THE BOX BOTTOM SURFACE.

1.4  
T. 1000

MISSING SYMBOLS
1 7

DWG STATUS					ZONE	REVISION HISTORY	AUTH	DR	APVD	APD2
DATE	STG	REV	N/P	CHG						
28FE19	R	01	-	-	ALL PARTS - RELEASED PART DRAWING	442472	LVD	RBS	RBS	
26AP19	R	02	-	-	35072397-98 - UPDATED PART AVAILABILITY	443031	JLL	JAS	OMS	
17JN19	R	03	-	-	35072396 - UPDATED PART AVAILABILITY	443686	GDH	JAA	OMS	
29NO19	R	04	-	-	35072396 - SIZEZ WAS 0.25-0.5 & DIA WAS 1.47-1.9; 35410017 - RELEASED	550373	LVD	JAA	RBS	

LINE DRAWN THROUGH A PORT NUMBER  
INDICATES THAT PHYSICAL PARTS ARE NOT AVAILABLE  
FOR ORDERING.

PART NUMBERS THAT DO NOT HAVE A LINE PRESENT INDICATE  
THAT PHYSICAL PARTS ARE AVAILABLE FOR ORDERING.

CONTACT APPLIC SALES TO ASSURE AVAILABILITY  
PARTS.

NEW TYPE

PART DRAWING

STYLE

VOLUME (CM<sup>3</sup>)

DISTR CODE

UNLESS OTHERWISE SPECIFIED

THIS DOCUMENT IS IN ACCORDANCE WITH ASME  
Y14.100, USE ASME Y14.100 ENGINTEERING DESIGN  
STANDARD 36-2017 FOR ISO 10112:2004  
RECOMMENDATION REQUIREMENTS.




ALL DIMENSIONS ARE IN MILLIMETERS

REFERENCE

THIRD ANGLE  
PROJECTION

DO NOT  
SCALE

USE MATH DATA

   **NX**

<h1 style="margin: 0;">• APTIV •</h1> <p style="margin: 5px 0;">CONNECTION SYSTEMS</p> <p style="margin: 5px 0;">WARREN, OH</p> <p style="margin: 5px 0;">COPYRIGHT 2019 APTIV, ALL RIGHTS RESERVED.</p> <p style="margin: 5px 0;">THIS DRAWING IS THE PROPERTY OF APTIV AND CONTAINS APTIV          CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND          UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD MATH DATA, AS WELL          AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS          AUTHORIZATION, IS PROHIBITED.</p>									
								DATE	
<div style="display: flex; justify-content: space-between;"> <div style="width: 15%;">                 DR                  APVD01                  APV02                  APV03                  APV04                  APV05             </div> <div style="width: 85%;">                 LUIS VILLARREAL                  ROBERT B SNADER                  ROBERT B SNADER                  ROBERT B SNADER                  SUBSTANCES OF THE HAZARDOUS AND RECYCLED                  CONTENT PER APTIV 10949001             </div> </div>									
MATERIAL SEE CHART									
DRAWING NAME <div style="text-align: center; font-size: 24px; font-weight: bold; margin-top: 20px;">                     TAXI TERM F_OCS 1.2                 </div>									
DRAWING NUMBER <div style="font-size: 48px; font-weight: bold; margin-top: 10px;">                     13543112                 </div>									
SIZE		SCALE		FHEET NO		SHEET NO		STO REV / N/P	
A0		10:1		1 OF 1		10		R 04 -	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Aptiv:](#)

[35072397-L](#) [35072398-L](#) [35072396-L](#) [35072396](#) [35072398](#) [35072397](#)